





METRIC COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M	
BILL OF MATERIAL					
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS () ARE INCHES					
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.					
		DENOTES CRITICAL CHARACTERISTICS.			
	CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
	CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

MATL SPEC		2.0mm MS PLATE	
COPIES TO		FINISH	
1	9	ZINC CHROMATE PLATED (t = 3-8 microns)	
2	10		
3	12		
4	13		
5	14		
6	15		
7	16		
8	17		
DATE		SCALE	
20/0ct/16		1:1	
DATE		SUPER DR	
DATE		FINSH GOOD WT	
APPD		GRAMS/PIECE	
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MH)			
DIMENSION		UP TO OVER UP TO OVER UP TO OVER	
0.5 - 3		3 - 6 6 - 30 30 - 120 120 - 400	
TOLERANCE		±0.1 ±0.1 ±0.2 ±0.3 ±0.5	
3RD ANGLE PROJECTION			
TITLE		METAL BRACKET	
(for HWB18,12&6)			
REVISION		DRWG. NO.	
B		868-068	
LITTLEFUSE®		OUTLINE	
LIPA CITY, BATANGAS, PHILIPPINES			