




- NOTES:
1. TOLERANCES PLUS OR MINUS 0.015 [0.38]
 2. CONTACT AREA SEALED TO IP67
 3. BACK OF SWITCH SEALED WHEN MATING CONNECTOR IS INSTALLED
 4. FOR RESISTIVE LOAD RATING SEE CHART OR BACK OF SWITCH
 5. KEY REMOVABLE IN OFF POSITION ONLY
 6. FOR PIN LOCATIONS SEE CHART
 7. MATERIALS: HOUSING BLACK THERMOPLASTIC
 8. KEY BOOT FITS OVER FACE NUT
 9. SWITCH TESTED TO SAE J259, UL RECOGNIZED TO UL 1054
 10. SWITCH 95060-50 IS MADE UP OF 95060 SWITCH & 31101 CONNECTOR
 11. SW. MUST NOT BREAK CIRCUIT OR BE DAMAGED IF TORQUED TO 15 IN-LBS [1.68Nm]
 12. IF THE APPLICATION MOUNTS THE SWITCH WITH THE LOCK CYLINDER OR LEVER APPROACHING VERTICAL, CONTACT THE FACTORY FOR AN APPLICATION REVIEW AND POTENTIAL ALTERNATE PRODUCTS BEFORE DESIGN IS SET.

PIN NUMBER	CIRCUIT	12VDC RESISTIVE LOAD	WIRE COLOR
2	START	5 AMPS	YELLOW WITH RED STRIP
3	ACCESSORY	10 AMPS	ORANGE
4 & 5	IGNITION	10 AMPS	PURPLE
1 & 6	BATTERY		RED

PINS 1 & 6 CONNECTED TOGETHER INTERNALLY
PINS 4 & 5 CONNECTED TOGETHER INTERNALLY

Revision Control Record				Cole Hersee Co.			
Rev.	Description of Change	ECN No.	Date	20 Old Colony Ave., South Boston, MA, 02127 Phn: 617-288-2100 Web: www.colehersee.com			
A	RELEASED DRAWING	10348	9/28/10	Special Characteristics: CC Critical Characteristic, relating to Safety and/or Regulatory Compliance X Significant Characteristic relating to Process Control CC Control Dimension relating to Form - Fit - Function as defined by the Customer			
B	ADDED MADE IN TAIWAN	11215	7/15/11				
C	ADDED HENCOL 13; ADDED TORQUE NOTE	13176	6/28/13				
				Drawing / Part No.:		Current Rev.	
				95060-50		C	

1

2

3

4