

preliminary

# Sonic Fast Recovery Diode

$$V_{RRM} = 1200 \text{ V}$$


$$I_{FAV} = 2 \times 50 \text{ A}$$

$$t_{rr} = 200 \text{ ns}$$

High Performance Fast Recovery Diode  
 Low Loss and Soft Recovery  
 Parallel legs


Part number

**DHG100X1200NA**



Backside: Isolated

 E72873



## Features / Advantages:

- Planar passivated chips
- Very low leakage current
- Very short recovery time
- Improved thermal behaviour
- Very low  $I_{rm}$ -values
- Very soft recovery behaviour
- Avalanche voltage rated for reliable operation
- Soft reverse recovery for low EMI/RFI
- Low  $I_{rm}$  reduces:
  - Power dissipation within the diode
  - Turn-on loss in the commutating switch

## Applications:

- Antiparallel diode for high frequency switching devices
- Antisaturation diode
- Snubber diode
- Free wheeling diode
- Rectifiers in switch mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)

## Package: SOT-227B (minibloc)

- Isolation Voltage: 3000 V~
- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0
- Base plate: Copper internally DCB isolated
- Advanced power cycling


## Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).



| Fast Diode |                                              |                                                                                   |                                | Ratings                        |      |      |               |
|------------|----------------------------------------------|-----------------------------------------------------------------------------------|--------------------------------|--------------------------------|------|------|---------------|
| Symbol     | Definition                                   | Conditions                                                                        |                                | min.                           | typ. | max. | Unit          |
| $V_{RSM}$  | max. non-repetitive reverse blocking voltage | $T_{VJ} = 25^{\circ}\text{C}$                                                     |                                |                                |      | 1200 | V             |
| $V_{RRM}$  | max. repetitive reverse blocking voltage     | $T_{VJ} = 25^{\circ}\text{C}$                                                     |                                |                                |      | 1200 | V             |
| $I_R$      | reverse current, drain current               | $V_R = 1200\text{ V}$                                                             | $T_{VJ} = 25^{\circ}\text{C}$  |                                |      | 100  | $\mu\text{A}$ |
|            |                                              | $V_R = 1200\text{ V}$                                                             | $T_{VJ} = 125^{\circ}\text{C}$ |                                |      | 1.2  | mA            |
| $V_F$      | forward voltage drop                         | $I_F = 50\text{ A}$                                                               | $T_{VJ} = 25^{\circ}\text{C}$  |                                |      | 2.16 | V             |
|            |                                              | $I_F = 100\text{ A}$                                                              |                                |                                |      | 2.78 | V             |
|            |                                              | $I_F = 50\text{ A}$                                                               | $T_{VJ} = 125^{\circ}\text{C}$ |                                |      | 2.13 | V             |
|            |                                              | $I_F = 100\text{ A}$                                                              |                                |                                |      | 2.97 | V             |
| $I_{FAV}$  | average forward current                      | $T_C = 65^{\circ}\text{C}$<br>rectangular $d = 0.5$                               | $T_{VJ} = 150^{\circ}\text{C}$ |                                |      | 50   | A             |
| $V_{F0}$   | threshold voltage                            | } for power loss calculation only                                                 |                                | $T_{VJ} = 150^{\circ}\text{C}$ |      | 1.26 | V             |
| $r_F$      | slope resistance                             |                                                                                   |                                |                                |      | 15.3 | m $\Omega$    |
| $R_{thJC}$ | thermal resistance junction to case          |                                                                                   |                                |                                |      | 0.6  | K/W           |
| $R_{thCH}$ | thermal resistance case to heatsink          |                                                                                   |                                |                                | 0.1  |      | K/W           |
| $P_{tot}$  | total power dissipation                      | $T_C = 25^{\circ}\text{C}$                                                        |                                |                                |      | 200  | W             |
| $I_{FSM}$  | max. forward surge current                   | $t = 10\text{ ms}; (50\text{ Hz}), \text{ sine}; V_R = 0\text{ V}$                | $T_{VJ} = 45^{\circ}\text{C}$  |                                |      | 500  | A             |
| $C_J$      | junction capacitance                         | $V_R = 600\text{ V}$ $f = 1\text{ MHz}$                                           | $T_{VJ} = 25^{\circ}\text{C}$  |                                | 27   |      | pF            |
| $I_{RM}$   | max. reverse recovery current                | $I_F = 60\text{ A}; V_R = 600\text{ V}$<br>$-di_F/dt = 1200\text{ A}/\mu\text{s}$ |                                | $T_{VJ} = 25^{\circ}\text{C}$  |      | 45   | A             |
|            |                                              |                                                                                   |                                | $T_{VJ} = 125^{\circ}\text{C}$ |      | 60   | A             |
| $t_{rr}$   | reverse recovery time                        |                                                                                   |                                | $T_{VJ} = 25^{\circ}\text{C}$  |      | 200  | ns            |
|            |                                              |                                                                                   |                                | $T_{VJ} = 125^{\circ}\text{C}$ |      | 350  | ns            |

| Package SOT-227B (minibloc) |                                                              |                      |                                     | Ratings |      |      |      |
|-----------------------------|--------------------------------------------------------------|----------------------|-------------------------------------|---------|------|------|------|
| Symbol                      | Definition                                                   | Conditions           |                                     | min.    | typ. | max. | Unit |
| $I_{RMS}$                   | RMS current                                                  | per terminal         |                                     |         |      | 100  | A    |
| $T_{VJ}$                    | virtual junction temperature                                 |                      |                                     | -40     |      | 150  | °C   |
| $T_{op}$                    | operation temperature                                        |                      |                                     | -40     |      | 125  | °C   |
| $T_{stg}$                   | storage temperature                                          |                      |                                     | -40     |      | 150  | °C   |
| <b>Weight</b>               |                                                              |                      |                                     |         | 30   |      | g    |
| $M_D$                       | mounting torque                                              |                      |                                     | 1.1     |      | 1.5  | Nm   |
| $M_T$                       | terminal torque                                              |                      |                                     | 1.1     |      | 1.5  | Nm   |
| $d_{Spp/App}$               | creepage distance on surface   striking distance through air | terminal to terminal | 10.5                                | 3.2     |      |      | mm   |
| $d_{Spb/Apb}$               |                                                              | terminal to backside | 8.6                                 | 6.8     |      |      | mm   |
| $V_{ISOL}$                  | isolation voltage                                            | t = 1 second         | 50/60 Hz, RMS; $I_{ISOL} \leq 1$ mA | 3000    |      |      | V    |
|                             |                                                              | t = 1 minute         |                                     | 2500    |      |      | V    |




### Part description


D = Diode  
 H = Sonic Fast Recovery Diode  
 G = extreme fast  
 100 = Current Rating [A]  
 X = Parallel legs  
 1200 = Reverse Voltage [V]  
 NA = SOT-227B (minibloc)

| Ordering | Ordering Number | Marking on Product | Delivery Mode | Quantity | Code No. |
|----------|-----------------|--------------------|---------------|----------|----------|
| Standard | DHG100X1200NA   | DHG100X1200NA      | Tube          | 10       | 507759   |


### Equivalent Circuits for Simulation

\* on die level

 $T_{VJ} = 150^{\circ}\text{C}$ 


**Outlines SOT-227B (minibloc)**


| Dim. | Millimeter |       | Inches |       |
|------|------------|-------|--------|-------|
|      | min        | max   | min    | max   |
| A    | 31.50      | 31.88 | 1.240  | 1.255 |
| B    | 7.80       | 8.20  | 0.307  | 0.323 |
| C    | 4.09       | 4.29  | 0.161  | 0.169 |
| D    | 4.09       | 4.29  | 0.161  | 0.169 |
| E    | 4.09       | 4.29  | 0.161  | 0.169 |
| F    | 14.91      | 15.11 | 0.587  | 0.595 |
| G    | 30.12      | 30.30 | 1.186  | 1.193 |
| H    | 37.80      | 38.23 | 1.488  | 1.505 |
| J    | 11.68      | 12.22 | 0.460  | 0.481 |
| K    | 8.92       | 9.60  | 0.351  | 0.378 |
| L    | 0.74       | 0.84  | 0.029  | 0.033 |
| M    | 12.50      | 13.10 | 0.492  | 0.516 |
| N    | 25.15      | 25.42 | 0.990  | 1.001 |
| O    | 1.95       | 2.13  | 0.077  | 0.084 |
| P    | 4.95       | 6.20  | 0.195  | 0.244 |
| Q    | 26.54      | 26.90 | 1.045  | 1.059 |
| R    | 3.94       | 4.42  | 0.155  | 0.167 |
| S    | 4.55       | 4.85  | 0.179  | 0.191 |
| T    | 24.59      | 25.25 | 0.968  | 0.994 |
| U    | -0.05      | 0.10  | -0.002 | 0.004 |
| V    | 3.20       | 5.50  | 0.126  | 0.217 |
| W    | 19.81      | 21.08 | 0.780  | 0.830 |
| Z    | 2.50       | 2.70  | 0.098  | 0.106 |







**Fast Diode**

 Fig. 1 Typ. Forward current versus  $V_F$ 

 Fig. 2 Typ. reverse recov. charge  $Q_{rr}$  versus  $di_F/dt$ 

 Fig. 3 Typ. peak reverse current  $I_{RM}$  versus  $di_F/dt$ 

 Fig. 4 Dynamic parameters  $Q_{rr}$ ,  $I_{RM}$  versus  $T_{VJ}$ 



 Fig. 5 Typ. recovery time  $t_{rr}$  versus  $di_F/dt$ 

 Fig. 6 Typ. recovery energy  $E_{rec}$  versus  $di_F/dt$ 


Fig. 7 Typ. transient thermal impedance junction to case