


# ATO® FBA5 Series

## 32V 5-Position Terminal Fuse Block



### Description

The ATO® FBA5 Series 32V 5-Position Terminal Fuse Block helps you protect up to 5 circuits using ATO® blade fuses rated up to 15A (fuses sold separately). Supporting up to 11A of continuous current, this ATO® fuse box is ideal for accessory lighting, audio and display equipment, and communications equipment.

The ATO® FBA5 Series fuse holder is available in panel-mount versions featuring Quick Connect terminals on either the side or the bottom of the box for simple wiring. Detachable side-mounting brackets are included with the bottom, vertical terminal option and are available for the side, horizontal terminal option. For versatility, the ATO® FBA5 Series fuse holder is also available with printed circuit board (PCB) terminals.

In addition, the 5-position fuse block comes with a clear protective cover, which safeguards the installed fuses from dust and debris while making it easy to view and identify blown fuses. The clear cover is a feature that's especially useful when using ATO® Smart Glow fuses.

### Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/FBA5](http://littelfuse.com/FBA5)

### Specifications

<b>Current Rating Max:</b>	15A
<b>Fuse Type:</b>	ATO® Fuse
<b>Mounting Method:</b>	Horizontal Contacts Mount, Vertical Contacts Mount, PCB Mount
<b>Max Voltage Rating:</b>	32V DC

### Applications

- Accessory Lighting
- Audio & Display Equipment
- Communications Equipment

### Features and Benefits

- Works with 5 ATO® blade fuses rated up to 15A (fuses sold separately)
- Supports up to 11A of continuous current
- Panel-mount configurations feature Quick Connect terminals positioned at either the side (horizontal terminals) or the bottom of the box (vertical terminals)
- Detachable side-mounting brackets are included with the panel-mount vertical terminal version and are optional for the panel-mount horizontal terminal version
- Available with printed circuit board (PCB) terminals
- Removable, Smart Glow fuse-compatible, clear polycarbonate cover protects installed fuses from debris and dislodgement and allows easy viewing for identifying blown fuses

### Ordering Information

PART NUMBER	DESCRIPTION	CURRENT RATING MAX	FUSE TYPE	MOUNTING METHOD	MAX VOLTAGE RATING
03500417TXN (W/O Fuse)	32V 5-Position Panel-Mount Horizontal-Terminal Fuse Block	15 AMPS	ATO FUSE	HORIZONTAL CONTACTS MOUNT	32V DC
03500417XP (W/O FUSE)	32V 5-Position Panel-Mount Horizontal-Terminal Fuse Block - Blister Pack	15 AMPS	ATO FUSE	HORIZONTAL CONTACTS MOUNT	32V DC
03500417Z (W/O FUSE)	32V 5-Position Panel-Mount Horizontal-Terminal Fuse Block - Bulk	15 AMPS	ATO FUSE	HORIZONTAL CONTACTS MOUNT	32V DC
03500418TXN (W/O FUSE)	32V 5-Position Panel-Mount Vertical-Terminal Fuse Block	15 AMPS	ATO FUSE	VERTICAL CONTACTS MOUNT	32V DC
03500418XP (W/O Fuse)	32V 5-Position Panel-Mount Vertical-Terminal Fuse Block - Blister Pack	15 AMPS	ATO FUSE	VERTICAL CONTACTS MOUNT	32V DC
03500418Z (W/O Fuse)	32V 5-Position Panel-Mount Vertical-Terminal Fuse Block - Bulk	15 AMPS	ATO FUSE	VERTICAL CONTACTS MOUNT	32V DC
03500420Z (W/O Fuse)	32V 5-Position PCB-Terminal Fuse Block - Bulk	15 AMPS	ATO FUSE	PCB MOUNT	32V DC