

Note: In the process of enhancing our systems, we are transitioning data to a new PiQ data view. This data is being verified with the "Historical" view for accuracy. Once the data is confirmed, the "Historical" view will be discontinued. During this transition, you may encounter duplicate entries or missing/outdated data. For queries during this interim period, please visit our [Historical View FAQs](#) or contact our [Customer Service](#).

## Cartridge Fuses, Nonrenewable Certified for Canada

**COMPANY**

**LITTELFUSE INC**

8755 W Higgins Rd, Suite 500  
Chicago, IL 60631 United States

E81895

**Nonrenewable cartridge fuses**

Class	Cat. No.+	Interrupting Capacity		Fuse Rating	
		V ac	RMS	V ac	Amps
H	NLKP	250Vac	10,000	250Vac	15 - 60

**Nonrenewable cartridge fuses: current-limiting**

Class	Cat. No.+	Interrupting Capacity		Fuse Rating	
		V ac	RMS	V ac	Amps
CC	542	600Vac	200,000	600Vac	0 - 30
T	JLLN, 558	300Vac	200,000	300Vac	0 - 600
		300Vac	200,000	300Vac	800 - 1200
		160Vdc	50,000	160Vdc	0 - 30
		160Vdc	20,000	160Vdc	35 - 60
		125Vdc	20,000	125Vdc	70 - 1200
T	JLLS, 559	600Vac	200,000	600Vac	0 - 1200
T	JLLT, 579	300Vac	200,000	300Vac	0 - 600
		300Vac	200,000	300Vac	800 - 1200
J	JLS	600Vac	200,000	600Vac	0 - 600
CC	KLKR	600Vac	200,000	600Vac	0 - 30
RK1	KLNR, 548	250Vac	200,000	250Vac	0 - 600
RK1	KLSR, 549	600Vac	200,000	600Vac	0 - 600
K5	NLN	250Vac	50,000	250Vac	0 - 600
		250Vdc	20,000	250Vdc	0 - 60

		250Vdc	50,000	250Vdc	70 - 600
K5	<b>NLS</b>	600Vac	50,000	600Vac	0 - 600
		600Vdc	20,000	600Vdc	0 - 7
		500Vdc	20,000	500Vdc	8 - 30
		400Vdc	20,000	400Vdc	35 - 60
		600Vdc	50,000	600Vdc	65 - 200
		500Vdc	50,000	500Vdc	225 - 600

**Nonrenewable cartridge fuses: time delay, current-limiting**

Class	Cat. No. +	Interrupting Capacity		Fuse Rating	
		V ac	RMS	V ac	Amps
CC	<b>CCMR (CC)</b>	600Vac	200,000	600Vac	0.1 - 30
		500Vdc	20,000	500Vdc	6 - 30
CD	<b>CCMR (CD)</b>	600Vac	200,000	600Vac	35 - 60
RK5	<b>DCSR</b>	600Vac	200,000	600Vac	30
		600Vdc	20,000	600Vdc	30
H	<b>FLN</b>	250Vac	10,000	250Vac	0 - 600
		125Vdc	10,000	125Vdc	0 - 600
RK5	<b>FLNR</b>	250Vac	200,000	250Vac	0 - 600
		125Vdc	20,000	125Vdc	0 - 600
RK5	<b>FLNRxxxID (xxx=amp. rating)</b>	250Vac	200,000	250Vac	35 - 600
		125Vdc	20,000	125Vdc	35 - 600
H	<b>FLS</b>	600Vac	10,000	600Vac	0 - 600
RK5	<b>FLSR</b>	600Vac	200,000	600Vac	0 - 600
		300Vdc	20,000	300Vdc	0 - 600
RK5	<b>FLSRxxxxID (xxxx=amp. rating)</b>	600Vac	200,000	600Vac	0 - 600
		300Vdc	20,000	300Vdc	0 - 600
J	<b>JTD</b>	600Vac	200,000	600Vac	0 - 600
J	<b>JTD-ID</b>	600Vac	200,000	600Vac	0 - 600
CC	<b>KLDR</b>	600Vac	200,000	600Vac	0.1 - 30
L	<b>LDC</b>	600Vac	200,000	600Vac	601 - 2000
		600Vdc	50,000	600Vdc	601 - 2000
RK1	<b>LLNRK</b>	250Vac	200,000	250Vac	0 - 600
RK1	<b>LLSRK</b>	600Vac	200,000	600Vac	0 - 600
RK1	<b>LLSRKxxID (xx=amp rating)</b>	600Vac	200,000	600Vac	0 - 12

		600Vac	200,000	600Vac	15 - 60
		600Vac	200,000	600Vac	225 - 400
		600Vac	200,000	600Vac	450 - 500
		600Vac	200,000	600Vac	600
H	<b>NLKP</b>	250Vac	10,000	250Vac	15 - 60
		125Vdc	10,000	125Vdc	15 - 60
G	<b>SLC</b>	600Vac	100,000	600Vac	0 - 20
		480Vac	100,000	480Vac	21 - 60
		170Vdc	10,000	170Vdc	0 - 60

+ - Type numbers include suffix digits indicating ampere rating

Last Updated on 2023-09-21

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2024 UL LLC."