


DCNLM Series

60V DC MAX Contactor Relays

OBSOLETE: June, 2025



Specifications

Max Voltage Rating (V DC):	60
Current Rating Continuous (A):	50, 100, 200, 400
Coil Voltage Rating (V DC):	12, 24, 48, 60
Ingress Protection:	IP 40
Operating Temperature (°C):	-40°C to +70°C
Approvals:	400A have CCC and are UL Recognized UL File No. E47258

Applications

- Communication Power Supplies
- UPS

Features and Benefits

- Available with up to 400A contact switching capability
- Main contacts are rated for 48V (typical) and 60V (max)
- Coil voltage options include 12V, 24V, 48V, and 60V
- Available in single-coil and double-coil configurations
- Normally open, monostable relay design
- Non-polarized main contacts

Description


The DCNLM Series 48V High-Current DC Contactor Relay is available up to 400A contact switching capability as well as multiple coil voltage options to suit a wide variety of stationary applications, including use in electrical control systems for communication power supplies, industrial machines, and uninterruptible power supplies (UPS).

The DCNLM normally open, high-current DC contactor features 48V non-polarized main contacts and is available in single-coil and double-coil configurations.


Web Resources

Download 2D print, installation guide and technical resources at: littelfuse.com/DCNLM

Electrical Diagram



DCNLM100NBxx-01
DCNLM200NB12xx
DCNLM400NB12
DCNLM400NB24-01
DCNLM400NB48-01



DCNLM50NBxx
DCNLM100NBxx
DCNLM200NBxx-01
DCNLM200NB24-02
DCNLM400NBxx

DCNLM Series

60V DC MAX Contactor Relays

Ordering Information

PART NUMBER	CONTINUOUS CURRENT (A)	VOLTAGE RATING		MOUNTING	COIL VOLTAGE (V DC)	COIL TYPE	AUX CONTACT	POLARIZED	2D PRINT
		SYSTEM NOMINAL (V DC)	MAX VOLTAGE (V DC)						
DCNLM50NB12	50	48	60	SIDE MOUNT	12	Single	No	No	↓
DCNLM50NB24	50	48	60	SIDE MOUNT	24	Single	No	No	↓
DCNLM50NB48	50	48	60	SIDE MOUNT	48	Single	No	No	↓
DCNLM50NB60	50	48	60	SIDE MOUNT	60	Single	No	No	↓
DCNLM100NB12-01	100	48	60	SIDE MOUNT	12	Dual	No	No	↓
DCNLM100NB24-01	100	48	60	SIDE MOUNT	24	Dual	No	No	↓
DCNLM100NB48-01	100	48	60	SIDE MOUNT	48	Dual	No	No	↓
DCNLM100NB12	100	48	60	SIDE MOUNT	12	Single	No	No	↓
DCNLM100NB24	100	48	60	SIDE MOUNT	24	Single	No	No	↓
DCNLM100NB48	100	48	60	SIDE MOUNT	48	Single	No	No	↓
DCNLM200NB12	200	48	60	SIDE MOUNT	12	Dual	No	No	↓
DCNLM200NB24	200	48	60	SIDE MOUNT	24	Dual	No	No	↓
DCNLM200NB48	200	48	60	SIDE MOUNT	48	Dual	No	No	↓
DCNLM200NB12-01	200	48	60	SIDE MOUNT	12	Single	No	No	↓
DCNLM200NB24-01	200	48	60	SIDE MOUNT	24	Single	No	No	↓
DCNLM200NB24-02	200	48	60	TOP MOUNT	24	Single	No	No	↓
DCNLM200NB48-01	200	48	60	SIDE MOUNT	48	Single	No	No	↓
DCNLM400NB12	400	48	60	SIDE MOUNT	12	Dual	No	No	↓
DCNLM400NB24	400	48	60	SIDE MOUNT	24	Single	No	No	↓
DCNLM400NB48	400	48	60	SIDE MOUNT	48	Single	No	No	↓
DCNLM400NB24-01	400	48	60	SIDE MOUNT	24	Dual	No	No	↓
DCNLM400NB48-01	400	48	60	SIDE MOUNT	48	Dual	No	No	↓


Performance Data

MAIN CONTACT			LIFE							
Contact Arrangement	SPST NO		Electrical Life					6000 Cycles		
Rated Operating Voltage	48V DC		Mechanical Life					100,000		
Max Short Circuit Current	DCNLM50	200A @ 48V DC	PART NUMBER	COIL VOLTAGE (V DC)	COIL TYPE	PICKUP VOLTAGE @ 25°C (V DC MAX)	DROPOUT VOLTAGE @ 25°C (V DC MIN)	HOLD CURRENT (A)	COIL WATTS @ 25°C (W)	
	DCNLM100	400A @ 48V DC							Start Up	Hold
	DCNLM200	800A @ 48V DC								
	DCNLM400	1600A @ 48V DC								
Dielectric Withstand Voltage	1000V AC		DCNLM50NB12	12	Single	8.4	1	0.71	9	-
Insulation Resistance	≥50MΩ @ 500V DC		DCNLM50NB24	24	Single	16.8	2	0.35	9	-
Max Voltage Drop	DCNLM50	≤50mV @ 50 A	DCNLM50NB48	48	Single	33.6	4	0.18	9	-
	DCNLM100	≤80mV @ 100 A	DCNLM50NB60	60	Single	42	5	0.13	9	-
	DCNLM200, 400	≤50mV @ 100A	DCNLM100NB12-01	12	Dual	8.4	1	0.75	150	9
OPERATE / RELEASE TIME			DCNLM100NB24-01	24	Dual	16.8	2	0.35	150	9
Close (ms)	DCNLM50	40	DCNLM100NB48-01	48	Dual	33.6	4	0.15	150	9
	DCNLM100	30	DCNLM100NB12	12	Single	8.4	1	0.48	6	-
	DCNLM200	50	DCNLM100NB24	24	Single	16.8	2	0.2	6	-
	DCNLM400	50	DCNLM100NB48	48	Single	33.6	4	0.08	6	-
Release (ms)	DCNLM50	20	DCNLM200NB12	12	Dual	8.4	1	0.7	180	8.5
	DCNLM100	30	DCNLM200NB24	24	Dual	16.8	2	0.37	170	9
	DCNLM200	25	DCNLM200NB48	48	Dual	33.6	4	0.15	180	8
	DCNLM400	25	DCNLM200NB12-01	12	Single	8.4	1	0.84	10	-
ENVIRONMENTAL DATA			DCNLM200NB24-01	24	Single	16.8	2	0.4	10	-
Shock	DCNLM50NB DVP 50G, 6ms		DCNLM200NB48-01	48	Single	33.6	4	0.21	10.5	-
Vibration	1~50Hz (freq.1~10Hz, amp;.25/f ² ; freq.10~50Hz, ampl.250/f ²)		DCNLM200NB24-02	24	Single	16.8	2	0.4	10	-
Operating Ambient Temperature	-40°C~+70°C		DCNLM400NB24	24	Single	16.8	2	0.39	10	-
Weight (g)	DCNLM50	157	DCNLM400NB48	48	Single	33.6	4	0.24	11.5	-
	DCNLM100NBxx	283	DCNLM400NB12	12	Dual	8.4	1	0.77	80	9.5
	DCNLM100NBxx-01	193.3	DCNLM400NB24-01	24	Dual	16.8	2	0.45	175	11
	DCNLM200NBxx	445.1	DCNLM400NB48-01	48	Dual	33.6	4	0.1	154	5
	DCNLM200NBxx-0x	439								
	DCNLM400NBxx	866								
DCNLM400NBxx-01	888									

DCNLM Series

60V DC MAX Contactor Relays

Part Number System



MAIN CONTACTS POLARIZATION AND AUX CONTACT		
POLARIZED?		INCLUDE AUX CONTACT?
N:	No	No

MAIN CONTACTS VOLTAGE RATING		
B:	48	V DC

COIL VOLTAGE		
12:	12	V DC
24:	24	V DC
48:	48	V DC
60:	60	V DC

OBSOLETE

DCNLM Series

60V DC MAX Contactor Relays

Application Notes & Definitions

- Be sure to use a washer to prevent screws from loosening. Tighten the screw so that the torque is in the range specified below. Exceeding the maximum torque can lead to product rupture. See chart below.
- Please refer to the drawing for connection polarity.
- Do not use dropped products.
- Avoid installing the product in a strong magnetic field (Close to the transformer or magnet), or near an object with heat radiation.
- Electrical life
Please use under load capability and life cycle so as not to cause a function failure. (Please also treat the contactor as a product with specified life and replace it when necessary). It is possible to make parts burn around the contactor once operating failure happens. So it is necessary to take layout into account to make sure power shall be cut off within 1 second.
- Do not let particle and oil stain on the main terminal with which the load shall make a reliable contact or it will cause a lot of heat.

PRODUCT SERIES	PRODUCT MODEL	CONTACT TERMINAL		COIL TERMINAL		MOUNTING	
		HOLE OR BOLT	REFERENCE TORQUE	HOLE/BOLT/WIRE/TERMINAL	REFERENCE TORQUE	REFERENCE TORQUE	REFERENCE BOLT SIZE
DCNLM50NB	DCNLM50NB12	Bolt : M5	4~5N.m	Bolt : M4	1.7~2.5N.m	1.7~2.5N.m	M4
	DCNLM50NB24						
	DCNLM50NB48						
	DCNLM50NB60						
DCNLM100NB	DCNLM100NB12	Bolt : M6	4~6N.m	Bolt : M4	1.7~2.5N.m	1.7~2.5N.m	M4
	DCNLM100NB24						
	DCNLM100NB48						
	DCNLM100NB12-01						
	DCNLM100NB24-01						
DCNLM100NB48-01							
DCNLM200NB	DCNLM200NB12	Bolt : M8	9~11N.m	Bolt : M4	1.7~2.5N.m	4~5N.m	M5
	DCNLM200NB24						
	DCNLM200NB48						
	DCNLM200NB12-01						
	DCNLM200NB24-01						
	DCNLM200NB48-01						
DCNLM200NB24-02	Bolt : M8	9~11N.m	Wire	-	4~5N.m	M5	
DCNLM400NB	DCNLM400NB24	Bolt : M10	15~18N.m	Bolt : M4	1.7~2.5N.m	6~8N.m	M6
	DCNLM400NB48						
	DCNLM400NB12						
	DCNLM400NB24-01						