






REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	GCF#524592 INITIAL RELEASE	SEP./23/2021	D. ZHANG




NAME PLATE

TABLE 1: TECHNICAL PARAMETERS				
ITEM		PARAMETER		
		DCNLB200NB24	DCNLB200NB48	DCNLB200NB60
HOLD POWER	START POWER	MAX 15W		
	MAINTAIN POWER	MAX 15W		
MAXIMUM CONTACT VOLTAGE		60V DC		
RATED CONTACT VOLTAGE		48V DC		
RATED CONTACT CURRENT		200A		
RATED COIL VOLTAGE		24V DC	48V DC	60V DC
OPERATING VOLTAGE IN COLD STATE @ (20±5)°C	PICKUP	17V DC MAX	34V DC MAX	42V DC MAX
	RELEASE	2V DC MIN	4V DC MIN	5V DC MIN
OPERATE TIME		MAX 50ms		
RELEASE TIME		MAX 50ms		
BOUNCE TIME		MAX 12ms		
CONTACT VOLTAGE DROP		≤50mV@100 A		
LIMIT BREAKING ABILITY		4le/5ms,1CYCLES		
DIELECTRIC STRENGTH		1000V AC, 50Hz,1min., LEAKAGE CURRENT ≤1 mA		
INSULATION RESISTANCE		≥50MΩ@500VDC		
ELECTRIC LIFE		3000 CYCLES		
MECHANICAL LIFE		100,000 CYCLES		
WORKING DUTY		CONTINUOUS		

●TABLE 2 OPERATING VOLTAGE PARAMETER				
NO.	PN	NAME PLATE		REMARK
		"A" OF NAME PLATE	"B" OF NAME PLATE	
1	DCNLB200NB24	DCNLB200NB24	Rated Coil Voltage:24V DC	
2	DCNLB200NB48	DCNLB200NB48	Rated Coil Voltage:48V DC	
3	DCNLB200NB60	DCNLB200NB60	Rated Coil Voltage:60V DC	

- NOTES:
- ALL SIZES ARE FOR REFERENCE ONLY.
 - SEE TABLE 2 FOR CONFIGURATION OF NAME PLATE, OPERTING VOLTAGE AND PNs.
 - MATERIALS AND FINISHING:
 - 1 BASE: THERMOSETTING PLASTIC, UL94V-0.
 - 2 CONTACTS: SILVER ALLOY.
 - 3 COIL STUD: COPPER ALLY, SILVER PLATED.
 - PRODUCT TECHNICAL PARAMETERS: SEE TABLE 1.
 - 4.1 CONTACT ARRANGEMENT: SPST-NC.
 - 4.2 CONNECTION STUD: M8 STUD, RECOMMENDED TORQUE 9 N•m ~ 11 N•m; M4 STUD, RECOMMENDED TORQUE 1.7 N•m ~ 2.5 N•m.
 - 4.3 MOUNTING: M5 BOLT, RECOMMENDED TORQUE 4 N•m ~ 5 N•m.

CIRCUIT SCHEMATIC DIAGRAM



DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.				
PER CHNPD20-0008 PROCEDURE		FIT/ FUNCTION CRITICAL CHARACTERISTICS		
	<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL		
	CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE		
		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
	CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		
NAME		DATE		 Expertise Applied Answers Delivered
DRAWN JY_SHI		SEP./8/2021		
CHECKED J. LI		SEP./15/2021		
-		-		
FORM NO.: CVP-PE40-0005 REV B		TITLE		
THIRD ANGLE PROJECTION		DCNLB 200A 48V CONTACTOR		
		SIZE C	DWG. NO. OUTLINE OL-DCNLB200NB.CHART	REV. A
DO NOT SCALE DRAWING		SCALE 1:1		SHEET 1 OF 1