



DPS60C600HB

600 V, 2 x 30 A Fast Recovery Diode

RoHS



Pinout Diagram (TO-247)



1, 3: Anode; **2:** Cathode; **Backside:** Cathode

Description

This 600 V, 2 x 30 A general-purpose, fast recovery power diode features two chips with common cathode configuration in a TO-247 package.

Features

- Reverse leakage current, $I_R \leq 100 \mu\text{A}$ @ 25 °C
- Low thermal resistance, $R_{th(j-c)} = 0.45 \text{ K/W}$
- Planar passivated chips

Benefits

- Stable long-term reliability
- Higher current-handling capability
- Low standby losses
- High efficiency in switching

Applications

- Anti-parallel diode in high-frequency switching devices
- Snubber circuits
- Free wheeling diode in inverter stage
- Rectifiers in Switch Mode Power Supplies (SMPS)
- Uninterruptible Power Supplies (UPS)

Package

- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0

Product Summary

Characteristic	Value	Unit
V_{RRM}	600	V
$I_{F(AV)}$	60	A
$t_{rr} @ I_F = 1 \text{ A}$	38	ns

Maximum Ratings

Symbol	Characteristics	Condition	Value	Units
V_{RRM}	Repetitive Peak Reverse Voltage	$T_{vj} = 25\text{ }^{\circ}\text{C}$	600	V
$I_{F(AV)}$	Average Forward Current	$T_c = 130\text{ }^{\circ}\text{C}$, $T_{vj} = 150\text{ }^{\circ}\text{C}$, rectangular, $d = 0.5$	30	A
I_{FSM}	Non-repetitive Forward Surge Current	$t_p = 10\text{ ms}$, (50 Hz), half sine wave, $V_R = 0\text{ V}$	450	A
P_{tot}	Total Power Dissipation	$T_c = 25\text{ }^{\circ}\text{C}$	300	W
T_{vj}	Virtual Junction Temperature Range	–	–55 to +150	$^{\circ}\text{C}$
T_{stg}	Storage Temperature Range	–	–55 to +150	$^{\circ}\text{C}$

Electrical Characteristics – Static

Symbol	Characteristics	Conditions	Value			Units
			Min.	Typ.	Max.	
I_R	Reverse Current	$V_R = 600\text{ V}$, $T_{vj} = 25\text{ }^{\circ}\text{C}$	–	–	10	μA
		$V_R = 600\text{ V}$, $T_{vj} = 150\text{ }^{\circ}\text{C}$	–	–	5	mA
V_F	Forward Voltage	$I_F = 30\text{ A}$, $T_{vj} = 25\text{ }^{\circ}\text{C}$	–	1.35	1.45	V
		$I_F = 60\text{ A}$, $T_{vj} = 25\text{ }^{\circ}\text{C}$	–	–	1.68	
		$I_F = 30\text{ A}$, $T_{vj} = 150\text{ }^{\circ}\text{C}$	–	1.18	1.25	
		$I_F = 60\text{ A}$, $T_{vj} = 150\text{ }^{\circ}\text{C}$	–	–	1.35	
$V_{(TO)}$	Threshold Voltage	$T_{vj} = 150\text{ }^{\circ}\text{C}$	–	–	0.58	V
r_T	Slope Resistance	$T_{vj} = 150\text{ }^{\circ}\text{C}$	–	–	13.3	m Ω

Electrical Characteristics – Dynamic ($T_{vj} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

Symbol	Characteristics	Conditions	Value			Units
			Min.	Typ.	Max.	
C_j	Junction Capacitance	$V_R = 600\text{ V}$, $f = 1\text{ MHz}$	–	37	–	pF
t_{rr}	Reverse Recovery Time	$I_F = 1\text{ A}$, $V_R = 30\text{ V}$, $-di_F/dt = 200\text{ A}/\mu\text{s}$	–	38	–	ns
		$I_F = 30\text{ A}$, $V_R = 350\text{ V}$, $-di_F/dt = 200\text{ A}/\mu\text{s}$	–	120	–	
I_{RRM}	Peak Reverse Recovery Current	$I_F = 30\text{ A}$, $V_R = 350\text{ V}$, $-di_F/dt = 200\text{ A}/\mu\text{s}$	–	5.1	–	A

Thermal Specifications

Symbol	Characteristics	Value			Units
		Min.	Typ.	Max.	
$R_{th(j-c)}$	Thermal Resistance, Junction to Case	–	–	0.45	K/W

Package TO-247-2L

Symbol	Characteristics	Conditions	Value			Units
			Min.	Typ.	Max.	
M_s	Mounting Torque	–	0.8	–	1.2	Nm
F	Mounting Force	–	20	–	120	N
G	Weight	–	–	6	–	g
T_{op}	Operating Temperature Range	–	–55	–	+125	$^{\circ}\text{C}$

Characteristic Curves

Fig. 1. Typical Forward Characteristics




Fig. 2. Typical Reverse Recovery Charge vs. Diode Current Slope




Fig. 3. Typical Reverse Recovery Current vs. Diode Current Slope




Fig. 4. Typical Reverse Recovery Time vs. Diode Current Slope





Fig. 5. Typical Forward Voltage V_{fr} and t_{fr} vs $-di_F/dt$ 

Fig. 6. Typical Transient Thermal Impedance, Junction to Case



Part Outline Drawing (TO-247-3L)




Symbol	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	4.70	5.30	0.185	0.209
A1	2.21	2.59	0.087	0.102
A2	1.50	2.49	0.059	0.098
b	0.99	1.40	0.039	0.055
b2	1.65	2.39	0.065	0.094
b4	2.59	3.43	0.102	0.135
C	0.38	0.89	0.015	0.035
D	20.79	21.45	0.819	0.845
D1	13.07	–	0.515	–
D2	0.51	1.35	0.020	0.053
e	5.45 BSC		0.215 BSC	
E	15.48	16.24	0.610	0.640
E1	13.45	–	0.530	–
E2	4.31	5.48	0.170	0.216
L	19.80	20.30	0.780	0.800
L1	–	4.49	–	0.177
Q	5.38	6.19	0.212	0.244
S	6.14 BSC		0.242 BSC	
ØP	3.55	3.65	0.140	0.144
ØP1	–	7.39	–	0.29

Ordering Information

Part Number	Marking	Packing Mode
DPS60C600HB	DPS60C600HB	Tube (30 pcs)

Part Numbering and Marking



- D = Diode
- P = FRED
- S = Fast
- 60 = Current Rating (A)
- C = Common Cathode
- 600 = Voltage Rating (V)
- HB = Package (TO-247-3L)

Disclaimer Notice
Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.
Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

