


# DE150-501N04A


## RF Power MOSFET

### Key Attributes

Characteristic	Rating	Unit
$V_{DSS}$	500	V
$R_{DS(on)}$	$\leq 1.5$	$\Omega$
$I_{D25}$	4.5	A
$P_{tot}$	135	W



### Pinout Diagram (DE150)



$S_{G1}$ ,  $S_{G2}$ : Gate side source pins

$S_{D1}$ ,  $S_{D2}$ : Drain side source pins

### Description



The DE150-501N04A is a 500V, N-channel, enhancement mode MOSFET fabricated with Littelfuse's advanced low  $Q_g$  process.

With high input impedance and a low maximum on-resistance of  $1.5\Omega$ , the DE150-501N04A offers high power output in a small package with low input drive requirements. Low input capacitance and low gate charge enable operation at full power up to  $> 100$  MHz.

The DE150-501N04A is available in a flat, 6-lead SMD power package that incorporates an electrically isolated bottom side pad that enables efficient heat sinking.

### Features

- 500V breakdown voltage
- $1.5\Omega$  maximum on-resistance
- $V_{GS}$ : 2.5V to 4V
- $T_{vj(max)}$ : 125 °C
- High input impedance
- Electrically isolated substrate
  - High isolation voltage ( $> 2500$ V)
  - Excellent thermal transfer
  - Increased temperature and power
- Littelfuse advanced low  $Q_g$  process
- Low gate charge and capacitances
  - Easier to drive
  - Faster switching
- Very low insertion inductance ( $< 2$  nH)

### Benefits

- High speed switching at frequencies up to  $> 100$  MHz
- Easy to mount - no insulators needed
- High power density

### Ordering Information

Part Number	Description
DE150-501N04A	6-lead SMD (40/Tube)

## Absolute Maximum Ratings

Characteristic	Symbol	Conditions	Value	Unit
Drain-source voltage	$V_{DSS}$	$T_{vj} = 25^{\circ}\text{C}$ to $125^{\circ}\text{C}$	500	V
Drain-gate voltage	$V_{DGR}$	$T_{vj} = 25^{\circ}\text{C}$ to $125^{\circ}\text{C}$ ; $R_{GS} = 1\text{ M}\Omega$	500	
Gate-source voltage:				
Continuous	$V_{GS}$	—	$\pm 20$	V
Transient	$V_{GSM}$		$\pm 30$	
Drain current:				
Continuous	$I_{D25}$	$T_c = 25^{\circ}\text{C}$	4.5	A
Pulse <sup>1</sup>	$I_{DM}$		27	
Repetitive avalanche current	$I_{AR}$		4.5	
Rate of rise of voltage	$dV/dt$	$I_S \leq I_{DM}$ , $di/dt \leq 100\text{ A}/\mu\text{s}$ , $V_{DD} \leq V_{DSS}$ , $T_{vj} \leq 125^{\circ}\text{C}$ , $R_G = 0.2\ \Omega$ (External)	3.5	V/ns
		$I_S = 0$	>200	
Power dissipation:				
Total	$P_{tot}$	$T_c = 25^{\circ}\text{C}$	135	W
Heat Sink	$P_{DHS}$ <sup>2</sup>		66	
Ambient	$P_{DAMB}$		2.3	
Operating temperature	$T_a$	—	0 to 100	$^{\circ}\text{C}$

<sup>1</sup> Pulse width limited by  $T_{vj(max)}$

<sup>2</sup> Derate  $4.4\text{ W}/^{\circ}\text{C}$  above  $25^{\circ}\text{C}$

Absolute Maximum Ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at conditions beyond those indicated in the operational sections of this data sheet is not implied.

## Thermal Resistance

Characteristic	Symbol	Conditions	Value	Unit
Junction-to-case	$R_{th(j-c)}$	—	0.74	K/W
Junction-to-heatsink	$R_{th(j-s)}$		1.5	

## Package Weight

Characteristic	Symbol	Conditions	Value	Unit
Weight (Typ.)	—	—	2	g

## Electrical Characteristics

Unless otherwise specified, device characteristics are at  $T_{vj}=25^{\circ}\text{C}$ . Typical values are characteristic of the device at  $T_{vj}=25^{\circ}\text{C}$  and are the result of engineering evaluations. They are provided for informational purposes only and are not part of the manufacturing testing requirements.


Parameter	Symbol	Conditions	Value			Unit
			Min	Typ	Max	
Drain-source breakdown voltage	$V_{DSS}$	$V_{GS}=0\text{V}, I_D=3\text{mA}$	500	—	—	V
Gate threshold voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=250\mu\text{A}$	2.5	3.4	4	V
Gate leakage current	$I_{GSS}$	$V_{GS}=\pm 20V_{DC}, V_{DS}=0$	—	—	$\pm 100$	nA
Drain-source leakage current	$I_{DSS}$	$V_{DS}=0.8V_{DSS}, V_{GS}=0, T_{vj}=25^{\circ}\text{C}$	—	—	25	$\mu\text{A}$
		$V_{DS}=0.8V_{DSS}, V_{GS}=0, T_{vj}=125^{\circ}\text{C}$	—	—	250	
Drain-source on-state resistance	$R_{DS(on)}$	$V_{GS}=15\text{V}, I_D=0.5I_{D25}$ , Pulse test: $T \leq 300\mu\text{s}, D \leq 2\%$	—	1.2	1.5	$\Omega$
Forward transconductance	$g_{fs}$	Pulse test: $V_{DS}=60\text{V}, I_D=0.5I_{D25}$	—	1.9	—	S
Temperatures:						
Maximum Virtual Junction Temp.	$T_{vj(max.)}$	—	—	—	125	$^{\circ}\text{C}$
Storage Temperature	$T_{stg}$	—	0	—	125	
Lead Temperature	$T_L$	1.6 mm (0.063 in) from case, $t \leq 10\text{s}$	—	300	—	
Gate resistance	$R_G$	—	—	—	5	$\Omega$
Capacitance:						
Input	$C_{iss}$	$V_{GS}=0\text{V}, V_{DS}=0.8V_{DSS(max.)}$ , $f=1\text{MHz}$	—	570	—	$\text{pF}$
Output	$C_{oss}$		—	75	—	
Reverse Transfer	$C_{rss}$		—	3	—	
Stray Inductance Back Metal to any Pin	$C_{stray}$	$f=1\text{MHz}$	—	16	—	$\text{pF}$
Switching speeds:						
Turn-on delay	$t_{d(on)}$	$V_{GS}=15\text{V}, V_{DS}=0.8V_{DSS}$ $I_D=0.5I_{DM}$ $R_G=0.2\Omega$ (External)	—	4	—	ns
Turn-on	$t_{on}$					
Turn-off delay	$t_{d(off)}$					
Turn-off	$t_{off}$					
Charge:						
Gate	$Q_{G(on)}$	$V_{GS}=10\text{V}, V_{DS}=0.5V_{DSS}$ , $I_D=0.5I_{D25}$ , $I_G=3\text{mA}$	—	14	—	nC
Gate-source	$Q_{GS}$		—	3.5	—	
Gate-drain	$Q_{GD}$		—	5.5	—	

## Source-Drain Diode


Parameter	Symbol	Conditions	Value			Unit
			Min	Typ	Max	
Continuous source current	$I_S$	$V_{GS}=0\text{V}$	—	—	4.5	A
Maximum pulsed source current	$I_{SM}$	Repetitive, Pulse width limited by $T_{vj(max.)}$	—	—	27	A
Forward voltage drop	$V_{SD}$	$I_F=I_S, V_{GS}=0\text{V}$ , Pulse test: $T \leq 300\mu\text{s}, D \leq 2\%$	—	—	1.4	V
Reverse recovery time	$t_{rr}$	—	—	900	—	ns

Performance Data


Typical Transfer Characteristics  
 $V_{DS} = 60\text{ V}$ ,  $PW = 20\ \mu\text{s}$




Typical Output Characteristics



Gate Charge vs. Gate-to-Source Voltage  
 $V_{DS} = 250\text{ V}$ ,  $I_D = 2.25\text{ A}$



$V_{DSr}$  Voltage vs. Capacitance





## Manufacturing Information

### Moisture Sensitivity



All plastic encapsulated semiconductor packages are susceptible to moisture ingress. Littelfuse classifies its plastic encapsulated devices for moisture sensitivity according to the latest version of the joint industry standard, **IPC/JEDEC J-STD-020**, in force at the time of product evaluation. We test all of our products to the maximum conditions set forth in the standard, and guarantee proper operation of our devices when handled according to the limitations and information in that standard as well as to any limitations set forth in the information or standards referenced below.

Failure to adhere to the warnings or limitations as established by the listed specifications could result in reduced product performance, reduction of operable life, and/or reduction of overall reliability.

This product carries a **Moisture Sensitivity Level (MSL)** classification as shown below, and should be handled according to the requirements of the latest version of the joint industry standard **IPC/JEDEC J-STD-033**.

Device	Moisture Sensitivity Level (MSL) Classification
DE150-501N04A	MSL 1

### ESD Sensitivity



This product is ESD Sensitive, and should be handled according to the industry standard **JESD-625**.

### Soldering Profile

Provided in the table below is the **IPC/JEDEC J-STD-020** Classification Temperature ( $T_c$ ) and the maximum dwell time the body temperature of these surface mount devices may be ( $T_c - 5$ )°C or greater. The Classification Temperature sets the Maximum Body Temperature allowed for these devices during reflow soldering processes.


Device	Classification Temperature ( $T_c$ )	Dwell Time ( $t_p$ )	Maximum Reflow Cycles
DE150-501N04A	260°C	30 seconds	3

### Board Wash

Littelfuse recommends the use of no-clean flux formulations. Board washing to reduce or remove flux residue following the solder reflow process is acceptable provided proper precautions are taken to prevent damage to the device. These precautions include but are not limited to: Using a low pressure wash and providing a follow up bake cycle sufficient to remove any moisture trapped within the device due to the washing process. Due to the variability of the wash parameters used to clean the board, determination of the bake temperature and duration necessary to remove the moisture trapped within the package is the responsibility of the user (assembler). Cleaning or drying methods that employ ultrasonic energy may damage the device and should not be used. Additionally, the device must not be exposed to halide flux or solvents.



Mechanical Dimensions



N/C – DCB metalized bottom heatsink.  
 2500 V<sub>RMS</sub> AC, 1 minute isolation to leads.  
 LEADS – Pre-full silver plated (1.5–4 μm).  
 BOTTOM SIDE OF DCB – Pre Ni plated (2–6 μm).

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <https://www.littelfuse.com/disclaimer-electronics>