

 ASSOCIATION CONNECTING ELECTRONICS INDUSTRIES®		Material Composition Declaration © Copyright 2005. IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.				This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility. Adobe Reader version 7.0.5 is required to complete this declaration.			
1752-2	1.1	IPC Web Site for Information on IPC-1752 Standard http://www.ipc.org/IPC-175x				Form Type * Distribute		Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Information	
Supplier Information									
Company Name *		Company Unique ID		Unique ID Authority		Response Date *		Response Document ID	
Littelfuse, Inc.						2019-06-03			
Contact Name *		Title - Contact		Phone - Contact *		Email - Contact *			
Lya C. Latoza		Global EHS Analyst		+63-43-4300100		EnvRequests@littelfuse.com			
Authorized Representative *		Title - Representative		Phone - Representative *		Email - Representative *		Supplier Comments or URL for Additional Information	
Jennilyn D. Santos		Global EHS Supervisor		+63-43-4300100		EnvRequests@littelfuse.com			
Requester Item Number		Mfr Item Number		Mfr Item Name		Effective Date		Version	
						2005-03-08		China	
0219.040MXAESP				FUSE 250V 5X20 PT EBC SLE				Weight *	
Alternate Recommendation								1.31285	
								UOM	
								g	
								Unit Type	
								Each	
Manufacturing Process Information									
Terminal Plating / Grid Array Material				Terminal Base Alloy		J-STD-020 MSL Rating		Peak Process Body Temperature	
Nickel (Ni)				CU Alloy		Not Applicable		C	
Comments								seconds	
								Number of Reflow Cycles	
								Not Applicable	
Reflow soldering is not recommended. Compliant to RoHS Directive (EU) 2015-863.									

Save the fields in this form to a file

Export Data

Import fields from a file into this form

Import Data

Locked

RoHS Material Composition Declaration

RoHS Directive 2002/95/EC

RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material for Cadmium

Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2002/95/EC and implemented by the laws of the European Union member states) of the part identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a "RoHS restricted substance") in excess of the applicable quantity limit identified above. If a homogeneous material within the part contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Supplier's Standard Terms and Conditions of Sale applicable to such part shall apply.

RoHS Declaration *

1 - Item(s) does not contain RoHS restricted substances per the definition above

Supplier Declaration

Supplier Acceptance * Accepted

Exemptions: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.

Declaration Signature

Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.

Supplier Digital Signature

Lya C. Latoza

DNI es=Lya C. Latoza, o. ou. email=latoza@ltdifuse.com, cs=PH

Date: 2019.06.03 09:25:39 +06'00'

* Required Field

CAS Registry Number(R) is a Registered Trademark of the American Chemical Society

Form enabled by Adobe

Homogeneous Material Composition Declaration for Electronic Products

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Line Functions: +I Inserts a New Item /SubItem +M Inserts a new Material +C Inserts a new Substance Category +S Inserts a new Substance - Deletes the element line

Item/SubItem Name	Homogeneous Material	Unit of Measure	Level	Substance Category	Substance	CAS	Exempt	Weight	Unit of Measure	Tolerance		PPM
										-	+	
FUSE 250V 5X20 P	Cap base	0.28663g	Supplier	Copper	Copper	7440-50-8		0.180578	g			
			Supplier	Zinc	Zinc	7440-66-6		0.106054	g			
	Cap plating	0.006868g	B	Nickel (external applic	Nickel	7440-02-0		0.006868	g			
	Body	0.395 g	Supplier	Soda Lime Glass	Soda Lime Glass	65997-17-3		0.395	g			
	Solder	0.09 g	Supplier	Tin	Tin	7440-31-5		0.08685	g			
			Supplier	Copper	Copper	7440-50-8		0.00063	g			
			Supplier	Silver	Silver	7440-22-4		0.00027	g			
			Supplier	Flux	Rosin	8050-09-7		0.00225	g			
Element		0.00171 g	Supplier	Copper	Copper	7440-50-8		0.000855	g			
			Supplier	Silver	Silver	7440-22-4		0.000855	g			
	Cap Assy base	0.26191 g	Supplier	Copper	Copper	7440-50-8		0.17024	g			
			Supplier	Zinc	Zinc	7440-66-6		0.09167	g			
Cap plating		0.00855 g	B	Nickel (external applic	Nickel	7440-02-0		0.00855	g			
	Lead Assy base	0.23774 g	Supplier	Copper	Copper	7440-50-8		0.23774	g			
	Lead Assy platin	0.0146 g	Supplier	Tin	Tin	7440-31-5		0.0146	g			
	Yarn	0.00604 g	Supplier	Glass	Glass	65997-17-3		0.00604	g			
	Glue	0.0038 g	Supplier	Tetraethylene glycol	Tetraethylene glycol dii	109-17-1		0.0038	g			