



DPU60I1200HA

1200 V, 60 A Fast Recovery Diode

RoHS



Pinout Diagram TO-247-2L



1: Cathode; **3:** Anode; **Backside:** Cathode

Description

This 1200 V, 60 A general-purpose, fast recovery power diode features a single chip in a TO-247 package.

Features

- Reverse leakage current, $I_R \leq 100 \mu\text{A} @ 25^\circ\text{C}$
- Efficient heat transfer; $R_{th(j-c)}$ is 0.29 K/W
- Typical recovery time is 140 ns

Benefits

- Stable long-term reliability
- Higher current-handling capability
- Optimized for higher switching frequencies

Applications

- Power factor control
- Switch mode power supplies (SMPS)
- Maximum Power Point Tracking (MPPT) solar inverters

Package

- Industry standard outline
- Epoxy meets UL 94V-0
- RoHS compliant

Product Summary

Characteristic	Value	Unit
V_{RRM}	1200	V
$I_{F(AV)}$	60	A
$t_{rr} @ I_F = 1 \text{ A}$	45	ns

Maximum Ratings

Symbol	Characteristics	Condition	Value	Units
V_{RRM}	Repetitive Peak Reverse Voltage	$T_{vj} = 25\text{ }^{\circ}\text{C}$	1200	V
$I_{F(AV)}$	Average Forward Current	$T_c = 110\text{ }^{\circ}\text{C}$, $T_{vj} = 150\text{ }^{\circ}\text{C}$, rectangular, $d = 0.5$	60	A
I_{FSM}	Non-repetitive Surge Forward Current	$t_p = 10\text{ ms}$, (50 Hz), sine, $V_R = 0\text{ V}$, $T_{vj} = 45\text{ }^{\circ}\text{C}$	600	A
P_{tot}	Total Power Dissipation	$T_c = 25\text{ }^{\circ}\text{C}$	431	W
T_{vj}	Virtual Junction Temperature Range	–	–55 to +150	$^{\circ}\text{C}$
T_{stg}	Storage Temperature Range	–	–55 to +150	$^{\circ}\text{C}$

Electrical Characteristics – Static

Symbol	Characteristics	Conditions	Value			Units
			Min.	Typ.	Max.	
I_R	Reverse Current	$V_R = 1200\text{ V}$, $T_{vj} = 25\text{ }^{\circ}\text{C}$	–	–	100	μA
		$V_R = 1200\text{ V}$, $T_{vj} = 150\text{ }^{\circ}\text{C}$	–	–	1.5	mA
V_F	Forward Voltage	$I_F = 60\text{ A}$; $T_{vj} = 25\text{ }^{\circ}\text{C}$	–	1.9	2.4	V
		$I_F = 120\text{ A}$; $T_{vj} = 25\text{ }^{\circ}\text{C}$	–	–	2.65	
		$I_F = 60\text{ A}$; $T_{vj} = 150\text{ }^{\circ}\text{C}$	–	1.6	1.8	
		$I_F = 120\text{ A}$; $T_{vj} = 150\text{ }^{\circ}\text{C}$	–	–	2.3	
$V_{(TO)}$	Threshold Voltage	$T_{vj} = 150\text{ }^{\circ}\text{C}$	–	–	0.61	V
r_T	Slope Resistance	$T_{vj} = 150\text{ }^{\circ}\text{C}$	–	–	17.9	m Ω

Electrical Characteristics – Dynamic ($T_{vj} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

Symbol	Characteristics	Conditions	Value			Units
			Min.	Typ.	Max.	
C_j	Junction Capacitance	$V_R = 600\text{ V}$, $f = 1\text{ MHz}$	–	31	–	pF
t_{rr}	Reverse Recovery Time	$I_F = 1\text{ A}$, $V_R = 30\text{ V}$, $-di_F/dt = 200\text{ A}/\mu\text{s}$	–	45	–	ns
		$I_F = 60\text{ A}$, $V_R = 600\text{ V}$, $-di_F/dt = 200\text{ A}/\mu\text{s}$	–	140	–	
I_{RRM}	Peak Reverse Recovery Current	$I_F = 60\text{ A}$, $V_R = 600\text{ V}$, $-di_F/dt = 200\text{ A}/\mu\text{s}$	–	11	–	A

Thermal Specifications

Symbol	Characteristics	Value			Units
		Min.	Typ.	Max.	
$R_{th(j-c)}$	Thermal Resistance, Junction to Case	–	–	0.29	K/W

Package TO-247-2L

Symbol	Characteristics	Conditions	Value			Units
			Min.	Typ.	Max.	
I_{tRMS}	Terminal RMS Current	–	–	–	70	A
G	Weight	–	–	6	–	g
M_t	Mounting Torque for Terminal Screws	–	0.8	–	1.2	Nm
F	Mounting Force	–	20	–	120	N

Characteristic Curves

Fig. 1. Typical Forward Characteristics




Fig. 2. Typical Reverse Recovery Charge vs. Diode Current Slope




Fig. 3. Typical Reverse Recovery Current vs. Diode Current Slope




Fig. 4. Typical Reverse Recovery Time vs. Diode Current Slope





Fig. 5. Typical Forward Voltage V_{fr} and t_{fr} vs. $-di_F/dt$ 

Fig. 6. Typical Transient Thermal Impedance, Junction to Case



Part Outline Drawing TO-247-2L




Symbol	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	4.70	5.30	0.185	0.209
A1	2.21	2.59	0.087	0.102
A2	1.50	2.49	0.059	0.098
b	0.99	1.40	0.039	0.055
b2	1.65	2.39	0.065	0.094
b4	2.59	3.43	0.102	0.135
C	0.38	0.89	0.015	0.035
D	20.79	21.45	0.819	0.845
D1	13.07	—	0.515	—
D2	0.51	1.35	0.020	0.053
E	15.48	16.24	0.610	0.640
E1	13.45	—	0.530	—
E2	4.31	5.48	0.170	0.216
e	10.92 BSC		0.430 BSC	
L	19.80	20.30	0.780	0.800
L1	—	4.49	—	0.177
Q	5.38	6.19	0.212	0.244
S	6.14 BSC		0.242 BSC	
ØP	3.55	3.65	0.140	0.144
ØP1	—	7.39	—	0.29

Ordering Information

Part Number	Marking	Packing Mode
DPU60I1200HA	DPU60I1200HA	Tube (30 pcs)

Part Numbering and Marking



D	=	Diode
P	=	FRED
U	=	Ultra Fast
60	=	Current Rating (A)
I	=	Single Part Diode
1200	=	Voltage Rating (V)
HA	=	TO-247-AD (2 leads)

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

