


DS0404S2ARP

4 A Silicon Schottky Barrier Diode

RoHS

 **AUTOMOTIVE GRADE**

Description

These silicon Schottky Barrier Diodes are based on a metal-to-silicon junction principle in power rectifier design, resulting in a very low forward voltage drop and stable electrical performance. The devices are assembled in DO-214AA package, which is well suited for automated assembly processes. In addition, all devices are PPAP Level 3 compliant, supporting automotive qualification requirements.

Features

- Reverse leakage current $I_R \leq 0.4 \text{ mA @ } 25^\circ\text{C}$
- Forward voltage $V_F \leq 0.49 \text{ V @ } 4 \text{ A}$
- AEC-Q101 qualified
- Compact design in a DO-214AA package
- Maximum virtual junction temperature of 150°C
- PPAP capable


Benefits

- Reduces the PCB area and ideal for automated assembly
- Higher current in the same package
- High efficiency
- Low stand-by losses
- Ensures compliance with automotive industry standards

Applications

- Switch Mode Power Supplies (SMPS)
- Freewheeling diodes
- Reverse battery polarity protection
- DC-DC converter

Pinout Diagram (DO-214AA)



A: Anode; **K:** Cathode

Product Summary

Characteristic	Value	Unit
V_{RRM}	40	V
$I_{F(AV)}$	4	A

Maximum Ratings

Symbol	Characteristics	Conditions	Value	Units
V_{RRM}	Repetitive Peak Reverse Voltage	$T_{vj} = 25\text{ }^{\circ}\text{C}$	40	V
$I_{F(AV)}$	Average Forward Current	$T_L = 115\text{ }^{\circ}\text{C}$	4	A
I_{FSM}	Non-repetitive Surge Forward Current	Single half cycle; $f = 50\text{ Hz}$; $T_{vj}(\text{initial}) = 25\text{ }^{\circ}\text{C}$	200	A
		Single half cycle; $f = 60\text{ Hz}$; $T_{vj}(\text{initial}) = 25\text{ }^{\circ}\text{C}$	220	
T_{vj}	Virtual Junction Temperature Range	–	–65 to +150	$^{\circ}\text{C}$
T_{stg}	Storage Temperature Range	–	–65 to +150	$^{\circ}\text{C}$
I^2t	I^2t value	$t_p = 8.3\text{ ms}$, $T_{vj} = 25\text{ }^{\circ}\text{C}$	201	A^2S

Static Characteristics

Symbol	Characteristics	Conditions	Value			Units
			Min.	Typ.	Max.	
V_F	Forward Voltage	$I_F = 4\text{ A}$, $T_{vj} = 25\text{ }^{\circ}\text{C}$	–	–	0.49	V
I_R	Reverse Current	$V_R = V_{RRM}$	$T_{vj} = 25\text{ }^{\circ}\text{C}$		0.4	mA
			$T_{vj} = 125\text{ }^{\circ}\text{C}$		40	
$V_{(TO)}$	Threshold Voltage	$T_{vj} = 150\text{ }^{\circ}\text{C}$	–	–	0.22	V
r_T	Slope Resistance	$T_{vj} = 150\text{ }^{\circ}\text{C}$	–	–	38	$\text{m}\Omega$

Thermal Specifications

Symbol	Characteristics	Value	Unit
$R_{th(j-l)}$	Thermal Resistance, Junction to Lead	22	K/W
$R_{th(j-a)}$	Thermal Resistance, Junction to Ambient	80	K/W

Note: Mounted on a 1S1P 1" square FR-4 board, top layer pad size 2.0 mm * 2.2 mm & 2 oz 1" square copper plane

Characteristic Curves

Fig. 1. Typical Forward Characteristics




Fig. 2. Average Power Dissipation vs. Average Forward On-State Current (Typical)




Fig. 3. Maximum Allowable Lead Temperature vs. Average On-State Current




Fig. 4. Junction Capacitance vs. Reverse Voltage






Fig. 5. Typical Reverse Characteristics



Soldering Parameters

Characteristic		Value
Reflow Condition		Pb – free assembly
Pre-heat	Temperature Min ($T_{s(min)}$)	150 °C
	Temperature Max ($T_{s(max)}$)	200 °C
	Time (min to max) (t_s)	60 – 120 secs
Average ramp up rate (Liquidus Temp)(T_L) to peak		3 K/s max.
$T_{s(max)}$ to T_L - Ramp-up Rate		3 K/s max.
Reflow	Temperature (T_L) (Liquidus)	217 °C
	Time (t_L)	60 – 150 seconds
Peak Temperature (T_p)		260 ^{+0/-5} °C
Time within 5 °C of actual peak Temperature (t_p)		30 seconds max.
Ramp-down Rate		6 K/s max.
Time 25 °C to peak Temperature (T_p)		8 minutes max.
Do Not Exceed		260 °C





Physical Specifications

Characteristic	Value
Terminal Finish	100% Matte Tin-plated
Body Material	UL recognized compound meeting flammability rating V-0
Terminal Material	Copper Alloy


Packing Options

Part Number	Marking	Package	Packing Mode	Base Quantity
DS0404S2ARP	S404A	DO-214AA	Tape and Reel – 16 mm tape/ 13" reel	3000

Part Numbering and Marking




Package Dimensions DO-214AA



Symbol	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	1.950	2.200	0.077	0.086
B	4.060	4.570	0.160	0.180
C	3.300	3.940	0.130	0.155
D	2.130	2.440	0.084	0.096
E	0.760	1.520	0.030	0.060
F	–	0.203	–	0.008
G	5.210	5.590	0.205	0.220
H	0.152	0.305	0.006	0.012
I	2.260	–	0.089	–
J	2.160	–	0.085	–
K	–	2.740	–	0.107
L	2.160	–	0.085	–

Tape and Reel Specification



Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.

Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

