



DSA30C200PC

200 V, 30 A Schottky Rectifier Diode

RoHS



Pinout Diagram (TO-263AB)



C: Cathode; **A:** Anode; **tab:** Cathode

Features

- Extremely low switching losses
- Low I_{RM} values
- Very low V_F

Benefits

- Low voltage peaks for reduced protection circuits
- Low-noise switching
- High reliability circuit operation
- Improved thermal behavior
- Longer lifetime of the system

Applications

- Rectifiers in Switch Mode Power Supplies (SMPS)
- Free wheeling diode in low voltage converters

Package

- Terminals finish: 100% pure tin
- Epoxy meets UL 94V-0
- RoHS compliant

Product Summary

Characteristic	Value	Unit
V_{RRM}	200	V
$I_{F(AV)}$	2 x 15	A
V_F	0.78	V

Maximum Ratings ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)

Symbol	Characteristics	Condition	Max.	Units
V_{RRM}	Peak Repetitive Reverse Voltage	-	200	V
V_{RWM}	Working Peak Reverse Voltage			
V_R	DC Blocking Voltage			
$I_{F(AV)}$	Average Rectified Forward Current	50% duty cycle @ $T_c = 155\text{ }^{\circ}\text{C}$, rectangular wave form	15 (Per Leg)	A
			30 (Per Device)	
I_{FSM}	Peak One Cycle Non-Repetitive Surge Current (Per Leg)	10 ms, Half Sine pulse, $T_{vj} = 25\text{ }^{\circ}\text{C}$	300	A
P_{tot}	Total Power Dissipation	$T_c = 25\text{ }^{\circ}\text{C}$	85	W

Electrical Characteristics ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)

Symbol	Characteristics	Conditions	Typ.	Max.	Units
V_{F1}	Forward Voltage Drop (Per Leg) ¹	@ 15 A, Pulse, $T_{vj} = 25\text{ }^{\circ}\text{C}$	–	0.94	V
V_{F2}		@ 15 A, Pulse, $T_{vj} = 125\text{ }^{\circ}\text{C}$	–	0.78	V
I_{R1}	Reverse Current (Per Leg) ¹	@ $V_R = \text{rated } V_R$, $T_{vj} = 25\text{ }^{\circ}\text{C}$	–	250	μA
I_{R2}		@ $V_R = \text{rated } V_R$, $T_{vj} = 125\text{ }^{\circ}\text{C}$	–	2.5	mA
C_j	Junction Capacitance (Per Leg)	@ $V_R = 24\text{ V}$, $T_c = 25\text{ }^{\circ}\text{C}$ $f_{SIG} = 1\text{ MHz}$	100	–	pF

Note 1: Pulse width < 300 μs , duty cycle < 2%**Thermal-Mechanical Specifications**

Symbol	Characteristics	Condition	Specification	Units
T_{vj}	Virtual Junction Temperature Range	–	-55 to +175	$^{\circ}\text{C}$
T_{op}	Operating Temperature Range	–	-55 to +150	$^{\circ}\text{C}$
T_{stg}	Storage Temperature Range	–	-55 to +150	$^{\circ}\text{C}$
M_D	Mounting Torque	–	Min 0.4 Max 0.6	Nm
F_C	Mounting Force with Clip	–	Min 20 Max 60	N
$R_{th(j-c)}$	Maximum Thermal Resistance Junction to Case	DC operation	1.75	K/W
$R_{th(c-h)}$	Typical Thermal Resistance Case to Heat Sink	–	0.5	K/W
wt	Approximate Weight	–	2	g

Characteristic Curves

Fig. 1. Typical Forward Characteristics




Fig. 2. Typical Reverse Characteristics






Fig. 3. Typical Junction Capacitance




Part Outline Drawing (TO-263AB)



Symbol	Inches			Millimeters		
	Min.	Typical	Max.	Min.	Typical	Max.
A	0.16	–	0.19	4.06	–	4.83
A1	0	–	0.010	0	–	0.26
b	0.020	–	0.039	0.51	–	0.99
b1	0.045	–	0.070	1.14	–	1.78
c	0.012	–	0.029	0.31	–	0.74
c1	0.045	–	0.064	1.14	–	1.65
D	0.330	–	0.379	8.38	–	9.65
D1	0.251	–	–	6.40	–	–
E1	0.244	–	–	6.22	–	–
E2	0.379	–	0.420	9.65	–	10.67
e	0.100 BSC			2.54 BSC		
H	0.575	–	0.625	14.61	–	15.88
L	0.070	–	0.110	1.78	–	2.80
L1	–	–	0.066	–	–	1.68
L2	–	–	0.086	–	–	2.20
L3	0.010 BSC			0.255 BSC		
θ	0	–	8°	0	–	8°

Part Number and Marking




- D = Diode
- S = Schottky Diode
- A Low VF
- 30 = Forward Current (30A)
- C Common Cathode
- 200 = Reverse Voltage (200V)
- PC = Package Code (TO-263AB)
- YY = Year
- WW = Work Week
- S = Plant Location Code
- XXXXXX = Lot Number

Ordering Information

Part Number	Marking	Packing Mode	Quantity
DSA30C200PC-TRL	DSA30C200PC	Reel	800 pcs/ tube

Carrier Tape Specification (TO-263AB)



Symbol	Inches			Millimeters		
	Min.	Typical	Max.	Min.	Typical	Max.
A	0.421	–	0.429	10.70	–	10.90
B	0.631	–	0.639	16.03	–	16.23
C	0.201	–	0.209	5.11	–	5.31
d	0.057	–	0.065	1.45	–	1.65
E	0.065	–	0.07	1.65	–	1.85
F	0.449	–	0.457	11.40	–	11.60
P0	0.153	–	0.161	3.90	–	4.10
P	0.626	–	0.664	15.90	–	16.10
P1	0.075	–	0.082	1.90	–	2.10
W	0.941	–	0.957	23.90	–	24.30

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

