


IXSH65N120L3KHV

1200 V, 35 mΩ, 67 A SiC MOSFET

HF 

Features

- 3rd Generation SiC MOSFET Technology with -3.5/+15...18 V gate drive
- High blocking voltage with low on-state resistance
- High-speed switching with low capacitance
- 175 °C operating junction temperature capability
- Ultra-fast and robust intrinsic body diode
- Kelvin source contact



Applications

- Motor drives
- EV charging infrastructure
- DC/DC converter
- Switch mode power supplies
- Solar inverters

Product Summary

| Characteristic | Value | Unit |
|----------------------|-------|------|
| V_{DSS} | 1200 | V |
| $R_{DS(on)}$ | 35 | mΩ |
| $I_D @ 25\text{ °C}$ | 67 | A |

Pinout Diagram (TO-247-4L)



D: Drain; **G:** Gate; **KS:** Kelvin Source; **S:** Source

Maximum Ratings ($T_c = 25\text{ °C}$ unless otherwise specified)

| Symbol | Characteristic | Conditions | Value | Unit |
|------------|--|---|-------------|------|
| V_{DSS} | Drain-source voltage | $V_{GS} = 0\text{ V}, I_D = 100\text{ }\mu\text{A}$ | 1200 | V |
| V_{GSM} | Maximum gate-source voltage | Static (DC) | -5 to +20 | V |
| | Transient gate-source voltage | Pulse width < 200 ns, D < 1% | -10 to +23 | |
| I_D | Drain current (continuous) Fig.23 | $V_{GS} = 18\text{ V}, T_c = 25\text{ °C}$ | 67 | A |
| | | $V_{GS} = 18\text{ V}, T_c = 100\text{ °C}$ | 48 | A |
| I_{DM} | Peak drain current Fig. 25, 26 | Pulse width limited by SOA | 167 | A |
| I_{SM} | Diode pulsed forward current Fig. 25, 26 | Pulse width limited by SOA and dynamic $R_{th(j-c)}$ | 167 | A |
| P_{tot} | Total power dissipation Fig. 24 | $T_c = 25\text{ °C}$ | 288 | W |
| T_{vj} | Virtual junction temperature range | - | -55 to +175 | °C |
| T_{stg} | Storage temperature range | - | -55 to +175 | °C |
| T_{sold} | Soldering temperature | Wave soldering only allowed at leads, 1.6 mm from case for 10 s | 260 | °C |

Recommended Values

| Symbol | Characteristic | Value | | | Unit |
|-------------|------------------------------|-------|------|------|------|
| | | Min. | Typ. | Max. | |
| V_{GSon} | Recommended turn-on voltage | 15 | - | 18 | V |
| V_{GSoff} | Recommended turn-off voltage | -3.5 | - | -2 | |

Thermal Characteristics

| Symbol | Characteristic | Value | | | Unit |
|---------------|--|-------|------|------|------|
| | | Min. | Typ. | Max. | |
| $R_{th(j-c)}$ | Thermal resistance from junction to case Fig. 25 | - | 0.52 | - | K/W |

Electrical Characteristics – Static ($T_c = 25\text{ °C}$ unless otherwise specified)

| Symbol | Characteristic | Conditions | Value | | | Unit |
|--------------|--|--|-------|------|-----------|---------------|
| | | | Min. | Typ. | Max. | |
| I_{DSS} | Drain-source leakage current | $V_{DS} = 1200\text{ V}, V_{GS} = 0\text{ V}$ | - | 5 | 100 | μA |
| I_{GSS} | Gate leakage current | $V_{DS} = 0\text{ V}, V_{GS} = -5 \sim 20\text{ V}$ | - | - | ± 100 | nA |
| $V_{GS(th)}$ | Gate threshold voltage Fig. 8, 9 | $V_{GS} = V_{DS}, I_D = 8\text{ mA}$ | 2.0 | 2.8 | 4.0 | V |
| | | $V_{GS} = V_{DS}, I_D = 8\text{ mA}, T_{vj} = 175\text{ °C}$ | - | 2.0 | - | |
| $R_{DS(on)}$ | Drain-source on-state resistance Fig. 4, 5, 6, 7 | $V_{GS} = 18\text{ V}, I_D = 30\text{ A} @ T_{vj} = 25\text{ °C}$ | - | 35 | 46 | m Ω |
| | | $V_{GS} = 18\text{ V}, I_D = 30\text{ A} @ T_{vj} = 175\text{ °C}$ | - | 57 | - | |
| | | $V_{GS} = 15\text{ V}, I_D = 30\text{ A} @ T_{vj} = 25\text{ °C}$ | - | 45 | - | |
| | | $V_{GS} = 15\text{ V}, I_D = 30\text{ A} @ T_{vj} = 175\text{ °C}$ | - | 61 | - | |

Electrical Characteristics – Dynamic ($T_{vj} = 25\text{ °C}$ unless otherwise specified)

| Symbol | Characteristic | Conditions | Value | | | Unit | |
|--------------|---|--|--------------------------|------|-------|----------|---------------|
| | | | Min. | Typ. | Max. | | |
| C_{iss} | Input capacitance Fig. 16 | $V_{DS} = 800\text{ V}, V_{GS} = 0\text{ V},$ $f = 100\text{ kHz}, V_{AC} = 25\text{ mV}$ | – | 2082 | – | pF | |
| C_{oss} | Output capacitance Fig. 16 | | – | 95 | – | | |
| C_{rss} | Reverse transfer capacitance Fig. 16 | | – | 3 | – | | |
| E_{oss} | C_{oss} stored energy Fig. 17 | | – | 40 | – | | μJ |
| Q_G | Total gate charge Fig. 18 | $V_{DS} = 800\text{ V}, I_D = 30\text{ A},$ $V_{GS} = -3\text{ to }+18\text{ V}$ | – | 83 | – | nC | |
| Q_{GS} | Gate-source charge Fig. 18 | | – | 23.5 | – | | |
| Q_{GD} | Gate-drain charge Fig. 18 | | – | 21 | – | | |
| $R_{g(int)}$ | Gate input resistance | $f = 1\text{ MHz}$ | – | 2.5 | – | Ω | |
| E_{on} | Turn-on switching energy Fig. 19, 20 | $V_{DS} = 800\text{ V}, I_D = 40\text{ A},$ $V_{GS} = -3.5\text{ to }+18\text{ V},$ $R_{G(ext)} = 2.0\ \Omega, L = 200\ \mu\text{H}$ | $T_{vj} = 25\text{ °C}$ | – | 407.6 | – | μJ |
| | | | $T_{vj} = 175\text{ °C}$ | – | 631.1 | – | |
| E_{off} | Turn-off switching energy Fig. 19, 20, 22 | | $T_{vj} = 25\text{ °C}$ | – | 43.1 | – | μJ |
| | | | $T_{vj} = 175\text{ °C}$ | – | 52.5 | – | |
| $t_{d(on)}$ | Turn-on delay time Fig. 19, 20 | | $T_{vj} = 25\text{ °C}$ | – | 4.1 | – | ns |
| t_r | Rise time Fig. 19, 20 | | $T_{vj} = 25\text{ °C}$ | – | 13.9 | – | |
| $t_{d(off)}$ | Turn-off delay time Fig. 19, 20 | | $T_{vj} = 25\text{ °C}$ | – | 12.8 | – | |
| t_f | Fall time Fig. 19, 20 | | $T_{vj} = 25\text{ °C}$ | – | 6.4 | – | |

Reverse Diode Characteristics ($T_{vj} = 25\text{ °C}$ unless otherwise specified)

| Symbol | Characteristic | Conditions | Value | | | Unit |
|-----------|---------------------------------------|--|-------|-------|------|------|
| | | | Min. | Typ. | Max. | |
| V_{SD} | Diode forward voltage Fig. 10, 11, 12 | $I_{SD} = 30\text{ A}, V_{GS} = 0\text{ V}$ | – | 4.3 | – | V |
| | | $I_{SD} = 30\text{ A}, V_{GS} = 0\text{ V}, T_{vj} = 175\text{ °C}$ | – | 4.0 | – | V |
| I_s | Diode forward current (continuous) | $V_{GS} = -2\text{ V}, T_c = 25\text{ °C}$ | – | – | 57 | A |
| | | $V_{GS} = -2\text{ V}, T_c = 100\text{ °C}$ | – | – | 33 | |
| t_{rr} | Reverse recovery time | $V_{GS} = -3.5\text{ V}/+18\text{ V}, I_{SD} = 40\text{ A}, V_R = 800\text{ V},$ $R_{G(ext)} = 13.5\ \Omega, L = 200\ \mu\text{H}, di/dt = 3000\text{ A}/\mu\text{s}$ | – | 25.21 | – | ns |
| Q_{rr} | Reverse recovery charge | | – | 239.1 | – | nC |
| I_{rrm} | Peak reverse recovery current | | – | 25.1 | – | A |

Characteristic Curves









Fig. 7. $R_{DS(on)}$ vs. Temperature




Fig. 8. Transfer Curves




Fig. 9. Threshold Voltage vs. Temperature




Fig. 10. Body Diode Curves @ $T_{vj} = -55$ °C




Fig. 11. Body Diode Curves @ $T_{vj} = 25$ °C




Fig. 12. Body Diode Curves @ $T_{vj} = 175$ °C




Fig. 13. 3rd Quadrant Curves @ $T_{vj} = -55^\circ\text{C}$




Fig. 14. 3rd Quadrant Curves @ $T_{vj} = 25^\circ\text{C}$




Fig. 15. 3rd Quadrant Curves @ $T_{vj} = 175^\circ\text{C}$




Fig. 16. Capacitance vs. V_{DS}




Fig. 17. Output Capacitor Stored Energy




Fig. 18. Gate Charge Characteristics




Fig. 19. Switching Energy vs. $R_{G(ext)}$




Fig. 20. Switching Times vs. $R_{G(ext)}$




Fig. 21. Switching Energy vs. I_{DS}




Fig. 22. Switching Energy vs. Temperature




Fig. 23. Continuous Drain Current vs. Case Temperature




Fig. 24. Max. Power Dissipation Derating vs. Case Temperature




Fig. 25. Thermal Impedance





Fig. 26. Safe Operating Area



Part Number and Marking


IXSH65N120L3KHV = Device Part Number

YY = Year


WW = Work Week

Z = Assembly Location

XXXX = Lot Traceability



Part Outline Drawing (TO-247-4L)



Note:

1. Package reference: JEDEC TO247, Variation AD
- △ Slot required, notch may be rounded
- △ Dimension D&E do not include mold flash
4. Subject to change without notice

| Symbol | Inches | | | Millimeters | | |
|--------|------------|---------|-------|-------------|---------|-------|
| | Min. | Typical | Max. | Min. | Typical | Max. |
| A | 0.190 | - | 0.205 | 4.83 | - | 5.21 |
| A1 | 0.090 | - | 0.100 | 2.29 | - | 2.54 |
| A2 | 0.075 | - | 0.085 | 1.91 | - | 2.16 |
| b | 0.042 | - | 0.052 | 1.07 | - | 1.33 |
| b* | 0.042 | - | 0.050 | 1.07 | - | 1.28 |
| b1 | 0.094 | - | 0.116 | 2.39 | - | 2.94 |
| b2 | 0.094 | - | 0.112 | 2.39 | - | 2.84 |
| b3 | 0.042 | - | 0.063 | 1.07 | - | 1.60 |
| b4 | 0.042 | - | 0.059 | 1.07 | - | 1.50 |
| b5 | 0.094 | - | 0.106 | 2.39 | - | 2.69 |
| b6 | 0.094 | - | 0.104 | 2.39 | - | 2.64 |
| c | 0.022 | - | 0.027 | 0.55 | - | 0.68 |
| c1 | 0.022 | - | 0.026 | 0.55 | - | 0.65 |
| D | 0.917 | - | 0.929 | 23.30 | - | 23.60 |
| D1 | 0.640 | - | 0.695 | 16.25 | - | 17.65 |
| D2 | 0.037 | - | 0.049 | 0.95 | - | 1.25 |
| E | 0.620 | - | 0.635 | 15.75 | - | 16.13 |
| E1 | 0.516 | - | 0.557 | 13.10 | - | 14.15 |
| E2 | 0.145 | - | 0.201 | 3.68 | - | 5.10 |
| E3 | 0.039 | - | 0.075 | 1.00 | - | 1.90 |
| E4 | 0.487 | - | 0.529 | 12.38 | - | 13.43 |
| e | 0.100 BSC | | | 2.54 BSC | | |
| e1 | 0.200 BSC | | | 5.08 BSC | | |
| e2 | - | 0.500 | - | - | 12.70 | - |
| e3 | - | 0.330 | - | - | 8.38 | - |
| H1 | - | 0.200 | - | - | 5.08 | - |
| H2 | - | 0.100 | - | - | 2.54 | - |
| H3 | - | 0.100 | - | - | 2.54 | - |
| L | 0.681 | - | 0.702 | 17.31 | - | 17.82 |
| L1 | 0.156 | - | 0.172 | 3.97 | - | 4.37 |
| L2 | 0.093 | - | 0.104 | 2.35 | - | 2.65 |
| ØP | 0.138 | - | 0.144 | 3.51 | - | 3.65 |
| ØP1 | 0.283 REF. | | | 7.18 REF. | | |
| ØP2 | - | 0.088 | - | - | 2.24 | - |
| ØP3 | - | 0.067 | - | - | 1.70 | - |
| Q | 0.216 | - | 0.236 | 5.49 | - | 6.00 |
| S | 0.238 | - | 0.248 | 6.04 | - | 6.30 |

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

