


Dxx02 Series

2 A Rectifiers

RoHS

AUTOMOTIVE GRADE




Description

These silicon rectifiers have glass-passivated junctions, providing stable operation. They are assembled in a small-size SOD-123FL package which is ideal for automated assembly. All devices feature PPAP-3.

Features

- Reverse leakage current $I_R \leq 10 \mu\text{A}$ @ 25 °C
- Forward voltage $V_F \leq 1.1 \text{ V}$ @ 25 °C
- SOD-123FL package
- Increased maximum virtual junction temperature from 125 °C to 150 °C
- AEC-Q101 qualified

Pinout Diagram



A: Anode; **K:** Cathode

Benefits

- Low stand-by losses
- High efficiency
- Reduces the PCB area and ideal for automated assembly
- Higher current in the same package
- Ensures compliance with automotive industry standards

Applications

- Automotive reverse battery protection
- DC-DC converter
- Switch Mode Power Supplies (SMPS)

Product Summary

Characteristic	Value	Unit
V_{RRM}	600	V
$I_{F(AV)}$	2	A

Maximum Ratings

Symbol	Characteristics	Conditions	Value	Units
V_{RRM}	Repetitive Peak Reverse Voltage	$T_{vj} = 25\text{ °C}$	600	V
$I_{F(AV)}$	Average Forward Current	$T_c = 107\text{ °C}$	2	A
I_{FSM}	Non-repetitive Surge Forward Current	Single half cycle; $f = 50\text{ Hz}$; $T_{vj}(\text{initial}) = 25\text{ °C}$	42	A
		Single half cycle; $f = 60\text{ Hz}$; $T_{vj}(\text{initial}) = 25\text{ °C}$	50	A
I^2t	I^2t Value	$t_p = 8.3\text{ ms}$	10.4	A^2s
T_{vj}	Virtual Junction Temperature Range	–	–55 to +150	$^{\circ}C$
T_{stg}	Storage Temperature Range	–	–55 to +150	$^{\circ}C$

Electrical Characteristics – Static ($T_{vj} = 25\text{ °C}$, unless otherwise specified)

Symbol	Characteristics	Conditions	Maximum Value	Units
V_F	Forward Voltage	$I_F = 2\text{ A}$, $t_p = 380\text{ }\mu s$	1.1	V
I_R	Reverse Current	$V_R = V_{RRM}$	$T_{vj} = 25\text{ °C}$	10
			$T_{vj} = 125\text{ °C}$	50
			$T_{vj} = 150\text{ °C}$	200

Thermal Specifications

Symbol	Characteristics	Value			Unit
		Min.	Typ.	Max.	
$R_{th(j-c)}$	Thermal Resistance Junction to Case	–	20	–	K/W
$R_{th(j-a)}$	Thermal Resistance Junction to Ambient	–	80	–	K/W

Characteristic Curves

Figure 1. Typical On-state Current vs. On-state Voltage




Figure 2. Typical Power Dissipation vs. Average Forward On-state Current




Figure 3. Maximum Allowable Case Temperature vs. Average On-state Current





Figure 4. Surge Peak On-state Current vs. Number of Cycles




Soldering Parameters

Characteristic		Value
Reflow Condition		Pb – Free assembly
Pre-heat	Temperature Min ($T_{s(min)}$)	150 °C
	Temperature Max ($T_{s(max)}$)	200 °C
	Time (min to max) (t_s)	60 – 120 secs
Average ramp up rate (Liquidus Temp)(T_L) to peak		3 °C/second max
$T_{s(max)}$ to T_L - Ramp-up Rate		3 °C/second max
Reflow	Temperature (T_L) (Liquidus)	217 °C
	Time (t_L)	60 – 150 seconds
Peak Temperature (T_p)		260 ^{+0/-5} °C
Time within 5 °C of actual peak Temperature (t_p)		30 seconds
Ramp-down Rate		6 °C/second max
Time 25 °C to peak Temperature (T_p)		8 minutes max
Do Not Exceed		260 °C

Physical Specifications


Characteristic	Value
Terminal Finish	100% Matte Tin-plated
Body Material	UL Recognized compound meeting flammability rating V-0
Terminal Material	Copper Alloy



Environmental Specifications

Test	Specifications and Conditions
High Temperature Voltage Blocking	MIL-STD-750, M-1040, Condition A Rated V_{RRM} , 150 °C, 1008 hours
Temperature/Humidity	EIA / JEDEC, JESD22-A101, 1008 hours; 320 V DC: 85 °C; 85% relative humidity
Temperature Cycling	MIL-STD-750, M-1051, 1000 cycles; -55°C to +150 °C; 15-min dwell-time
Resistance to Solder Heat	MIL-STD-750: Method 2031, 260 °C, 10 seconds
Solderability	ANSI/J-STD-002
High Temperature Storage	MIL-STD-750, Method 1031, 150 °C, 1008 hours

Part Outline Drawing SOD-123FL



Symbol	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	1.20	1.30	1.40	0.047	0.051	0.055
A1	0.00	0.05	0.10	0	0.002	0.004
b	1.10	1.20	1.30	0.043	0.047	0.051
c	0.10	0.17	0.25	0.004	0.007	0.01
D	2.25	2.35	2.45	0.089	0.093	0.096
E	3.25	3.35	3.45	0.128	0.132	0.136
L	0.35	0.47	0.60	0.014	0.019	0.024
H_E	3.75	3.85	3.95	0.148	0.152	0.156
θ	2°	–	8°	2°	–	8°



Product Selector

Part Number	Voltage	Type	Package
	600 V		
D6002S4ARP	X	Rectifier	SOD-123FL

Packing Options



Part Number	Marking	Weight	Packing Mode	Base Quantity
D6002S4ARP	D602A	0.0268 g	Tape and Reel	5000

Part Numbering and Marking



LF = Littelfuse Logo
XXXXX = Marking Code
Y = Year
M = Month
A = Assembly Location
WW = Lot Code

Packing Specification



Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

