

$\varnothing 20.7 \pm 0.18$
[$\varnothing 0.813 \pm 0.007$]

3.2 ± 0.08
[0.125 ± 0.003]

8.7 ± 0.13
[0.343 ± 0.005]

63.5 ± 1.60
[2.500 ± 0.063]

57.2 ± 1.60
[2.250 ± 0.063]

41.3 ± 1.60
[1.625 ± 0.063]

81.0 ± 1.60
[3.189 ± 0.063]

18.3 ± 0.25
[0.720 ± 0.010]

REVISION

REV	DATE	DESCRIPTION
A	6/27/23	526654GCP - RELEASE MRY

1				
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

BILL OF MATERIAL

<S> CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE

● DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE

ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.

CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

A

MATL SPEC

FINISH

DRW
JMoler


DATE
6/20/2023

SCALE
NTS

FINISH GOOD WT
GRAMS/PIECE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

3RD ANGLE
PROJECTION



TITLE

L25S 35-60A OUTLINE

Littelfuse
CHICAGO, ILLINOIS 60631

REVISION

A

DRWG NO.

OL-L25S060

SHEET 1 OF 1