


Ø25.40 ± 0.381
[Ø1.000 ± 0.015]




3.18 ± 0.15
[0.125 ± 0.006]

17.02 ± 0.89
[0.670 ± 0.035]

8.73 ± 0.25
[0.344 ± 0.010]

14.29 ± 0.25
[0.563 ± 0.010]



65.07 ± 1.590
[2.562 ± 0.063]

76.19 ± 1.590
[2.999 ± 0.063]

53.98 ± 1.00
[2.125 ± 0.039]

92.08 ± 1.590
[3.625 ± 0.063]

REVISION		
REV	DATE	DESCRIPTION
A	3/27/25	528679GCP - RELEASE JTM

1	NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
---	----	--------------	-------------	-------	-----

BILL OF MATERIAL

<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE
●	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
⊠	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

A

MATL SPEC	FINISH
-----------	--------

DRW JCHAVARRIA	DATE 6/21/2023	SCALE NTS	FINISH GOOD WT GRAMS/PIECE
-------------------	-------------------	--------------	-------------------------------

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

3RD ANGLE PROJECTION	
----------------------	--

TITLE	L50QS 125A-100 OUTLINE
--------------	------------------------

Littelfuse CHICAGO, ILLINOIS 60631	REVISION A	DRWG NO. OL-L50QS125-100	SHEET 1 OF 1
--	----------------------	------------------------------------	--------------