



IXFH34N65X2W

650 V, 34 A, 100 mΩ, X2 Class HiPerFET™ Power MOSFET

N-Channel Enhancement Mode, Avalanche Rated



Pinout Diagram TO-247 (IXFH)



G: Gate; **D:** Drain; **S:** Source; **Tab:** Drain

Features

- International standard package
- High power density
- Low $R_{DS(on)}$ and Q_g
- Avalanche rated

Benefits

- Reduced conduction losses
- Reduced driver power requirements
- Easy to mount
- Space savings

Applications

- Switch-mode and resonant-mode power supplies
- DC-DC converters
- PFC circuits
- AC and DC motor drives
- Robotics and servo controls

Product Summary

Characteristic	Value	Unit
V_{DSS}	650	V
I_{D25}	34	A
$R_{DS(on)}$	≤ 100	mΩ

Maximum Ratings

Symbol	Characteristic	Conditions	Value	Unit
V_{DSS}	Drain-source voltage	$T_{vj} = 25\text{ °C to }150\text{ °C}$	650	V
V_{GSS}	Gate-source voltage	Continuous	± 30	V
V_{GSM}		Transient	± 40	
I_{D25}	Drain current	$T_c = 25\text{ °C}$	34	A
I_{DM}	Peak drain current	$T_c = 25\text{ °C}$, pulse width limited by $T_{vj(max)}$	68	
I_{AS}	Single pulse avalanche current	$T_c = 25\text{ °C}$	7	A
E_{AS}	Single pulse avalanche energy	$T_c = 25\text{ °C}$	1	J
dv/dt	Source-drain diode dv/dt capability	$I_s \leq I_{DM}$, $V_{DD} \leq V_{DSS}$, $T_{vj} \leq 150\text{ °C}$	50	V/ns
P_{tot}	Total power dissipation	$T_c = 25\text{ °C}$	540	W
T_{vj}	Virtual junction temperature range	–	–55 to +150	°C
$T_{vj(max)}$	Maximum virtual junction temperature	–	150	
T_{stg}	Storage temperature range	–	–55 to +150	
T_{slid}	Soldering Temperature	Maximum lead temperature for soldering	300	°C
M_d	Mounting torque	–	1.13 / 10	Nm/lb.in
G	Weight	–	6	g

Thermal Characteristics

Symbol	Characteristic	Value			Unit
		Min.	Typ.	Max.	
$R_{th(j-c)}$	Thermal resistance junction to case	–	–	0.23	K/W
$R_{th(c-h)}$	Thermal resistance case to heat sink	–	0.21	–	K/W

Electrical Characteristics – Static ($T_{vj} = 25\text{ °C}$ unless otherwise specified)

Symbol	Characteristic	Conditions	Value			Unit
			Min.	Typ.	Max.	
$V_{(BR)DSS}$	Drain-source breakdown voltage	$I_D = 1\text{ mA}$, $V_{GS} = 0\text{ V}$	650	–	–	V
$V_{GS(th)}$	Gate threshold voltage	$I_D = 2.5\text{ mA}$, $V_{GS} = V_{DS}$	3.5	–	5.0	V
I_{GSS}	Gate-source leakage current	$V_{DS} = 0\text{ V}$, $V_{GS} = \pm 30\text{ V}$	–	–	± 100	nA
I_{DSS}	Drain-source leakage current	$V_{DS} = V_{DSS}$, $V_{GS} = 0\text{ V}$	–	–	10	μA
		$V_{DS} = V_{DSS}$, $V_{GS} = 0\text{ V}$, $T_{vj} = 125\text{ °C}$	–	–	1.75	mA
$R_{DS(on)}$	Drain-source on-resistance ¹	$V_{GS} = 10\text{ V}$, $I_D = 0.5 \times I_{D25}$	–	–	100	m Ω

Note 1: Pulse test, $t \leq 300\text{ }\mu\text{s}$, duty cycle, $d \leq 2\%$

Electrical Characteristics – Dynamic ($T_{vj} = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Characteristic	Conditions	Value			Unit
			Min.	Typ.	Max.	
g_{fs}	Transconductance ¹	$V_{DS} = 10\text{ V}, I_D = 0.5 \times I_{D25}$	18	29	–	S
$R_{g(int)}$	Gate input resistance	–	–	1.0	–	Ω
C_{iss}	Input capacitance	$V_{GS} = 0\text{ V}, V_{DS} = 25\text{ V}, f = 1\text{ MHz}$	–	3200	–	pF
C_{oss}	Output capacitance		–	1560	–	
C_{rss}	Reverse transfer capacitance		–	1.4	–	
$C_{o(er)}$	Effective output capacitance – energy related	$V_{GS} = 0\text{ V}, V_{DS} = 0.8 \times V_{DSS}$	–	127	–	pF
$C_{o(tr)}$	Effective output capacitance – time related		–	460	–	
Q_G	Total gate charge	$V_{GS} = 10\text{ V}, V_{DS} = 0.5 \times V_{DSS},$ $I_D = 0.5 \times I_{D25}$	–	64	–	nC
Q_{GS}	Gate-source charge		–	22	–	
Q_{GD}	Gate-drain charge		–	22	–	
$t_{d(on)}$	Turn-on delay time	Resistive Switching $V_{GS} = 10\text{ V}, V_{DS} = 0.5 \times V_{DSS},$ $I_D = 0.5 \times I_{D25}, R_{G(ext)} = 10\ \Omega$	–	38	–	ns
t_r	Rise time		–	52	–	
$t_{d(off)}$	Turn-off delay time		–	66	–	
t_f	Fall time		–	31	–	

Note 1: Pulse test, $t \leq 300\ \mu\text{s}$, duty cycle, $d \leq 2\%$

Source-Drain Diode Characteristics ($T_{vj} = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Characteristic	Conditions	Value			Unit
			Min.	Typ.	Max.	
I_S	Continuous diode forward current	$V_{GS} = 0\text{ V}$	–	–	34	A
I_{SM}	Diode pulse current	Repetitive, pulse width limited by $T_{vj(max)}$	–	–	136	A
V_{SD}	Diode forward voltage ¹	$I_F = I_S, V_{GS} = 0\text{ V}$	–	–	1.4	V
t_{rr}	Reverse recovery time	$I_F = 17\text{ A}, -di/dt = 100\text{ A}/\mu\text{s},$ $V_R = 100\text{ V}, V_{GS} = 0\text{ V}$	–	180	–	ns
Q_{rr}	Reverse recovery charge		–	1.44	–	μC
I_{rrm}	Peak reverse recovery current		–	16	–	A

Note 1: Pulse test, $t \leq 300\ \mu\text{s}$, duty cycle, $d \leq 2\%$

Characteristic Curves

Fig. 1. Output Characteristics @ $T_J = 25^\circ\text{C}$




Fig. 2. Extended Output Characteristics @ $T_J = 25^\circ\text{C}$




Fig. 3. Output Characteristics @ $T_J = 125^\circ\text{C}$




Fig. 4. $R_{DS(on)}$ Normalized to $I_D = 17\text{ A}$ Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to $I_D = 17\text{ A}$ Value vs. Drain Current




Fig. 6. Normalized Breakdown & Threshold Voltages vs. Junction Temperature




Fig. 7. Maximum Drain Current vs. Case Temperature




Fig. 8. Input Admittance




Fig. 9. Transconductance




Fig. 10. Forward Voltage Drop of Intrinsic Diode




Fig. 11. Gate Charge




Fig. 12. Capacitance




Fig. 13. Output Capacitance Stored Energy




Fig. 14. Forward-Bias Safe Operating Area






Fig. 15. Maximum Transient Thermal Impedance



Part Outline Drawing TO-247 (IXFH)



Symbol	Inches			Millimeters		
	Min.	Typical	Max.	Min.	Typical	Max.
A	0.190	–	0.205	4.83	–	5.21
A1	0.090	–	0.100	2.29	–	2.54
A2	0.075	–	0.085	1.91	–	2.16
b	0.045	–	0.055	1.14	–	1.40
b2	0.075	–	0.087	1.91	–	2.20
b4	0.115	–	0.126	2.92	–	3.20
c	0.024	–	0.031	0.61	–	0.80
D	0.819	–	0.840	20.80	–	21.34
D1	0.650	–	0.690	16.51	–	17.53
D2	0.035	–	0.050	0.89	–	1.27
E	0.620	–	0.635	15.57	–	16.13
E1	0.545	–	0.565	13.84	–	14.35
e	0.215 BSC			5.45 BSC		
L	0.780	–	0.810	19.81	–	20.57
L1	0.150	–	0.170	3.81	–	4.32
ØP	0.140	–	0.144	3.55	–	3.65
ØP1	0.275	–	0.290	6.99	–	7.37
Q	0.220	–	0.244	5.59	–	6.20
R	0.170	–	0.190	4.62	–	4.83
S	0.242 BSC			6.15 BSC		

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.

Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

