

IXYH55N120C4H1

1200 V, 55 A XPT™ Gen4 IGBT with Sonic Diode

High Speed IGBT for 20–50 kHz Switching



Pinout Diagram (TO-247-3L)



G: Gate; **C:** Collector; **E:** Emitter; **backside:** Collector

Description:

Developed using our proprietary XPT™ thin-wafer technology and state-of-the-art Trench IGBT process, these devices feature reduced thermal resistance, low energy losses, fast switching, low tail current, and high current densities.

Features & Benefits:

- Optimized for Low Switching Loss
- Positive Thermal Coefficient of $V_{CE(sat)}$
- International Standard Package
- High Current Handling Capability
- High Power Density
- Low Gate Drive Requirement
- Anti-Parallel Sonic Diode

Applications:

- Power Inverters
- UPS
- Motor Drives
- SMPS
- PFC Circuits
- Battery Chargers
- Welding Machines

Product Summary

Characteristic	Value	Unit
V_{CES}	1200	V
I_{C110}	55	A
$V_{CE(sat)}$	2.50	V
$t_{fi(typ)}$	42	ns

OBSOLETE

© 2023 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: XZ 04/19/2023

Maximum Ratings

Symbol	Characteristic	Conditions	Value	Unit
V_{CES}	Collector-Emitter Voltage	T_J = 25°C to 175°C	1200	V
V_{GES}	Gate-Emitter Voltage	Continuous	±20	V
V_{GEM}	Transient Gate-Emitter Voltage	Transient	±30	V
I_{C25}	Continuous Collector Current	T_C = 25°C	126	A
I_{C110}	Continuous Collector Current	T_C = 110°C	55	A
I_{F110}	Diode Forward Current	T_C = 110°C	37	A
I_{CM}	Pulsed Collector Current	T_C = 25°C, 1 ms	290	A
SSOA (RBSOA)	Switching Safe Operating Area (Reverse Biased Safe Operating Area)	V_{GE} = 15 V, T_{VJ} = 150°C, R_G = 5 Ω, Clamped Inductive Load, $I_{CM} = V_{CE} \le 0.8 \times V_{CES}$	110	A
P_C	Collector Power Dissipation	T_C = 25°C	650	W
T_J	Junction Temperature	–	-55 to 175	°C
T_{JM}	Maximum Junction Temperature	–	175	°C
T_{stg}	Storage Temperature	–	-55 to 175	°C
T_L	Lead Temperature for Soldering	1.6 mm (0.062 in.) from Case for 10 s	300	°C
M_d	Mounting Torque	–	1.13 / 10	Nm/lb.in
W	Weight	–	6	g

Thermal Characteristics

Symbol	Characteristic	Value			Unit
		Min.	Typ.	Max.	
$R_{th, JC}$	Thermal Resistance, junction-to-case	–	–	0.23	°C/W
$R_{th, CS}$	Thermal Resistance, case-to-heat sink	–	0.21	–	°C/W

Electrical Characteristics – Static (T_J = 25°C unless otherwise specified)

Symbol	Characteristic	Conditions	Value			Unit
			Min.	Typ.	Max.	
BV_{CES}	Collector-Emitter Breakdown Voltage	I_C = 250 µA, V_{GE} = 0 V	1200	–	–	V
$V_{GE(th)}$	Gate-Emitter Threshold Voltage	I_C = 250 µA, $V_{CE} = V_{GE}$	4.0	–	6.5	V
I_{GES}	Gate-Emitter Leakage Current	V_{CE} = 0 V, V_{GE} = ±20 V	–	–	±100	nA
I_{CES}	Zero Gate Voltage Collector Current	$V_{CE} = V_{CES}$, V_{GE} = 0 V	–	–	50	µA
		$V_{CE} = V_{CES}$, V_{GE} = 0 V, T_J = 125°C	–	–	5	mA
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage[1]	I_C = 55 A, V_{GE} = 15 V	–	2.10	2.50	V
		I_C = 55 A, V_{GE} = 15 V, T_J = 150°C	–	2.60	–	V

Note 1: Pulse test, t ≤ 300 µs, duty cycle, d ≤ 2%

OBSOLETE

© 2023 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: XZ 04/19/2023

Electrical Characteristics – Dynamic (T_J = 25°C unless otherwise specified)

Symbol	Characteristic	Conditions		Value			Unit
				Min.	Typ.	Max.	
g_{fs}	Transconductance[1]	I_C = 55 A, V_{CE} = 10 V		18	30	–	S
C_{ies}	Input Capacitance	V_{GE} = 0 V, V_{CE} = 25 V, f = 1 MHz		–	2300	–	pF
C_{oes}	Output Capacitance			–	180	–	
C_{res}	Reverse Transfer Capacitance			–	77	–	
$Q_{g(on)}$	Total Gate Charge	V_{GE} = 15 V, V_{CE} = 0.5 x V_{CES}, I_C = 55 A		–	114	–	nC
Q_{ge}	Gate-Emitter Charge			–	19	–	
Q_{gc}	Gate-Collector Charge			–	49	–	
$t_{d(on)}$	Turn-on Delay Time[2]	Inductive Load, V_{GE} = 15 V, V_{CE} = 0.5 x V_{CES}, I_C = 40 A, $R_{G(ext)}$ = 5 Ω	T_J = 25°C	–	20	–	ns
			T_J = 150°C	–	20	–	
t_{ri}	Turn-on Rise Time[2]		T_J = 25°C	–	50	–	ns
			T_J = 150°C	–	34	–	
E_{on}	Turn-on Energy[2]		T_J = 25°C	–	3.50	–	mJ
			T_J = 150°C	–	4.80	–	
$t_{d(off)}$	Turn-off Delay Time[2]		T_J = 25°C	–	180	–	ns
			T_J = 150°C	–	200	–	
t_{fi}	Turn-off Fall Time[2]		T_J = 25°C	–	42	–	ns
			T_J = 150°C	–	123	–	
E_{off}	Turn-off Energy[2]		T_J = 25°C	–	1.34	–	mJ
			T_J = 150°C	–	2.50	–	

Note 1: Pulse test, t ≤ 300 µs, duty cycle, d ≤ 2%
Note 2: Switching times and energy losses may increase for higher $V_{CE(clamp)}$, T_J, or R_G.

Reverse Sonic Diode (FRD) (T_J = 25°C unless otherwise specified)

Symbol	Characteristic	Conditions	Value			Unit
			Min.	Typ.	Max.	
V_F	Diode Forward Voltage[1]	I_F = 40 A, V_{GE} = 0 V	–	2.40	2.80	V
		I_F = 40 A, V_{GE} = 0 V, T_J = 150°C	–	3.00	–	
I_{RM}	Reverse Recovery Current	I_F = 40 A, V_{GE} = 0 V, T_J = 150°C	–	27	–	A
t_{rr}	Reverse Recovery Time	$-di_F/dt$ = 450 A/µs, V_R = 600 V	–	180	–	ns
$R_{th, JC}$	Thermal Resistance, junction-to-case	–	–	–	0.35	°C/W

Note 1: Pulse test, t ≤ 300 µs, duty cycle, d ≤ 2%

OBSOLETE

© 2023 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: XZ 04/19/2023

Characteristic Curves

Fig. 1. Output Characteristics @ T_J = 25ºC




Fig. 2. Extended Output Characteristics @ T_J = 25ºC




Fig. 3. Output Characteristics @ T_J = 150ºC




Fig. 4. Dependence of $V_{CE(sat)}$ on Junction Temperature




Fig. 5. Collector-to-Emitter Voltage vs. Gate-to-Emitter Voltage





Fig. 6. Input Admittance



OBSOLETE

© 2023 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: XZ 04/19/2023

Fig. 7. Transconductance




Fig. 8. Gate Charge




Fig. 9. Capacitance




Fig. 10. Reverse-Bias Safe Operating Area




Fig. 11. Maximum Transient Thermal Impedance





Fig. 12. Inductive Switching Energy Loss vs. Collector Current



OBSOLETE

© 2023 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: XZ 04/19/2023

Fig. 13. Inductive Switching Energy Loss vs. Collector-Emitter Voltage




Fig. 14. Inductive Switching Energy Loss vs. Gate Resistance




Fig. 15. Inductive Switching Energy Loss vs. Junction Temperature




Fig. 16. Inductive Turn-off Switching Times vs. Gate Resistance




Fig. 17. Inductive Turn-off Switching Times vs. Collector Current





Fig. 18. Inductive Turn-off Switching Times vs. Junction Temperature



OBSOLETE

© 2023 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: XZ 04/19/2023

Fig. 19. Inductive Turn-on Switching Times vs. Gate Resistance




Fig. 20. Inductive Turn-on Switching Times vs. Collector Current




Fig. 21. Inductive Turn-on Switching Times vs. Junction Temperature




Fig. 22. Maximum Peak Load Current vs. Frequency




Fig. 23. Diode Forward Characteristics





Fig. 24. Reverse Recovery Charge vs. -di$_F$/dt



OBSOLETE

© 2023 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: XZ 04/19/2023

Fig. 25. Reverse Recovery Current vs. -di$_F$/dt




Fig. 26. Reverse Recovery Time vs. -di$_F$/dt




Fig. 27. Dynamic Parameters Q$_{RR}$, I$_{RR}$ vs. Junction Temperature






Fig. 28. Maximum Transient Thermal Impedance (Diode)



OBSOLETE

© 2023 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: XZ 04/19/2023

Part Outline Drawing (TO-247-3L)



Symbol	Inches			Millimeters		
	Min.	Typical	Max.	Min.	Typical	Max
A	0.185	–	0.209	4.70	–	5.30
A1	0.087	–	0.102	2.21	–	2.59
A2	0.059	–	0.098	1.50	–	2.49
b	0.039	–	0.055	0.99	–	1.40
b2	0.065	–	0.094	1.65	–	2.39
b4	0.102	–	0.135	2.59	–	3.43
c	0.015	–	0.035	0.38	–	0.89
D	0.819	–	0.844	20.79	–	21.45
D1	0.515	–	–	13.07	–	–
D2	0.020	–	0.053	0.51	–	1.35
E	0.609	–	0.639	15.48	–	16.24
E1	0.530	–	–	13.45	–	–
E2	0.170	–	0.216	4.31	–	5.48
e	0.215 BSC			5.45 BSC		
L	0.780	–	0.799	19.80	–	20.30
L1	–	–	0.177	–	–	4.49
Ø P1	0.140	–	0.144	3.55	–	3.65
Ø P2	–	–	0.291	-	–	7.39
Q	0.212	–	0.244	5.38	–	6.19
S	0.242 BSC			6.14 BSC		

OBSOLETE

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at http://www.littelfuse.com/disclaimer-electronics.

© 2023 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: XZ 04/19/2023