



Ø10.3 ± 0.1
[Ø0.406 ± 0.004]



38.0 ± 0.8
[1.5 ± 0.031]



REVISION		
REV	DATE	DESCRIPTION
A	3/11/24	527567/GCF - RELEASE JTM

1						
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M		
BILL OF MATERIAL						
<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE					
●	DENOTES CRITICAL CHARACTERISTICS.					
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE					
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.					
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.					
MATL SPEC			FINISH			
DRW JMoler	DATE 12/31/1969	SCALE NTS	FINISH GOOD WT GRAMS/PIECE			
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994						
3RD ANGLE PROJECTION						
TITLE L60QS000 OUTLINE						
Littelfuse [®] CHICAGO, ILLINOIS 60631			REVISION A	DRWG NO. OL-L60QS000		

SHEET 1 OF 1