


ET Series

Sealed Subminiature Toggle Switches



Description

The ET series sealed subminiature toggle switches are often used in the medical and telecommunications industry in hand-held or instrumentation applications. Featuring a small footprint (to help save space on the PCB) and ESD protection, long-lasting ET switches also come with strong protection from solder and cleaning process contaminants.

Features & Benefits

- Sealed against solder and cleaning process contaminants
- ESD protection available
- Thru-hole and surface mount models
- Compact size and small footprint save PCB space
- RoHS compliant models available

Agency Approvals

Agency	Agency File Number
US	E42363

Specifications

Contact Rating	B contact material: 0.4 VA max. @ 20 V AC or DC max.
Electrical Life	ETX1 models: 60,000 make-and-break cycles at full load. All other models: 30,000 cycles.
Contact Resistance	Below 20 m Ω typ. initial @ 2-4 V DC, 100 mA, for both silver and gold plated contacts.
Insulation Resistance	10 ⁹ Ω min.
Dielectric Strength	1000 Vrms min. @ sea level.
Operating Temperature	-30°C to 85°C
Solderability	Per MIL-STD-202F method 208D, or EIA RS-186E method 9 (1 hour steam aging).
Degree of Protection	IP57; Protection against harmful dust deposit, full-scale voltage protection, temporary immersion.
Packaging	Surface mount switches are shipped in tape and reel packaging.

Applications

- Hand-held telecommunications
- Instrumentation
- Medical equipment

Materials

Case & Bushing	Glass filled nylon 6/6, flame retardant, heat stabilized (UL 94V-0) or glass filled 4/6 nylon, flame retardant, heat stabilized (UL 94V-0).
Actuator	M3 anti-static actuator: Nylon 4/6, black standard (UL 94V-0). All other actuators: Brass, chrome plated. Internal o-ring seal standard with all actuators.
Switch Support	Brass, tin plated.
Contact & Terminals	B contact material: Copper alloy, with gold plate over nickel plate. Q contact material: Copper alloy, silver plated.
Terminal Seal	Epoxy

Notes:


Any models supplied with Q, B, G or P contact material are RoHS compliant and compatible. Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.


ET Series

Sealed Subminiature Toggle Switches




DPDT

No. Poles	Model No.	Switch Function			Connected Terminals			Schematic
		POS. 1 	POS. 2 	POS. 3 	POS. 1 	POS. 2 	POS. 3 	
		C&K Marking on Opposite Side						
DP	ET21	ON	NONE	ON	2-3,5-6	N/A	2-1,5-4	DPDT 
	ET23	ON	OFF	ON	2-3,5-6	OPEN	2-1,5-4	
	ET25	MOM.	OFF	MOM.	2-3,5-6	OPEN	2-1,5-4	
	ET28	ON	NONE	MOM.	2-3,5-6	N/A	2-1,5-4	



Part number shown: ET21MD1CBE




Notes:

MOM. = Momentary All models us with all options when ordered with G, Q or S contact material.
 2. Wiring for 3 way switch.


Actuator

M 0.240" High




Standard with A, AV, V3 & V31 terminations.

M3 Plastic, Antistatic 0.240" High




Material: Nylon 4/6 (UL 94V-0), black standard.
 Static resistance: 9,000 V DC min. @ sea level, actuator to terminals.

S 0.400" High



Standard with C or W terminations.

S1 0.550" High




Notes: All actuators have chrome finish (except M3).

ET Series

Sealed Subminiature Toggle Switches




L 0.320" High



Option Code	L3 Actuator Color
(None)	Black (M3 only)
1	White (M3 only)


Notes: Other colors available, consult Customer Service Center.
No color choice required for S & M actuators.

Bushing
D1 0.177" High, Unthreaded




Terminations

C PC Thru-hole




W Wire Wrap




PC Mounting

SP




ET02 – omit center hole.



DP



Sealed Subminiature Toggle Switches




Notes: Terminal bend radii and lead-in manufacturing option.

ET Series

Sealed Subminiature Toggle Switches




AV Vertical Right Angle, PC Thru-hole ET21MD1AVBE Vertical Actuation DPDT




Actuator Shown in Pos.1

Notes: Terminal bend radii and lead-in manufacturing option.

PC Mounting




AV3 Vertical Right Angle, Snap-in, PC Thru-hole ET01SD1AV2BE Vertical Actuation SPDT




Actuator Shown in Pos.1

PC Mounting




SA Right Angle, Surface Mount ET01M3D1SAPE Horizontal Actuation SPDT Only



Actuator Shown in Pos.1

Notes: Not available with S and S1 actuators. Standard with tape & reel packaging.

PC Mounting




ET Series

Sealed Subminiature Toggle Switches




SA1 Right Angle, Surface Mount ET01M3D1SA1BE Horizontal Actuation SPDT Only




Notes: Not available in ET02. Actuators M and M3, bushing D1, contact material B. Standard with tape and reel packaging.

V3 Vertical Mount, V-Bracket V31 Vertical Mount, V-Bracket, Snap-in ET01MD1V3BE SPDT




Actuator Shown in Pos.1
ET02 Models: Omit terminal 2

PC Mounting




V3 Vertical Mount, V-Bracket ET21MD1V3BE DPDT



Actuator Shown in Pos.1

PC Mounting



ET Series

Sealed Subminiature Toggle Switches



Contact Material

Option Code	Contact Material	Terminal Plating	Ratings	
B	Gold ¹	Gold ¹	Low Level / Dry Circuit	0.4 VA Max. @ 20 V AC or DC Max.
P		Matte-Tin ⁶		
Q	Silver ^{4,5}	Silver ⁵	Power	ETX1 models: 3 amps @ 120 V AC OR 28 V DC All other models: 2 amps @ 120 V AC OR 28 V DC
S		Matte-Tin ⁶		
G	Gold over Silver ^{2,3}	Gold ³	Low Level / Dry Level Circuit or Power	ETX1 models: 0.4 VA Max. @ 20 V AC OR DC Max. or 3 amps @ 120 V AC OR 28 V DC All other models: 0.4 VA Max. @ 20 V AC OR DC Max. or 2 amps @ 120 V AC OR 28 V DC
		Matte-Tin ⁶		

Notes: 1. Contacts & Terminals: Copper alloy, with gold plate over nickel plate.

2. End Contacts: Coin silver, with gold plate over nickel plate.

3. Center Contacts & All Terminals: Copper alloy, with gold plate over nickel plate.

4. End Contacts: Coin silver, silver plated.


5. Center Contacts & All Terminals: Copper alloy, silver plated.

6. Terminals: Copper alloy, with matte tin alloy nickel plate.

Notes: Any models supplied with Q, B, G or P contact material are RoHS compliant.


All models  with all options (except M3 actuator) when ordered with G, L or Q contact material.

Seal




Available Hardware

Cap



Part No.
706201000 White
706202000 Black
706203000 Red
Material: Vinyl
Finish: Matte

Tape & Reel




For part number ET01M3D1SAPE

Reel Information

Outside Diameter	13.00 (330.0)
Pilot Hole	0.512 (13.0)
Quantity Per Reel	600

Tape & Reel



Outside Diameter	13.00 (330.0)
Pilot Hole	0.795 (20.20)
Quantity Per Reel	500

