

MAXI+ Series

Blade Fuses – Rated 32V



Description

The MAXI+® Fuse is new standard for vehicle circuit protection. Its miniature design meets the need for more circuits to be protected while utilizing less space, and its ability to cope with high temperatures in adverse environments makes the MAXI+® Fuse of recommended choice for protection.

Features & Benefits

- Color coding indicates amperage rating for each fuse
- See-through housing makes it easy to check whether a fuse has blown
- Checkpoints on top make it possible to measure resistance without removing the fuse
- Simple to install and remove
- Comply with ISO 8820-10:2020
- High-contrast amperage stamp on the top of the housing aids identification
- Silver plating allows up to 150°C at the terminal interface

Agency Approvals

Agency	Agency File Number	Current Rating (A)
	E71611 - 20221130 - 0899	60 A

Applications

- Cars / SUVs
- Trucks
- Offroad vehicles
- Buses
- Watercraft as approved by Littelfuse®

Additional Information



Resources



Samples

See Disclaimer Notice

Specifications

Voltage Rating:	32 V DC
Interrupting Rating:	1000 A @ 32 V DC
Recommended Environmental Temperature:	-40 °C to +125 °C
Terminals Material:	Silver-plated zinc alloy *
Housing Material:	PA66 (UL 94 Flammability rating of V-2)
Typical Weight per Fuse:	2 g
Comply With:	ISO 8820-10:2020

*Note: Silver plating allows up to 150 °C at the terminal interface.








Ordering Information

Part Number	Current Rating (A)	Package Size
0899xxx.Z	20 – 60	1000

MAXI+ Series

Blade Fuses – Rated 32V


Ratings

Part Number	Current Rating (A)	Housing Material Color	Test Cable Size (mm ²)	Typ. Voltage Drop (mV)	Typ. Cold Resistance (mΩ)	Typ. I ² t (A ² s)
0899020.Z	20		1.5	80	3.0	1300
0899025.Z	25		2.5	77	2.3	2200
0899030.Z	30		2.5	60	1.7	3900
0899035.Z	35		4	58	1.2	4900
0899040.Z	40		4	55	1.0	9400
0899050.Z	50		6	50	0.7	16 500
0899060.Z	60		6	62	0.5	17 500

Note: The typical I²t is an average value calculated from the breaking capacity tests by using the melting time before the arcing occurs.

Dimensions


Dimensions in mm. Please refer to the outline drawing for dimensions and tolerances.




MAXI+ Series

Blade Fuses – Rated 32V

Time-Current Characteristic



% of Rating	Opening Time Min. / Max. (s)
100	360 000 / -
135	60 / 900
160	10 / 100
200	2 / 50
350	0.2 / 7
600	0.04 / 1




Note: Current recommendation may be impacted by the final condition of the application (terminals characteristics, wire size etc.). Please contact Littelfuse® for more information.


Typical Derating Curves

Temperature security margin is 20%.

Please contact Littelfuse® for Details Regarding Derating Test Set Up.



	Max. allowed current load (A) at ambient temperature based on typical derating						
	-40 °C	0 °C	20 °C	65 °C	85 °C	110 °C	125 °C
20 A	20	20	20	17	15	13	11
25 A	25	25	25	21	19	16	14
30 A	30	30	30	26	24	20	17
35 A	35	35	35	33	29	24	21
40 A	40	40	40	36	32	27	23
50 A	50	50	50	42	38	32	27
60 A	60	60	56	47	42	36	31



Note: Current recommendation may be impacted by the final condition of the application (terminals characteristics, wire size etc.). Please contact Littelfuse® for more information.

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <https://www.littelfuse.com/legal/disclaimers/product-disclaimer.aspx>