


DSA50C100QB

100 V, 2x 25 A Schottky Rectifier Diode


RoHS

**Features**

- Very low V_F
- Extremely low switching losses
- Low I_{RM} values
- Improved thermal behavior
- High reliability circuit operation
- Low voltage peaks for reduced protection circuits
- Low noise switching
- Terminals finish: 100% Pure Tin
- Epoxy meets UL 94V-0

Applications

- Rectifiers in switch mode power supplies (SMPS)
- Free wheeling diode in low voltage converters

Pinout Diagram (TO-3P)**C:** Cathode; **A:** Anode; **tab:** Cathode**Product Summary**

Characteristic	Value	Unit
V_{RRM}	100	V
I_{FAV}	2 x 25	A
V_F	0.72	V

Maximum Ratings ($T_A = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Characteristics	Condition	Max.	Units
V_{RRM}	Peak Repetitive Reverse Voltage	—	100	V
V_{RWM}	Working Peak Reverse Voltage			
V_R	DC Blocking Voltage			
I_{FAV}	Average Rectified Forward Current	50% duty cycle @ $T_C = 155^\circ\text{C}$, rectangular wave form	25 (Per Leg)	A
			50 (Per Device)	
I_{FSM}	Peak One Cycle Non-Repetitive Surge Current (Per Leg)	10 ms, Half Sine pulse, $T_{VJ} = 25^\circ\text{C}$	340	A
P_{tot}	Total power dissipation	$T_C = 25^\circ\text{C}$	160	W

Electrical Characteristics ($T_A = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Characteristics	Conditions	Typ.	Max.	Units
V_{F1}	Forward Voltage Drop (Per Leg) ¹	@ 25 A, Pulse, $T_{VJ} = 25^\circ\text{C}$	—	0.90	V
V_{F2}		@ 25 A, Pulse, $T_{VJ} = 125^\circ\text{C}$	—	0.72	V
I_{R1}	Reverse Current (Per Leg)*	@ $V_R = \text{rated } V_R$, $T_{VJ} = 25^\circ\text{C}$	—	450	μA
I_{R2}		@ $V_R = \text{rated } V_R$, $T_{VJ} = 125^\circ\text{C}$	—	15	mA
C_T	Junction Capacitance	@ $V_R = 12\text{ V}$, $T_C = 25^\circ\text{C}$ $f_{SIG} = 1\text{ MHz}$	334	—	pF

Note 1: Pulse width < 300 μs , duty cycle < 2%**Thermal-Mechanical Specifications**

Symbol	Characteristics	Condition	Specification	Units
T_{VJ}	Junction Temperature	—	-55 to +175	$^\circ\text{C}$
T_O	Operation Temperature	—	-55 to +150	$^\circ\text{C}$
T_{stg}	Storage Temperature	—	-55 to +150	$^\circ\text{C}$
M_D	Mounting Torque	—	Min 0.8 Max 1.2	Nm
F_C	Mounting force with clip	—	Min 20 Max 120	N
R_{thJC}	Maximum Thermal Resistance Junction to Case	DC operation	0.95	K/W
R_{thCS}	Typical Thermal Resistance Case to Heat Sink	—	0.30	K/W
wt	Approximate Weight	—	6.28	g

Characteristic Curves

Fig. 1. Typical Forward Characteristics




Fig. 2. Typical Reverse Characteristics






Fig. 3. Typical Junction Capacitance




Part Outline Drawing (TO-3P)



Symbol	Inches			Millimeters		
	Min.	Typical	Max.	Min.	Typical	Max.
A	0.185	–	1.193	4.70	–	4.90
A1	0.051	–	0.059	1.30	–	1.50
A2	0.057	–	0.065	1.45	–	1.65
b	0.035	–	0.045	0.90	–	1.15
b2	0.075	–	0.087	1.90	–	2.20
b4	0.114	–	0.126	2.90	–	3.20
c	0.022	–	0.031	0.55	–	0.80
D	0.780	–	0.791	19.80	–	20.10
D1	0.665	–	0.677	16.90	–	17.20
E	0.610	–	0.622	15.50	–	15.80
E1	0.531	–	0.539	13.50	–	13.70
e	0.215 BSC			5.45 BSC		
L	0.780	–	0.795	19.80	–	20.20
L1	0.134	–	0.142	3.40	–	3.60
Ø P	0.126	–	0.134	3.20	–	3.40
Ø P1	0.272	–	0.280	6.90	–	7.10
S	0.193	–	0.201	4.90	–	5.10

Part Number and Marking




DS = Schottky Diode
 A = Product Generation
 50 = Current Rate
 C = Common Cathode
 100 = Voltage Rating
 QB = Package Code
 YY = Year
 WW = Work Week
 S = Plant Location Code
 XXXX = Lot Number

Ordering Information

Part Number	Marking	Packing Mode	M.O.Q
DSA50C100QB	DSA50C100QB	Tube (30 pcs)	–

Packing Specifications



Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

