


High Voltage XPT™ IGBT w/ Diode

IXYF16N250CV1




$$\begin{aligned} V_{CES} &= 2500V \\ I_{C110} &= 14A \\ V_{CE(sat)} &\leq 4.0V \\ t_{fi(typ)} &= 250ns \end{aligned}$$

(Electrically Isolated Tab)

Symbol	Test Conditions	Maximum Ratings	
V_{CES}	$T_J = 25^\circ\text{C}$ to 175°C	2500	V
V_{CGR}	$T_J = 25^\circ\text{C}$ to 175°C , $R_{GE} = 1\text{M}\Omega$	2500	V
V_{GES}	Continuous	± 20	V
V_{GEM}	Transient	± 30	V
I_{C25}	$T_C = 25^\circ\text{C}$	26	A
I_{C110}	$T_C = 110^\circ\text{C}$	14	A
I_{F110}	$T_C = 110^\circ\text{C}$	9	A
I_{CM}	$T_C = 25^\circ\text{C}$, 1ms	160	A
SSOA (RBSOA)	$V_{GE} = 15\text{V}$, $T_{VJ} = 150^\circ\text{C}$, $R_G = 10\Omega$ Clamped Inductive Load	$I_{CM} = 64$ 1500	A V
P_C	$T_C = 25^\circ\text{C}$	180	W
T_J		-55 ... +175	$^\circ\text{C}$
T_{JM}		175	$^\circ\text{C}$
T_{stg}		-55 ... +175	$^\circ\text{C}$
T_L	Maximum Lead Temperature for Soldering	300	$^\circ\text{C}$
T_{SOLD}	1.6 mm (0.062in.) from Case for 10s	260	$^\circ\text{C}$
F_C	Mounting Force	20..120 / 4.5..27	Nm/lb.in.
V_{ISOL}	50/60Hz, 1 Minute	2500	V~
Weight		8	g

ISOPLUS i4-Pak™



1 = Gate
2 = Emitter
5 = Collector

Features

- Silicon Chip on Direct-Copper Bond (DCB) Substrate
- Isolated Mounting Surface
- 2500V~ Electrical Isolation
- High Blocking Voltage
- High Peak Current Capability
- Low Saturation Voltage

Advantages

- Low Gate Drive Requirement
- High Power Density

Applications

- Switch-Mode and Resonant-Mode Power Supplies
- Uninterruptible Power Supplies (UPS)
- Laser Generators
- Capacitor Discharge Circuits
- AC Switches

Symbol	Test Conditions ($T_J = 25^\circ\text{C}$, Unless Otherwise Specified)	Characteristic Values		
		Min.	Typ.	Max.
BV_{CES}	$I_C = 250\mu\text{A}$, $V_{GE} = 0\text{V}$	2500		V
$V_{GE(th)}$	$I_C = 250\mu\text{A}$, $V_{CE} = V_{GE}$	3.0		5.0 V
I_{CES}	$V_{CE} = V_{CES}$, $V_{GE} = 0\text{V}$ $V_{CE} = 0.8 \cdot V_{CES}$, $V_{GE} = 0\text{V}$ Note 2, $T_J = 150^\circ\text{C}$			50 μA 4 mA
I_{GES}	$V_{CE} = 0\text{V}$, $V_{GE} = \pm 20\text{V}$			± 100 nA
$V_{CE(sat)}$	$I_C = 16\text{A}$, $V_{GE} = 15\text{V}$, Note 1 $T_J = 150^\circ\text{C}$	3.30 4.75	4.00	V V

Symbol Test Conditions (T _J = 25°C Unless Otherwise Specified)		Characteristic Values		
		Min.	Typ.	Max.
g_{fs}	I _C = 16A, V _{CE} = 10V, Note 1	11	18	S
R_{GI}	Gate Input Resistance		5.8	Ω
C_{ies}	} V _{CE} = 25V, V _{GE} = 0V, f = 1MHz		1980	pF
C_{oes}			94	pF
C_{res}			28	pF
Q_{g(on)}	} I _C = 16A, V _{GE} = 15V, V _{CE} = 0.5 • V _{CES}		97	nC
Q_{ge}			13	nC
Q_{gc}			43	nC
t_{d(on)}	} Inductive load, T_J = 25°C I _C = 16A, V _{GE} = 15V V _{CE} = 0.5 • V _{CES} , R _G = 10Ω Note 3		14	ns
t_{ri}			19	ns
E_{on}			4.75	mJ
t_{d(off)}			260	ns
t_{fi}			250	ns
E_{off}			3.90	mJ
t_{d(on)}	} Inductive load, T_J = 150°C I _C = 16A, V _{GE} = 15V V _{CE} = 0.5 • V _{CES} , R _G = 10Ω Note 3		15	ns
t_{ri}			24	ns
E_{on}			5.80	mJ
t_{d(off)}			305	ns
t_{fi}			236	ns
E_{off}			4.40	mJ
R_{thJC}			0.83 °C/W	
R_{thCS}		0.15	°C/W	

Reverse Diode (FRED)

(T _J = 25°C, Unless Otherwise Specified)		Characteristic Value		
Symbol	Test Conditions	Min.	Typ.	Max.
V _F	I _F = 16A, V _{GE} = 0V, Note 1 T_J = 150°C		4.8	5.0 V
I _{RM}	I _F = 16A, V _{GE} = 0V, -di _F /dt = 500A/μs, V _R = 1200V, T _J = 150°C		28	A
t _{rr}			165	ns
R _{thJC}				1.5 °C/W


Notes:

1. Pulse test, $t \leq 300\mu s$, duty cycle, $d \leq 2\%$.
2. Part must be heatsunk for high-temp lces measurement.
3. Switching times & energy losses may increase for higher V_{CE} (Clamp), T_J or R_{GS} .

ADVANCE TECHNICAL INFORMATION

The product presented herein is under development. The Technical Specifications offered are derived from a subjective evaluation of the design, based upon prior knowledge and experience, and constitute a "considered reflection" of the anticipated result. IXYS reserves the right to change limits, test conditions, and dimensions without notice.

ISOPLUS i4-Pak™ (HV) Outline



SYM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	.190	.205	4.83	5.21
A1	.102	.118	2.59	3.00
A2	.046	.085	1.17	2.16
b	.045	.055	1.14	1.40
b1	.058	.068	1.47	1.73
C	.020	.029	0.51	0.74
D	.819	.840	20.80	21.34
E	.770	.799	19.56	20.29
e	.150 BSC		3.81 BSC	
e1	.450 BSC		11.43 BSC	
L	.780	.840	19.81	21.34
L1	.083	.102	2.11	2.59
Q	.210	.244	5.33	6.20
R	.100	.180	2.54	4.57
S	.660	.690	16.76	17.53
T	.590	.620	14.99	15.75
U	.065	.080	1.65	2.03

Fig. 1. Output Characteristics @ $T_J = 25^\circ\text{C}$




Fig. 2. Extended Output Characteristics @ $T_J = 25^\circ\text{C}$




Fig. 3. Output Characteristics @ $T_J = 150^\circ\text{C}$




Fig. 4. Dependence of $V_{CE(sat)}$ on Junction Temperature




Fig. 5. Collector-to-Emitter Voltage vs. Gate-to-Emitter Voltage




Fig. 6. Input Admittance




Fig. 7. Transconductance




Fig. 8. Gate Charge




Fig. 9. Capacitance




Fig. 10. Reverse-Bias Safe Operating Area




Fig. 11. Maximum Transient Thermal Impedance (IGBT)




Fig. 12. Inductive Switching Energy Loss vs. Gate Resistance




Fig. 13. Inductive Switching Energy Loss vs. Collector Current




Fig. 14. Inductive Switching Energy Loss vs. Junction Temperature




Fig. 15. Inductive Turn-off Switching Times vs. Gate Resistance




Fig. 16. Inductive Turn-off Switching Times vs. Collector Current




Fig. 17. Inductive Turn-off Switching Times vs. Junction Temperature




Fig. 18. Inductive Turn-on Switching Times vs. Gate Resistance




Fig. 19. Inductive Turn-on Switching Times vs. Collector Current




Fig. 20. Inductive Turn-on Switching Times vs. Junction Temperature




Fig. 21. Diode Forward Characteristics




Fig. 22. Reverse Recovery Charge vs. $-di_F/dt$




Fig. 23 Reverse Recovery Current vs. $-di_F/dt$




Fig. 24. Reverse Recovery Time vs. $-di_F/dt$




Fig. 25. Dynamic Parameters Q_{RR} , I_{RR} vs. Junction Temperature





Fig. 26. Maximum Transient Thermal Impedance (Diode)





Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.