
CoolMOS™ [1] Pow er MOSFET with HiPerDyn™ FRED


Buck and Boost Topologies

I_{D25} = 47 A
V_{DSS} = 600 V
$R_{DS(on)\ max}$ = 0.045 Ω

Electrically isolated back surface
2500 V electrical isolation
N-Channel Enhancement Mode
Low R_{DSon}, high V_{DSS} MOSFET
Ultra low gate charge



ISOPLUS i4™



E72873

Features

- Silicon chip on Direct-Copper-Bond substrate
  - high power dissipation
  - isolated mounting surface
  - 2500 V electrical isolation
  - low drain to tab capacitance (< 40 pF)
- Fast CoolMOS™ [1] power MOSFET 4th generation
  - high blocking capability
  - lowest resistance
  - avalanche rated for unclamped inductive switching (UIS)
  - low thermal resistance due to reduced chip thickness
- Enhanced total power density
- HiPerDyn™ FRED
  - consisting of series connected diodes
  - enhanced dynamic behaviour for high frequency operation

Applications

- Switched mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)
- Power factor correction (PFC)

Advantages

- Easy assembly: no screws or isolation foils required
- Space savings
- High power density
- High reliability

MOSFET T

Symbol	Conditions	Maximum Ratings	
V_{DSS}	T_{VJ} = 25°C	600	V
V_{GS}		± 20	V
I_{D25}	T_C = 25°C	47	A
I_{D90}	T_C = 90°C	32	A
E_{AS}	single pulse	1950	mJ
E_{AR}	repetitive; I_D = 11 A; T_C = 25°C	3	mJ
dV/dt	MOSFET dV/dt ruggedness V_{DS} = 0...480 V	50	V/ns

Symbol	Conditions	Characteristic Values (T_{VJ} = 25°C, unless otherwise specified) min.	typ.	max.	
R_{DSon}	V_{GS} = 10 V; I_D = 44 A		40	45	mΩ
$V_{GS(th)}$	V_{DS} = V_{GS}; I_D = 3 mA	2.5	3	3.5	V
I_{DSS}	V_{DS} = V_{DSS}; V_{GS} = 0 V; T_{VJ} = 25°C			10	µA
	T_{VJ} = 125°C		50		µA
I_{GSS}	V_{GS} = ± 20 V; V_{DS} = 0 V			100	nA
C_{iss}	V_{GS} = 0 V; V_{DS} = 100 V		6800		pF
C_{oss}	f = 1 MHz		320		pF
Q_g	V_{GS} = 0 to 10 V; V_{DS} = 400 V; I_D = 44 A		150	190	nC
Q_{gs}			35		nC
Q_{gd}			50		nC
$t_{d(on)}$	V_{GS} = 10 V; V_{DS} = 400 V		30		ns
t_r	I_D = 44 A; R_G = 3.3 Ω		20		ns
$t_{d(off)}$			100		ns
t_f			10		ns
E_{on}			tbd		mJ
E_{off}			tbd		mJ
$E_{rec\ off}$			tbd		mJ
R_{thJC}				0.45	K/W
R_{thCH}	with heat transfer paste		0.25		K/W

[1] CoolMOS™ is a trademark of Infineon Technologies AG.

OBSOLETE

© 2009 IXYS All rights reserved

MOSFET T Source-Drain Diode

Symbol	Conditions	Characteristic Values (T_{VJ} = 25°C, unless otherwise specified) min.	typ.	max.	
I_S	V_{GS} = 0 V			44	A
V_{SD}	I_F = 44 A; V_{GS} = 0 V		0.9	1.2	V
t_{rr}	I_F = 44 A; -di_F/dt = 100 A/µs; V_R = 400 V		600		ns
Q_{RM}			17		µC
I_{RM}			60		A

Diode D (data for series connection)

Symbol	Conditions	Maximum Ratings	
V_{RRM}	T_{VJ} = 25°C to 150°C	600	V
I_{F25}	T_C = 25°C	95	A
I_{F90}	T_C = 90°C	56	A

Symbol	Conditions		Characteristic Values min.	typ.	max.	
V_F	I_F = 30 A	T_{VJ} = 25°C			2.48	V
	I_F = 60 A				3.02	V
	I_F = 30 A	T_{VJ} = 150°C			1.89	A
	I_F = 60 A				2.45	A
I_R	V_R = V_{RRM}	T_{VJ} = 25°C			1	µA
		T_{VJ} = 150°C			0.2	mA
I_{FSM}	t = 10 ms (50 Hz), sine;	T_{VJ} = 45°C			450	A
I_{RM}	I_F = 30 A; V_R = 100 V;	T_{VJ} = 25°C			2	A
t_{rr}	-di_F/dt = 200 A/µs				30	ns
R_{thJC}					0.55	K/W
R_{thCH}	with heat transfer paste			0.25		K/W

Component


Symbol	Conditions	Maximum Ratings	
T_{VJ}	operating	-55...+150	°C
T_{stg}	storage	-55...+125	°C
V_{ISOL}	I_{ISOL} < 1 mA; 50/60 Hz	2500	V~
F_C	mounting force with clip	20...120	N

Symbol	Conditions	Characteristic Values min.	typ.	max.	
C_P	coupling capacity between shorted pins and mounting tab in the case		40		pF
d_S, d_A	pin - pin	1.7			mm
d_S, d_A	pin - backside metal	5.5			mm
Weight			9		g

OBSOLETE

© 2009 IXYS All rights reserved

ISOPLUS i4™ Outline



OBSOLETE

© 2009 IXYS All rights reserved

OBSOLETE

OBSOLETE

IXYS
A Littelfuse Technology

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.