

HiPerFET™ Power MOSFETs


N-Channel Enhancement Mode
High dv/dt, Low t_{rr} , HDMOS™ Family

Obsolete:
IXFM42N20
IXFM50N20


~~IXFH/IXFM42N20~~
~~IXFH/IXFM/IXFT50N20~~
IXFH/IXFT58N20

V_{DSS}	I_{D25}	$R_{DS(on)}$
200 V	42 A	60mΩ
200 V	50 A	45mΩ
200 V	58 A	40mΩ


$t_{rr} \leq 200 \text{ ns}$



TO-247 AD (IXFH)




TO-268 (D3) Case Style



~~TO-204 AE (IXFM)~~

Package
unavailable



G = Gate,
S = Source,

D = Drain,
TAB = Drain

Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	$T_J = 25^\circ\text{C}$ to 150°C	200	V
V_{DGR}	$T_J = 25^\circ\text{C}$ to 150°C ; $R_{GS} = 1 \text{ M}\Omega$	200	V
V_{GS}	Continuous	± 20	V
V_{GSM}	Transient	± 30	V
I_{D25}	$T_C = 25^\circ\text{C}$	42N20	42 A
		50N20	50 A
		58N20	58 A
I_{DM}	$T_C = 25^\circ\text{C}$, pulse width limited by T_{JM}	42N20	168 A
		50N20	200 A
		58N20	232 A
I_{AR}	$T_C = 25^\circ\text{C}$	42N20	42 A
		50N20	50 A
		58N20	58 A
E_{AR}	$T_C = 25^\circ\text{C}$	30	mJ
dv/dt	$I_S \leq I_{DM}$, $di/dt \leq 100 \text{ A}/\mu\text{s}$, $V_{DD} \leq V_{DSS}$, $T_J \leq 150^\circ\text{C}$, $R_G = 2 \Omega$	5	V/ns
P_D	$T_C = 25^\circ\text{C}$	300	W
T_J		-55 ... +150	$^\circ\text{C}$
T_{JM}		150	$^\circ\text{C}$
T_{stg}		-55 ... +150	$^\circ\text{C}$
T_L	1.6 mm (0.062 in.) from case for 10 s	300	$^\circ\text{C}$
M_d	Mounting torque	1.13/10	Nm/lb.in.
Weight		TO-204 = 18 g, TO-247 = 6 g	

Symbol	Test Conditions	Characteristic Values ($T_J = 25^\circ\text{C}$, unless otherwise specified)		
		min.	typ.	max.
V_{DSS}	$V_{GS} = 0 \text{ V}$, $I_D = 250 \mu\text{A}$	200		V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, $I_D = 4 \text{ mA}$	2		V
I_{GSS}	$V_{GS} = \pm 20 \text{ V}_{DC}$, $V_{DS} = 0$			$\pm 100 \text{ nA}$
I_{DSS}	$V_{DS} = 0.8 \cdot V_{DSS}$	$T_J = 25^\circ\text{C}$		200 μA
	$V_{GS} = 0 \text{ V}$	$T_J = 125^\circ\text{C}$		1 mA

Features

- International standard packages
- Low $R_{DS(on)}$ HDMOS™ process
- Rugged polysilicon gate cell structure
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
 - easy to drive and to protect
- Fast intrinsic Rectifier

Applications

- DC-DC converters
- Synchronous rectification
- Battery chargers
- Switched-mode and resonant-mode power supplies
- DC choppers
- AC motor control
- Temperature and lighting controls
- Low voltage relays

Advantages

- Easy to mount with 1 screw (TO-247) (isolated mounting screw hole)
- High power surface mountable package
- High power density

Fig. 1 Output Characteristics




Fig. 2 Input Admittance




Fig. 3 $R_{DS(on)}$ vs. Drain Current


Fig. 4 Temperature Dependence of Drain to Source Resistance




Fig. 5 Drain Current vs. Case Temperature




Fig. 6 Temperature Dependence of Breakdown and Threshold Voltage




Fig.7 Gate Charge Characteristic Curve




Fig.8 Forward Bias Safe Operating Area




Fig.9 Capacitance Curves




Fig.10 Source Current vs. Source to Drain Voltage





Fig.11 Transient Thermal Impedance





Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.