


IXTK22N100L

1000 V, 600 mΩ, Linear™ Power MOSFET w/ Extended FBSOA

N-Channel Enhancement Mode Avalanche Rated



Features

- Designed for Linear Operation
- Avalanche Rated
- Molding Epoxy Meets UL94 V-0 Flammability Classification

Advantages

- Easy to Mount
- Space Savings
- High Power Density


Applications

- Programmable Loads
- Current Regulators
- DC-DC Converters
- Battery Chargers
- DC Choppers
- Temperature and Lighting

Product Summary

Characteristic	Value	Unit
V_{DSS}	1000	V
I_{D25}	22	A
$R_{DS(on)}$	600	mΩ

Pinout Diagram TO-264 (IXTK)



1/G: Gate; 2/D: Drain; 3/S: Source; Tab: Drain

Maximum Ratings

Symbol	Characteristic	Conditions	Value	Unit
V_{DSS}	Drain-source voltage	$T_{vj} = 25\text{ °C to }150\text{ °C}$	1000	V
V_{DGR}	Drain-gate voltage	$T_{vj} = 25\text{ °C to }150\text{ °C}, R_{GS} = 1\text{ M}\Omega$	1000	V
V_{GSS}	Gate-source voltage	Continuous	± 30	V
V_{GSM}		Transient	± 40	
I_D	Drain current	$T_c = 25\text{ °C}$	22	A
I_{DM}	Pulse drain current	$T_c = 25\text{ °C}$, pulse width limited by $T_{vj(max)}$	50	
I_A	Avalanche current	$T_c = 25\text{ °C}$	22	A
E_{AS}	Avalanche energy	$T_c = 25\text{ °C}$	1.5	J
P_D	Power dissipation	$T_c = 25\text{ °C}$	700	W
T_{vj}	Virtual junction temperature range	–	–55 to +150	°C
$T_{vj(max)}$	Maximum virtual junction temperature	–	150	
T_{stg}	Storage temperature range	–	–55 to +150	
T_L	Maximum lead temperature for soldering purposes	1.6mm (0.063 in.) from Case for 10s	300	°C
T_{sld}	Soldering temperature	Plastic Body for 10s	260	°C
M_d	Mounting torque	–	1.13/10	Nm/lb.in.
–	Weight	–	10	g

Electrical Characteristics – Static ($T_{vj} = 25\text{ °C}$ unless otherwise specified)

Symbol	Characteristic	Conditions	Value			Unit
			Min.	Typ.	Max.	
$V_{(BR)DSS}$	Drain-source breakdown voltage	$I_D = 1\text{ mA}, V_{GS} = 0\text{ V}$	1000	–	–	V
$V_{GS(th)}$	Gate threshold voltage	$I_D = 250\text{ }\mu\text{A}, V_{GS} = V_{DS}$	3.0	–	5.5	V
I_{GSS}	Gate-source leakage current	$V_{DS} = 0\text{ V}, V_{GS} = \pm 30\text{ V}$	–	–	± 200	nA
I_{DSS}	Drain-source leakage current	$V_{DS} = V_{DSS}, V_{GS} = 0\text{ V}$	–	–	50	μA
		$V_{DS} = V_{DSS}, V_{GS} = 0\text{ V}, T_{vj} = 125\text{ °C}$	–	–	1	mA
$R_{DS(on)}$	Drain-source on-resistance ¹	$V_{GS} = 20\text{ V}, I_D = 0.5 \times I_{DSS}$	–	–	600	m Ω

Note 1: Pulse test, $t \leq 300\text{ }\mu\text{s}$, duty cycle, $d \leq 2\%$

Electrical Characteristics – Dynamic ($T_{vj} = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Characteristic	Conditions	Value			Unit
			Min.	Typ.	Max.	
g_{fs}	Transconductance ¹	$V_{DS} = 20\text{ V}, I_D = 0.5 \times I_{DSS}$	4.5	7.0	9.5	S
C_{iss}	Input capacitance	$V_{GS} = 0\text{ V}, V_{DS} = 25\text{ V}, f = 1\text{ MHz}$	–	7050	–	pF
C_{oss}	Output capacitance		–	600	–	
C_{rss}	Reverse transfer capacitance		–	100	–	
$t_{d(on)}$	Turn-on delay time	Resistive Switching Times $V_{GS} = 15\text{ V}, V_{DS} = 0.5 \times V_{DSS},$ $I_D = 0.5 \times I_{DSS}, R_{G(ext)} = 2\ \Omega$	–	36	–	ns
t_r	Rise time		–	35	–	
$t_{d(off)}$	Turn-off delay time		–	80	–	
t_f	Fall time		–	50	–	
Q_G	Total gate charge	$V_{GS} = 15\text{ V}, V_{DS} = 0.5 \times V_{DSS},$ $I_D = 0.5 \times I_{DSS}$	–	270	–	nC
Q_{GS}	Gate-source charge		–	70	–	
Q_{GD}	Gate-drain charge		–	110	–	

Note 1: Pulse test, $t \leq 300\ \mu\text{s}$, duty cycle, $d \leq 2\%$

Thermal Specifications

Symbol	Characteristics	Value	Unit
$R_{th(j-c)}$	Thermal Resistance, Junction to Case	0.18	K/W
$R_{th(j-a)}$	Thermal Resistance, Junction to Ambient	0.15	K/W

Safe-Operating-Area Specification

Symbol	Conditions	Value			Unit
		Min.	Typ.	Max.	
SOA	$V_{DS} = 800\text{ V}, I_D = 0.3\text{ A}, T_C = 90^\circ\text{C}, t_p = 5\text{ s}$	240	–	–	W

Source-Drain Diode Characteristics ($T_{vj} = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Characteristic	Conditions	Value			Unit
			Min.	Typ.	Max.	
I_S	Continuous diode forward current	$V_{GS} = 0\text{ V}$	–	–	22	A
I_{SM}	Diode pulse current	Repetitive, pulse width limited by $T_{vj(max)}$	–	–	50	A
V_{SD}	Diode Forward Voltage ¹	$I_F = I_S, V_{GS} = 0\text{ V}$	–	–	1.5	V
t_{rr}	Reverse Recovery Time	$I_F = I_S, -di/dt = 100\text{ A}/\mu\text{s},$ $V_R = 100\text{ V}, V_{GS} = 0\text{ V}$	–	1000	–	ns

Note 1: Pulse test, $t \leq 300\ \mu\text{s}$, duty cycle, $d \leq 2\%$

Characteristic Curves

Fig. 1. Output Characteristics @ $T_{vj} = 25\text{ }^\circ\text{C}$




Fig. 2. Extended Output Characteristics @ $T_{vj} = 25\text{ }^\circ\text{C}$




Fig. 3. Output Characteristics @ $T_{vj} = 125\text{ }^\circ\text{C}$




Fig. 4. $R_{DS(on)}$ Normalized to $I_D = 11\text{ A}$ Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to $I_D = 11\text{ A}$ Value vs. Drain Current




Fig. 6. Maximum Drain Current vs. Case Temperature




Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Gate Charge




Fig. 11. Capacitance




Fig. 12. Maximum Transient Thermal Impedance




Fig. 13. Forward-Bias Safe Operating Area @ $T_c = 25^\circ\text{C}$






Fig. 14. Forward-Bias Safe Operating Area @ $T_c = 90^\circ\text{C}$



Part Outline Drawing (TO-264)



Symbol	Inches		Millimeters	
	Min.	Max.	Min.	Max.
A	4.82	5.13	0.190	0.202
A1	2.54	2.89	0.100	0.114
A2	2.00	2.10	0.079	0.083
b	1.12	1.42	0.044	0.056
b1	2.39	2.69	0.094	0.106
b2	2.90	3.09	0.114	0.122
c	0.53	0.83	0.021	0.033
D	25.91	26.16	1.020	1.030
E	19.81	19.96	0.780	0.786
e	5.46 BSC		0.215 BSC	
J	0.00	0.25	0.000	0.010
K	0.00	0.25	0.000	0.010
L	20.32	20.83	0.800	0.820
L1	2.29	2.59	0.090	0.102
P	3.17	3.66	0.125	0.144
Q	6.07	6.27	0.239	0.247
Q1	8.38	8.69	0.330	0.342
R	3.81	4.32	0.150	0.170
R1	1.78	2.29	0.070	0.090
S	6.04	6.30	0.238	0.248
T	1.57	1.83	0.062	0.072

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

