


**TrenchT4™**  
**Power MOSFET**
**IXTA270N04T4**  
**IXTA270N04T4-7**


$$V_{DSS} = 40V$$

$$I_{D25} = 270A$$


$$R_{DS(on)} \leq 2.2m\Omega$$

 N-Channel Enhancement Mode  
 Avalanche Rated


TO-263 AA


 G = Gate      D = Drain  
 S = Source    Tab = Drain

TO-263 (7-Leads)


 Pins: 1 - Gate  
 2, 3, 5, 6, 7 - Source  
 4 (Tab) - Drain

| Symbol     | Test Conditions                                                       | Maximum Ratings   |                  |
|------------|-----------------------------------------------------------------------|-------------------|------------------|
| $V_{DSS}$  | $T_J = 25^\circ\text{C}$ to $175^\circ\text{C}$                       | 40                | V                |
| $V_{DGR}$  | $T_J = 25^\circ\text{C}$ to $175^\circ\text{C}$ , $R_{GS} = 1M\Omega$ | 40                | V                |
| $V_{GSM}$  | Transient                                                             | $\pm 15$          | V                |
| $I_{D25}$  | $T_C = 25^\circ\text{C}$                                              | 270               | A                |
| $I_{LRMS}$ | Lead Current Limit, RMS                                               | 160               | A                |
| $I_{DM}$   | $T_C = 25^\circ\text{C}$ , Pulse Width Limited by $T_{JM}$            | 800               | A                |
| $I_A$      | $T_C = 25^\circ\text{C}$                                              | 135               | A                |
| $E_{AS}$   | $T_C = 25^\circ\text{C}$                                              | 750               | mJ               |
| $I_A$      | $T_C = 25^\circ\text{C}$                                              | 270               | A                |
| $E_{AS}$   | $T_C = 25^\circ\text{C}$                                              | 350               | mJ               |
| $P_D$      | $T_C = 25^\circ\text{C}$                                              | 375               | W                |
| $T_J$      |                                                                       | -55 ... +175      | $^\circ\text{C}$ |
| $T_{JM}$   |                                                                       | 175               | $^\circ\text{C}$ |
| $T_{stg}$  |                                                                       | -55 ... +175      | $^\circ\text{C}$ |
| $T_L$      | Maximum Lead Temperature for Soldering                                | 300               | $^\circ\text{C}$ |
| $T_{SOLD}$ | 1.6 mm (0.062in.) from Case for 10s                                   | 260               | $^\circ\text{C}$ |
| $F_C$      | Mounting Force (TO-263)                                               | 10.65 / 2.2..14.6 | N/lb             |
| Weight     | TO-263                                                                | 2.5               | g                |
|            | TO-263 (7Leads)                                                       | 3.0               | g                |

**Features**

- International Standard Packages
- $175^\circ\text{C}$  Operating Temperature
- High Current Handling Capability
- Avalanche Rated
- Low  $R_{DS(on)}$

**Advantages**

- Easy to Mount
- Space Savings
- High Power Density

**Applications**

- Synchronous Buck Converters
- High Current Switching Power Supplies
- Battery Powered Electric Motors
- Resonant-Mode Power Supplies
- Electronics Ballast Application
- Class D Audio Amplifiers

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ Unless Otherwise Specified) | Characteristic Values |      |                   |
|--------------|---------------------------------------------------------------------------|-----------------------|------|-------------------|
|              |                                                                           | Min.                  | Typ. | Max.              |
| $BV_{DSS}$   | $V_{GS} = 0V$ , $I_D = 250\mu\text{A}$                                    | 40                    |      | V                 |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 250\mu\text{A}$                                | 2.0                   |      | 4.0 V             |
| $I_{GSS}$    | $V_{GS} = \pm 15V$ , $V_{DS} = 0V$                                        |                       |      | $\pm 200$ nA      |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$ , $V_{GS} = 0V$<br>$T_J = 150^\circ\text{C}$           |                       |      | 5 $\mu\text{A}$   |
|              |                                                                           |                       |      | 750 $\mu\text{A}$ |
| $R_{DS(on)}$ | $V_{GS} = 10V$ , $I_D = 50A$ , Note 1                                     |                       |      | 2.2 m $\Omega$    |

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified)                                                                  | Characteristic Values |      |                         |
|--------------|----------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|------|-------------------------|
|              |                                                                                                                                              | Min.                  | Typ. | Max.                    |
| $g_{fs}$     | $V_{DS} = 10\text{V}$ , $I_D = 60\text{A}$ , Note 1                                                                                          | 90                    | 150  | S                       |
| $R_{Gi}$     | Gate Input Resistance                                                                                                                        |                       | 1.4  | $\Omega$                |
| $C_{iss}$    | $V_{GS} = 0\text{V}$ , $V_{DS} = 25\text{V}$ , $f = 1\text{MHz}$                                                                             |                       | 9140 | pF                      |
| $C_{oss}$    |                                                                                                                                              |                       | 1450 | pF                      |
| $C_{rss}$    |                                                                                                                                              |                       | 980  | pF                      |
| $t_{d(on)}$  | <b>Resistive Switching Times</b><br>$V_{GS} = 10\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 135\text{A}$<br>$R_G = 2\Omega$ (External) |                       | 18   | ns                      |
| $t_r$        |                                                                                                                                              |                       | 28   | ns                      |
| $t_{d(off)}$ |                                                                                                                                              |                       | 72   | ns                      |
| $t_f$        |                                                                                                                                              |                       | 23   | ns                      |
| $Q_{g(on)}$  | $V_{GS} = 10\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 0.5 \cdot I_{D25}$                                                             |                       | 182  | nC                      |
| $Q_{gs}$     |                                                                                                                                              |                       | 45   | nC                      |
| $Q_{gd}$     |                                                                                                                                              |                       | 67   | nC                      |
| $R_{thJC}$   |                                                                                                                                              |                       |      | 0.40 $^\circ\text{C/W}$ |

#### Source-Drain Diode

| Symbol   | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified)                            | Characteristic Values |      |        |
|----------|--------------------------------------------------------------------------------------------------------|-----------------------|------|--------|
|          |                                                                                                        | Min.                  | Typ. | Max.   |
| $I_S$    | $V_{GS} = 0\text{V}$                                                                                   |                       |      | 270 A  |
| $I_{SM}$ | Repetitive, Pulse width limited by $T_{JM}$                                                            |                       |      | 1080 A |
| $V_{SD}$ | $I_F = 100\text{A}$ , $V_{GS} = 0\text{V}$ , Note 1                                                    |                       |      | 1.4 V  |
| $t_{rr}$ | $I_F = 150\text{A}$ , $V_{GS} = 0\text{V}$<br>$-di/dt = 100\text{A}/\mu\text{s}$<br>$V_R = 30\text{V}$ |                       | 48   | ns     |
| $I_{RM}$ |                                                                                                        |                       | 1.8  | A      |
| $Q_{RM}$ |                                                                                                        |                       | 43   | nC     |

- Notes: 1. Pulse test,  $t \leq 300\mu\text{s}$ , duty cycle,  $d \leq 2\%$ .  
 2. On through-hole packages,  $R_{DS(on)}$  Kelvin test contact location must be 5mm or less from the package body.


#### PRELIMINARY TECHNICAL INFORMATION

The product presented herein is under development. The Technical Specifications offered are derived from a subjective evaluation of the design, based upon prior knowledge and experience, and constitute a "considered reflection" of the anticipated result. IXYS reserves the right to change limits, test conditions, and dimensions without notice.


IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,931,844 5,049,961 5,237,481 6,162,665 6,404,065 B1 6,683,344 6,727,585 7,005,734 B2 7,157,338B2  
 4,860,072 5,017,508 5,063,307 5,381,025 6,259,123 B1 6,534,343 6,710,405 B2 6,759,692 7,063,975 B2  
 4,881,106 5,034,796 5,187,117 5,486,715 6,306,728 B1 6,583,505 6,710,463 6,771,478 B2 7,071,537


**Fig. 1. Output Characteristics @  $T_J = 25^\circ\text{C}$**




**Fig. 2. Extended Output Characteristics @  $T_J = 25^\circ\text{C}$**




**Fig. 3. Output Characteristics @  $T_J = 150^\circ\text{C}$**




**Fig. 4. Normalized  $R_{DS(on)}$  to  $I_D = 135\text{A}$  Value vs. Junction Temperature**




**Fig. 5. Normalized  $R_{DS(on)}$  to  $I_D = 135\text{A}$  vs. Drain Current**




**Fig. 6. Drain Current vs. Case Temperature**




**Fig. 7. Input Admittance**




**Fig. 8. Transconductance**




**Fig. 9. Forward Voltage Drop of Intrinsic Diode**




**Fig. 10. Gate Charge**




**Fig. 11. Capacitance**




**Fig. 12. Forward-Bias Safe Operating Area**




**Fig. 13. Resistive Turn-on Rise Time vs. Junction Temperature**




**Fig. 14. Resistive Turn-on Rise Time vs. Drain Current**




**Fig. 15. Resistive Turn-on Switching Times vs. Gate Resistance**




**Fig. 16. Resistive Turn-off Switching Times vs. Junction Temperature**




**Fig. 17. Resistive Turn-off Switching Times vs. Drain Current**




**Fig. 18. Resistive Turn-off Switching Times vs. Gate Resistance**



**Fig. 19. Maximum Transient Thermal Impedance**




**TO-263 (IXTA) Outline**



| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .160     | .190 | 4.06        | 4.83  |
| A1  | .080     | .110 | 2.03        | 2.79  |
| b   | .020     | .039 | 0.51        | 0.99  |
| b2  | .045     | .055 | 1.14        | 1.40  |
| c   | .016     | .029 | 0.40        | 0.74  |
| c2  | .045     | .055 | 1.14        | 1.40  |
| D   | .340     | .380 | 8.64        | 9.65  |
| D1  | .315     | .350 | 8.00        | 8.89  |
| E   | .380     | .410 | 9.65        | 10.41 |
| E1  | .245     | .320 | 6.22        | 8.13  |
| e   | .100 BSC |      | 2.54 BSC    |       |
| L   | .575     | .625 | 14.61       | 15.88 |
| L1  | .090     | .110 | 2.29        | 2.79  |
| L2  | .040     | .055 | 1.02        | 1.40  |
| L3  | .050     | .070 | 1.27        | 1.78  |
| L4  | 0        | .005 | 0           | 0.13  |

**TO-263 (7-lead) (IXTA..7) Outline**



| SYM | INCHES   |      | MILLIMETER |       |
|-----|----------|------|------------|-------|
|     | MIN      | MAX  | MIN        | MAX   |
| A   | .170     | .185 | 4.30       | 4.70  |
| A1  | .085     | .104 | 2.15       | 2.65  |
| b   | .026     | .035 | 0.65       | 0.90  |
| c   | .016     | .024 | 0.40       | 0.60  |
| c2  | .049     | .055 | 1.25       | 1.40  |
| D   | .355     | .370 | 9.00       | 9.40  |
| D1  | .272     | .280 | 6.90       | 7.10  |
| E   | .386     | .402 | 9.80       | 10.20 |
| E1  | .311     | .319 | 7.90       | 8.10  |
| e   | .050 BSC |      | 1.27 BSC   |       |
| L   | .591     | .614 | 15.00      | 15.60 |
| L1  | .091     | .110 | 2.30       | 2.80  |
| L2  | .039     | .059 | 1.00       | 1.50  |
| L3  | .000     | .059 | 0.00       | 1.50  |



---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).