


# TrenchMV™ Power MOSFET


**IXTP55N075T**  
**IXTY55N075T**

$$\begin{aligned} V_{DSS} &= 75 \text{ V} \\ I_{D25} &= 55 \text{ A} \\ R_{DS(on)} &\leq 19.5 \text{ m}\Omega \end{aligned}$$


N-Channel Enhancement Mode  
Avalanche Rated



TO-220 (IXTP)



TO-252 (IXTY)



G = Gate  
S = Source  
D = Drain  
TAB = Drain

| Symbol     | Test Conditions                                                                                                                        | Maximum Ratings |                  |
|------------|----------------------------------------------------------------------------------------------------------------------------------------|-----------------|------------------|
| $V_{DSS}$  | $T_J = 25^\circ\text{C to } 175^\circ\text{C}$                                                                                         | 75              | V                |
| $V_{DGR}$  | $T_J = 25^\circ\text{C to } 175^\circ\text{C}; R_{GS} = 1 \text{ M}\Omega$                                                             | 75              | V                |
| $V_{GSM}$  | Transient                                                                                                                              | $\pm 20$        | V                |
| $I_{D25}$  | $T_C = 25^\circ\text{C}$                                                                                                               | 55              | A                |
| $I_L$      | Package Current Limit, RMS TO-252                                                                                                      | 25              | A                |
| $I_{DM}$   | $T_C = 25^\circ\text{C}$ , pulse width limited by $T_{JM}$                                                                             | 150             | A                |
| $I_{AR}$   | $T_C = 25^\circ\text{C}$                                                                                                               | 10              | A                |
| $E_{AS}$   | $T_C = 25^\circ\text{C}$                                                                                                               | 250             | mJ               |
| $dv/dt$    | $I_S \leq I_{DM}$ , $di/dt \leq 100 \text{ A}/\mu\text{s}$ , $V_{DD} \leq V_{DSS}$<br>$T_J \leq 175^\circ\text{C}$ , $R_G = 18 \Omega$ | 3               | V/ns             |
| $P_D$      | $T_C = 25^\circ\text{C}$                                                                                                               | 130             | W                |
| $T_J$      |                                                                                                                                        | -55 ... +175    | $^\circ\text{C}$ |
| $T_{JM}$   |                                                                                                                                        | 175             | $^\circ\text{C}$ |
| $T_{stg}$  |                                                                                                                                        | -55 ... +175    | $^\circ\text{C}$ |
| $T_L$      | 1.6 mm (0.062 in.) from case for 10 s                                                                                                  | 300             | $^\circ\text{C}$ |
| $T_{SOLD}$ | Plastic body for 10 seconds                                                                                                            | 260             | $^\circ\text{C}$ |
| $M_d$      | Mounting torque (TO-220)                                                                                                               | 1.13 / 10       | Nm/lb.in.        |
| Weight     | TO-220                                                                                                                                 | 3               | g                |
|            | TO-252                                                                                                                                 | 0.35            | g                |

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ unless otherwise specified) | Characteristic Values |      |                       |
|--------------|---------------------------------------------------------------------------|-----------------------|------|-----------------------|
|              |                                                                           | Min.                  | Typ. | Max.                  |
| $BV_{DSS}$   | $V_{GS} = 0 \text{ V}$ , $I_D = 250 \mu\text{A}$                          | 75                    |      | V                     |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 25 \mu\text{A}$                                | 2.0                   |      | 4.0 V                 |
| $I_{GSS}$    | $V_{GS} = \pm 20 \text{ V}$ , $V_{DS} = 0 \text{ V}$                      |                       |      | $\pm 100 \text{ nA}$  |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$                                                        |                       |      | 1 $\mu\text{A}$       |
|              | $V_{GS} = 0 \text{ V}$ $T_J = 150^\circ\text{C}$                          |                       |      | 100 $\mu\text{A}$     |
| $R_{DS(on)}$ | $V_{GS} = 10 \text{ V}$ , $I_D = 0.5 I_{D25}$ , Notes 1, 2                |                       |      | 19.5 $\text{m}\Omega$ |

## Features

- Ultra-low On Resistance
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
  - easy to drive and to protect
- 175  $^\circ\text{C}$  Operating Temperature

## Advantages

- Easy to mount
- Space savings
- High power density

## Applications


- Automotive
  - Motor Drives
  - 42V Power Bus
  - ABS Systems
- DC/DC Converters and Off-line UPS
- Primary Switch for 24V and 48V Systems
- High Current Switching Applications

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ unless otherwise specified)                        | Characteristic Values |      |          |
|--------------|--------------------------------------------------------------------------------------------------|-----------------------|------|----------|
|              |                                                                                                  | Min.                  | Typ. | Max.     |
| $g_{fs}$     | $V_{DS} = 10\text{ V}; I_D = 0.5 I_{D25}, \text{ Note 1}$                                        | 16                    | 27   | S        |
| $C_{iss}$    | $V_{GS} = 0\text{ V}, V_{DS} = 25\text{ V}, f = 1\text{ MHz}$                                    |                       | 1400 | pF       |
| $C_{oss}$    |                                                                                                  |                       | 235  | pF       |
| $C_{rss}$    |                                                                                                  |                       | 123  | pF       |
| $t_{d(on)}$  | $V_{GS} = 10\text{ V}, V_{DS} = 0.5 V_{DSS}, I_D = 10\text{ A}$<br>$R_G = 18\ \Omega$ (External) |                       | 20   | ns       |
| $t_r$        |                                                                                                  |                       | 50   | ns       |
| $t_{d(off)}$ |                                                                                                  |                       | 44   | ns       |
| $t_f$        |                                                                                                  |                       | 41   | ns       |
| $Q_{g(on)}$  | $V_{GS} = 10\text{ V}, V_{DS} = 0.5 V_{DSS}, I_D = 10\text{ A}$                                  |                       | 33   | nC       |
| $Q_{gs}$     |                                                                                                  |                       | 10   | nC       |
| $Q_{gd}$     |                                                                                                  |                       | 9    | nC       |
| $R_{thJC}$   | TO-220                                                                                           | 0.5                   |      | 1.15°C/W |
| $R_{thCS}$   |                                                                                                  |                       |      | °C/W     |

## Source-Drain Diode

| Symbol   | Test Conditions<br>( $T_J = 25^\circ\text{C}$ unless otherwise specified)                          | Characteristic Values |      |       |
|----------|----------------------------------------------------------------------------------------------------|-----------------------|------|-------|
|          |                                                                                                    | Min.                  | Typ. | Max.  |
| $I_S$    | $V_{GS} = 0\text{ V}$                                                                              |                       |      | 55 A  |
| $I_{SM}$ | Repetitive                                                                                         |                       |      | 150 A |
| $V_{SD}$ | $I_F = 25\text{ A}, V_{GS} = 0\text{ V}, \text{ Note 1}$                                           |                       |      | 1.2 V |
| $t_{rr}$ | $I_F = 25\text{ A}, -di/dt = 100\text{ A}/\mu\text{s}$<br>$V_R = 40\text{ V}, V_{GS} = 0\text{ V}$ |                       | 50   | ns    |

## TO-220 (IXTP) Outline




Pins: 1 - Gate 2 - Drain  
3 - Source 4, TAB - Drain

| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .170     | .190 | 4.32        | 4.83  |
| b   | .025     | .040 | 0.64        | 1.02  |
| b1  | .045     | .065 | 1.15        | 1.65  |
| c   | .014     | .022 | 0.35        | 0.56  |
| D   | .580     | .630 | 14.73       | 16.00 |
| E   | .390     | .420 | 9.91        | 10.66 |
| e   | .100 BSC |      | 2.54 BSC    |       |
| F   | .045     | .055 | 1.14        | 1.40  |
| H1  | .230     | .270 | 5.85        | 6.85  |
| J1  | .090     | .110 | 2.29        | 2.79  |
| k   | 0        | .015 | 0           | 0.38  |
| L   | .500     | .550 | 12.70       | 13.97 |
| L1  | .110     | .230 | 2.79        | 5.84  |
| ØP  | .139     | .161 | 3.53        | 4.08  |
| Q   | .100     | .125 | 2.54        | 3.18  |

## Notes:

- Pulse test:  $t \leq 300\ \mu\text{s}$ , duty cycle  $d \leq 2\%$ ;
- On through-hole packages,  $R_{DS(on)}$  Kelvin test contact location must be 5 mm or less from the package body.

## TO-252 (IXTY) Outline



| Dim. | Millimeter |       | Inches    |       |
|------|------------|-------|-----------|-------|
|      | Min.       | Max.  | Min.      | Max.  |
| A    | 2.19       | 2.38  | 0.086     | 0.094 |
| A1   | 0.89       | 1.14  | 0.035     | 0.045 |
| A2   | 0          | 0.13  | 0         | 0.005 |
| b    | 0.64       | 0.89  | 0.025     | 0.035 |
| b1   | 0.76       | 1.14  | 0.030     | 0.045 |
| b2   | 5.21       | 5.46  | 0.205     | 0.215 |
| c    | 0.46       | 0.58  | 0.018     | 0.023 |
| c1   | 0.46       | 0.58  | 0.018     | 0.023 |
| D    | 5.97       | 6.22  | 0.235     | 0.245 |
| D1   | 4.32       | 5.21  | 0.170     | 0.205 |
| E    | 6.35       | 6.73  | 0.250     | 0.265 |
| E1   | 4.32       | 5.21  | 0.170     | 0.205 |
| e    | 2.28 BSC   |       | 0.090 BSC |       |
| e1   | 4.57 BSC   |       | 0.180 BSC |       |
| H    | 9.40       | 10.42 | 0.370     | 0.410 |
| L    | 0.51       | 1.02  | 0.020     | 0.040 |
| L1   | 0.64       | 1.02  | 0.025     | 0.040 |
| L2   | 0.89       | 1.27  | 0.035     | 0.050 |
| L3   | 2.54       | 2.92  | 0.100     | 0.115 |


## PRELIMINARY TECHNICAL INFORMATION

The product presented herein is under development. The Technical Specifications offered are derived from data gathered during objective characterizations of preliminary engineering lots; but also may yet contain some information supplied during a pre-production design evaluation. IXYS reserves the right to change limits, test conditions, and dimensions without notice.


IXYS reserves the right to change limits, test conditions, and dimensions.

|                                                                                  |           |           |           |           |              |              |              |              |              |
|----------------------------------------------------------------------------------|-----------|-----------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|
| IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: | 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665    | 6,404,065 B1 | 6,683,344    | 6,727,585    | 7,005,734 B2 |
|                                                                                  | 4,850,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343    | 6,710,405 B2 | 6,759,692    | 7,063,975 B2 |
|                                                                                  | 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505    | 6,710,463    | 6,771,478 B2 | 7,071,537    |


**Fig. 1. Output Characteristics**  
**@ 25°C**




**Fig. 2. Extended Output Characteristics**  
**@ 25°C**




**Fig. 3. Output Characteristics**  
**@ 150°C**




**Fig. 4.  $R_{DS(on)}$  Normalized to  $I_D = 27.5A$  Value**  
**vs. Junction Temperature**




**Fig. 5.  $R_{DS(on)}$  Normalized to  $I_D = 27.5A$  Value**  
**vs. Drain Current**




**Fig. 6. Maximum Drain Current vs.**  
**Case Temperature**




**Fig. 7. Input Admittance**




**Fig. 8. Transconductance**




**Fig. 9. Forward Voltage Drop of Intrinsic Diode**




**Fig. 10. Gate Charge**




**Fig. 11. Capacitance**




**Fig. 12. Maximum Transient Thermal Impedance**




**Fig. 13. Resistive Turn-on**  
**Rise Time vs. Junction Temperature**




**Fig. 14. Resistive Turn-on**  
**Rise Time vs. Drain Current**




**Fig. 15. Resistive Turn-on**  
**Switching Times vs. Gate Resistance**




**Fig. 16. Resistive Turn-off**  
**Switching Times vs. Junction Temperature**



**Fig. 17. Resistive Turn-off**  
**Switching Times vs. Drain Current**



**Fig. 18. Resistive Turn-off**  
**Switching Times vs. Gate Resistance**





---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).