



RESISTANCE @ +25°C = 500 Ω ± 10%  
 RESISTANCE/TEMPERATURE CURVE = "F"  
 TEMPERATURE COEFFICIENT @ +25°C = -3.86%/°C NOMINAL  
 BETA "β" (0 TO +50°C) = 3,419°K NOMINAL  
 DISSIPATION CONSTANT = 3 mW/°C NOMINAL (STILL AIR)  
 THERMAL TIME CONSTANT = 8 SECONDS MAXIMUM (STILL AIR)  
 THERMAL TIME CONSTANT = 2 SECONDS MAXIMUM (WELL STIRRED OIL)  
 MAXIMUM TEMPERATURE RATING = +300°C

"A"	LEAD WIRE GAUGE WAS 20 AWG	12/08/03	DD
---	ISO RELEASE	12/08/03	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	© COPYRIGHT <b>U.S. SENSOR CORP.</b> 714-639-1000 www.ussensor.com <b>NTC THERMISTOR</b> P/N 501FH1K
DRAWN BY	DAN DANKERT	
DATE	10/02/02	
REV.	"A"	
LAYER	0 OF 1	