




RESISTANCE @ +25°C = 2,000  $\Omega$   $\pm$  10%  
 RESISTANCE/TEMPERATURE CURVE = SEE GS202F1K R-T TABLE  
 BETA " $\beta$ " (+25 TO +50°C) = 3,470°K NOMINAL  
 BETA " $\beta$ " (+25 TO +85°C) = 3,518°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25°C = -3.92%/°C NOMINAL  
 DISSIPATION CONSTANT = 0.7 mW/°C NOMINAL (AIR)  
 THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (AIR)  
 MAXIMUM TEMPERATURE RATING = +300°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

|      |                       |          |     |
|------|-----------------------|----------|-----|
|      |                       |          |     |
| NONE | RELEASE TO PRODUCTION | 03/18/14 | DD  |
| REV  | REVISION RECORD       | DATE     | APP |

|          |             |                                                                                                                                           |  |
|----------|-------------|-------------------------------------------------------------------------------------------------------------------------------------------|--|
| SCALE    | NONE        | U.S. SENSOR CORP.<br>© COPYRIGHT<br>714-639-1000 <a href="http://www.ussensor.com">www.ussensor.com</a><br>NTC THERMISTOR<br>P/N GS202F1K |  |
| DRAWN BY | DAN DANKERT |                                                                                                                                           |  |
| DATE     | 03/18/14    |                                                                                                                                           |  |
| REV.     | NONE        |                                                                                                                                           |  |
| LAYER    | 0 OF 2      |                                                                                                                                           |  |