HiPerFRED


V_{RRM} = 400 V
I_{FAV} = 2x 10 A
t_{rr} = 45 ns

High Performance Fast Recovery Diode
Low Loss and Soft Recovery
Common Cathode


Part number

DPG20C400PC

Marking on Product: DPG20C400PC



Backside: cathode



Features / Advantages:

- Planar passivated chips
- Very low leakage current
- Very short recovery time
- Improved thermal behaviour
- Very low Irm-values
- Very soft recovery behaviour
- Avalanche voltage rated for reliable operation
- Soft reverse recovery for low EMI/RFI
- Low Irm reduces:
  - Power dissipation within the diode
  - Turn-on loss in the commutating switch

Applications:

- Antiparallel diode for high frequency switching devices
- Antisaturation diode
- Snubber diode
- Free wheeling diode
- Rectifiers in switch mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)

Package: TO-263 (D2Pak)

- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0

OBSOLETE

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

© 2019 IXYS all rights reserved

Fast Diode


Symbol	Definition	Conditions		Ratings min.	typ.	max.	Unit
V_{RSM}	*max. non-repetitive reverse blocking voltage*		T_{VJ} = 25°C			400	V
V_{RRM}	*max. repetitive reverse blocking voltage*		T_{VJ} = 25°C			400	V
I_R	*reverse current, drain current*	V_R = 400 V	T_{VJ} = 25°C			1	µA
		V_R = 400 V	T_{VJ} = 150°C			0.15	mA
V_F	*forward voltage drop*	I_F = 10 A	T_{VJ} = 25°C			1.32	V
		I_F = 20 A				1.51	V
		I_F = 10 A	T_{VJ} = 150°C			1.03	V
		I_F = 20 A				1.24	V
I_{FAV}	*average forward current*	T_C = 150°C	T_{VJ} = 175°C			10	A
		rectangular d = 0.5					
V_{F0}	*threshold voltage* } *for power loss calculation only*		T_{VJ} = 175°C			0.77	V
r_F	*slope resistance* }					19.8	mΩ
R_{thJC}	*thermal resistance junction to case*					2.3	K/W
R_{thCH}	*thermal resistance case to heatsink*				0.25		K/W
P_{tot}	*total power dissipation*		T_C = 25°C			65	W
I_{FSM}	*max. forward surge current*	t = 10 ms; (50 Hz), sine; V_R = 0 V	T_{VJ} = 45°C			150	A
C_J	*junction capacitance*	V_R = 200 V f = 1 MHz	T_{VJ} = 25°C		12		pF
I_{RM}	*max. reverse recovery current*		T_{VJ} = 25°C		4		A
		I_F = 10 A; V_R = 270 V	T_{VJ} = 125°C		6		A
t_{rr}	*reverse recovery time*	$-di_F/dt$ = 200 A/µs	T_{VJ} = 25°C		45		ns
			T_{VJ} = 125°C		65		ns

OBSOLETE

© 2019 IXYS all rights reserved

Package TO-263 (D2Pak)			Ratings			
Symbol	**Definition**	**Conditions**	**min.**	**typ.**	**max.**	**Unit**
I_{RMS}	*RMS current*	per terminal			35	A
T_{VJ}	*virtual junction temperature*		-55		175	°C
T_{op}	*operation temperature*		-55		150	°C
T_{stg}	*storage temperature*		-55		150	°C
Weight				1.5		g
F_C	*mounting force with clip*		20		60	N

Product Marking



Part description


D = Diode
P = HiPerFRED
G = extreme fast
20 = Current Rating [A]
C = Common Cathode
400 = Reverse Voltage [V]
PC = TO-263AB (D2Pak) (2)

Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	DPG20C400PC-TRL	DPG20C400PC	Tape & Reel	800	507327
Alternative	DPG20C400PC-TUB	DPG20C400PC	Tube	50	525092

Similar Part	Package	Voltage class
DPG20C400PB	TO-220AB (3)	400
DPG20C400PN	TO-220ABFP (3)	400

Equivalent Circuits for Simulation

** on die level* $T_{VJ} = 175°C$




		Fast Diode	
$V_{0\,max}$	*threshold voltage*	0.77	V
$R_{0\,max}$	*slope resistance **	16.6	mΩ

OBSOLETE


© 2019 IXYS all rights reserved

Outlines TO-263 (D2Pak)



Dim.	Millimeter		Inches	
	min	max	min	max
A	4.06	4.83	0.160	0.190
A1	typ. 0.10		typ. 0.004	
A2	2.41		0.095	
b	0.51	0.99	0.020	0.039
b2	1.14	1.40	0.045	0.055
c	0.40	0.74	0.016	0.029
c2	1.14	1.40	0.045	0.055
D	8.38	9.40	0.330	0.370
D1	8.00	8.89	0.315	0.350
D2	2.5		0.098	
E	9.65	10.41	0.380	0.410
E1	6.22	8.50	0.245	0.335
e	2,54 BSC		0,100 BSC	
e1	4.28		0.169	
H	14.61	15.88	0.575	0.625
L	1.78	2.79	0.070	0.110
L1	1.02	1.68	0.040	0.066
W	typ. 0.02	0.040	typ. 0.0008	0.002

All dimensions conform with and/or within JEDEC standard.



OBSOLETE

© 2019 IXYS all rights reserved

Fast Diode




Fig. 1 Forward current I_F versus V_F




Fig. 2 Typ. reverse recov. charge Q_{rr} versus $-di_F/dt$




Fig. 3 Typ. reverse recov. current I_{RM} versus $-di_F/dt$




Fig. 4 Typ. dynamic parameters Q_{rr}, I_{RM} versus T_{VJ}




Fig. 5 Typ. reverse recov. time t_{rr} versus $-di_F/dt$




Fig. 6 Typ. forward recov. voltage V_{FR} and t_{fr} versus di_F/dt




Fig. 7 Typ. recovery energy E_{rec} versus $-di_F/dt$




Fig. 8 Transient thermal resistance junction to case

OBSOLETE

© 2019 IXYS all rights reserved