preliminary

Sonic Fast Recovery Diode


V_{RRM} = 1200 V
I_{DAV} = 34 A
t_{rr} = 150 ns

High Performance Fast Recovery Diode
Low Loss and Soft Recovery
1~ Rectifier Bridge

Part number


DHG40B1200LB

Marking on Product: DHG40B1200LB



Backside: isolated

E72873



Features / Advantages:

- Planar passivated chips
- Very low leakage current
- Very short recovery time
- Improved thermal behaviour
- Very low Irm-values
- Very soft recovery behaviour
- Avalanche voltage rated for reliable operation
- Soft reverse recovery for low EMI/RFI
- Low Irm reduces:
  - Power dissipation within the diode
  - Turn-on loss in the commutating switch

Applications:

- Antiparallel diode for high frequency switching devices
- Antisaturation diode
- Snubber diode
- Free wheeling diode
- Rectifiers in switch mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)

Package: SMPD

- Isolation Voltage: 3000 V~
- Industry convenient outline
- RoHS compliant
- Epoxy meets UL 94V-0
- Soldering pins for PCB mounting
- Backside: DCB ceramic
- Reduced weight
- Advanced power cycling

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

© 2019 IXYS all rights reserved

Fast Diode


Symbol	Definition	Conditions		Ratings min.	typ.	max.	Unit
V_{RSM}	*max. non-repetitive reverse blocking voltage*		T_{VJ} = 25°C			1200	V
V_{RRM}	*max. repetitive reverse blocking voltage*		T_{VJ} = 25°C			1200	V
I_R	*reverse current, drain current*	V_R = 1200 V	T_{VJ} = 25°C			40	µA
		V_R = 1200 V	T_{VJ} = 125°C			0.4	mA
V_F	*forward voltage drop*	I_F = 20 A	T_{VJ} = 25°C			2.24	V
		I_F = 40 A				2.89	V
		I_F = 20 A	T_{VJ} = 125°C			2.24	V
		I_F = 40 A				3.15	V
I_{DAV}	*bridge output current*	T_C = 80°C	T_{VJ} = 150°C			34	A
		rectangular d = 0.5					
V_{F0}	*threshold voltage* } *for power loss calculation only*		T_{VJ} = 150°C			1.35	V
r_F	*slope resistance* }					43	mΩ
R_{thJC}	*thermal resistance junction to case*					1.5	K/W
R_{thCH}	*thermal resistance case to heatsink*				0.50		K/W
P_{tot}	*total power dissipation*		T_C = 25°C			80	W
I_{FSM}	*max. forward surge current*	t = 10 ms; (50 Hz), sine; V_R = 0 V	T_{VJ} = 45°C			150	A
C_J	*junction capacitance*	V_R = 600 V f = 1 MHz	T_{VJ} = 25°C		8		pF
I_{RM}	*max. reverse recovery current*		T_{VJ} = 25°C		15		A
		I_F = 15 A; V_R = 600 V	T_{VJ} = 125°C		20		A
t_{rr}	*reverse recovery time*	$-di_F/dt$ = 600 A/µs	T_{VJ} = 25°C		150		ns
			T_{VJ} = 125°C		250		ns

OBSOLETE

© 2019 IXYS all rights reserved

preliminary

Package SMPD				Ratings			
Symbol	**Definition**	**Conditions**		**min.**	**typ.**	**max.**	**Unit**
I_{RMS}	*RMS current*	per terminal				100	A
T_{VJ}	*virtual junction temperature*			-55		150	°C
T_{op}	*operation temperature*			-55		125	°C
T_{stg}	*storage temperature*			-55		150	°C
Weight					8.5		g
F_C	*mounting force with clip*			40		130	N
$d_{Spp/App}$	*creepage distance on surface | striking distance through air*		*terminal to terminal*	1.6			mm
$d_{Spb/Apb}$			*terminal to backside*	4.0			mm
V_{ISOL}	*isolation voltage*	t = 1 second	50/60 Hz, RMS; I_{ISOL} ≤ 1 mA	3000			V
		t = 1 minute		2500			V




Part description

D = Diode
H = Sonic Fast Recovery Diode
G = extreme fast
40 = Current Rating [A]
B = 1~ Rectifier Bridge
1200 = Reverse Voltage [V]
LB = SMPD-B

Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	DHG40B1200LB-TUB	DHG40B1200LB	Tube	20	525198
Alternative	DHG40B1200LB-TRR	DHG40B1200LB	Tape & Reel	200	524922

Equivalent Circuits for Simulation

** on die level* T_{VJ} = 150 °C




		Fast Diode	
$V_{0\ max}$	*threshold voltage*	1.35	V
$R_{0\ max}$	*slope resistance **	41	mΩ


OBSOLETE

© 2019 IXYS all rights reserved

Outlines SMPD



Notes:
1) potrusion may add 0.2 mm max. on each side
2) additional max. 0.05 mm per side by punching misalignement or overlap of dam bar or bending compression
3) DCB area 10 to 50 µm convex; position of DCB area in relation to plastic rim: ±25 µm (measured 2 mm from Cu rim)
4) terminal plating: 0.2 - 1 µm Ni + 10 - 25 µm Sn (gal v.) cutting edges may be partially free of plating



OBSOLETE

© 2019 IXYS all rights reserved