

Fast Recovery Epitaxial Diode (FRED)

I_{FAVM} = 2x 91 A
V_{RRM} = 1200 V
t_{rr} = 40 ns

Part number

DSEI 2x 101-12P





OBSOLETE

Features / Advantages:

- 2 independent FRED in 1 package
- Planar passivated chips
- Very short recovery time
- Leads suitable for PC board soldering
- Very short recovery time
- Soft recovery behaviour
- Easy to mount with two screws
- Space and weight savings
- Improved temperature and power cycling capability
- Low noise switching
- Small and light weight

Applications:

- Antiparallel diode for high frequency switching devices
- Anti saturation diode
- Snubber diode
- Free wheeling diode in converters and motor control circuits
- Rectifiers in switch mode power supplies (SMPS)
- Inductive heating and melting
- Uninterruptible power supplies (UPS)
- Ultrasonic cleaners and welders

Package: ECO-PAC2

- Isolation voltage: 3000 V~
- Industry standard outline
- RoHS compliant
- Soldering pins for PCB mounting
- Height: 9 mm
- Base plate: DCB ceramic
- Reduced weight
- Advanced power cycling

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

© 2022 IXYS all rights reserved


Diode				Ratings			
Symbol	**Definitions**	**Conditions**		**min.**	**typ.**	**max.**	
I_{FRMS}	*RMS forward current*		$T_{VJ} = T_{VJM}$			130	A
I_{FAVM} ①	*max. average forward current*	rectangular, d = 0.5	T_C = 50°C			91	A
I_{FRM}	*max. repetitive forward current*	t_p < 10 µs rep. rating, pulse width limited by T_{VJM}				tbd	A
I_{FSM}	*max. surge forward current*	t = 10 ms (50 Hz), sine	T_{VJ} = 45°C			900	A
P_{tot}	*total power dissipation*		T_{VJ} = 25°C			250	W
I_R	*reverse current*	$V_R = V_{RRM}$ $V_R = 0.8 \cdot V_{RRM}$ $V_R = 0.8 \cdot V_{RRM}$	T_{VJ} = 25°C T_{VJ} = 25°C T_{VJ} = 125°C			3.0 1.5 15	mA mA mA
V_F	*forward voltage*	I_F = 100 A	T_{VJ} = 150°C T_{VJ} = 25°C			1.61 1.87	V V
V_{T0} r_T	*threshold voltage* *slope resistance*	for power-loss calculations only	$T_{VJ} = T_{VJM}$			1.01 6.1	V mΩ
R_{thJC} R_{thCH}	*thermal resistance junction to case* *thermal resistance junction to heatsink*				 0.05	0.5	K/W K/W
t_{rr}	*reverse recovery time*	I_F = 1 A; -di/dt = 400 A/µs; V_R = 30 V	T_{VJ} = 25°C		40	60	ns
I_{RM}	*max. reverse recovery current*	I_F = 75 A; $-di_F/dt$ = 200 A/µs V_R = 100 V; L ≤ 0.05 µH	T_{VJ} = 100°C		24	30	A


① I_{FAVM} rating includes reverse blocking losses at T_{VJM}, $V_R = 0.8\ V_{RRM}$, duty cycle d = 0.5

OBSOLETE

© 2022 IXYS all rights reserved

Package	ECO-PAC2			Ratings			
Symbol	**Definitions**	**Conditions**		**min.**	**typ.**	**max.**	
I_{RMS}	*RMS current*	per terminal				100	A
T_{VJ} T_{op} T_{stg}	*virtual junction temperature* *operation temperature* *storage temperature*			-40 -40 -40		150 125 125	°C °C °C
Weight					24		g
M_D	*mounting torque*			1.4		2.0	Nm
$d_{Spp/App}$ $d_{Spb/Apb}$	*creepage distance on surface | striking distance through air*		terminal to terminal terminal to backside	6.0 10.0			mm mm
V_{ISOL}	*isolation voltage*	t = 1 second t = 1 minute	50/60 Hz, RMS; $I_{ISOL} \leq 1$ mA	3000 2500			V V





OBSOLETE

© 2022 IXYS all rights reserved

Curves




Fig. 1 Forward current I_F versus V_F




Fig. 2 Typ. reverse recov. charge Q_{rr} versus $-di_F/dt$




Fig. 3 Typ. peak reverse current I_{rr} versus $-di_F/dt$




Fig. 4 Dyn. parameters Q_r, I_{RM} versus T_{VJ}




Fig. 5 Typ. recovery time t_{rr} versus $-di_F/dt$




Fig. 6 Typ. peak forward voltage V_{FR} and t_{fr} versus di_F/dt




Fig. 7 Transient thermal impedance junction to case

Constants for Z_{thJC} calculation:

i	R_{thi} [K/W]	t_i [s]
1	0.020	0.00002
2	0.050	0.00081
3	0.076	0.01000
4	0.240	0.09400
5	0.114	0.45000

OBSOLETE

© 2022 IXYS all rights reserved