
HiPerFRED²

V_{RRM}	=	400 V
I_{FAV}	= 2x	30 A
t_{rr}	=	45 ns


High Performance Fast Recovery Diode
Low Loss and Soft Recovery
Common Cathode

Part number

DPG60C400HB



Backside: cathode



Features / Advantages:

- Planar passivated chips
- Very low leakage current
- Very short recovery time
- Improved thermal behaviour
- Very low Irm-values
- Very soft recovery behaviour
- Avalanche voltage rated for reliable operation
- Soft reverse recovery for low EMI/RFI
- Low Irm reduces:
  - Power dissipation within the diode
  - Turn-on loss in the commutating switch

Applications:

- Antiparallel diode for high frequency switching devices
- Antisaturation diode
- Snubber diode
- Free wheeling diode
- Rectifiers in switch mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)

Package: TO-247

- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0

OBSOLETE

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

© 2020 IXYS all rights reserved

Fast Diode


Symbol	Definition	Conditions		Ratings min.	typ.	max.	Unit
V_{RSM}	*max. non-repetitive reverse blocking voltage*		T_{VJ} = 25°C			400	V
V_{RRM}	*max. repetitive reverse blocking voltage*		T_{VJ} = 25°C			400	V
I_R	*reverse current, drain current*	V_R = 400 V	T_{VJ} = 25°C			1	µA
		V_R = 400 V	T_{VJ} = 150°C			0.2	mA
V_F	*forward voltage drop*	I_F = 30 A	T_{VJ} = 25°C			1.41	V
		I_F = 60 A				1.69	V
		I_F = 30 A	T_{VJ} = 150°C			1.13	V
		I_F = 60 A				1.46	V
I_{FAV}	*average forward current*	T_C = 135°C	T_{VJ} = 175°C			30	A
		rectangular d = 0.5					
V_{F0}	*threshold voltage* } *for power loss calculation only*		T_{VJ} = 175°C			0.76	V
r_F	*slope resistance* }					10.7	mΩ
R_{thJC}	*thermal resistance junction to case*					0.95	K/W
R_{thCH}	*thermal resistance case to heatsink*				0.3		K/W
P_{tot}	*total power dissipation*		T_C = 25°C			160	W
I_{FSM}	*max. forward surge current*	t = 10 ms; (50 Hz), sine; V_R = 0 V	T_{VJ} = 45°C			360	A
C_J	*junction capacitance*	V_R = 200 V f = 1 MHz	T_{VJ} = 25°C		39		pF
I_{RM}	*max. reverse recovery current*		T_{VJ} = 25°C		4		A
		I_F = 30 A; V_R = 270 V	T_{VJ} = 125°C		8.5		A
t_{rr}	*reverse recovery time*	$-di_F/dt$ = 200 A/µs	T_{VJ} = 25°C		45		ns
			T_{VJ} = 125°C		85		ns

OBSOLETE

© 2020 IXYS all rights reserved

Package TO-247			Ratings			
Symbol	**Definition**	**Conditions**	**min.**	**typ.**	**max.**	**Unit**
I_{RMS}	*RMS current*	per terminal [1]			50	A
T_{VJ}	*virtual junction temperature*		-55		175	°C
T_{op}	*operation temperature*		-55		150	°C
T_{stg}	*storage temperature*		-55		150	°C
Weight				6		g
M_D	*mounting torque*		0.8		1.2	Nm
F_C	*mounting force with clip*		20		120	N

Product Marking



Part description


D = Diode
P = HiPerFRED
G = extreme fast
60 = Current Rating [A]
C = Common Cathode
400 = Reverse Voltage [V]
HB = TO-247AD (3)

Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	DPG60C400HB	DPG60C400HB	Tube	30	505825

Similar Part	Package	Voltage class
DPG60C400QB	TO-3P (3)	400
DPG80C400HB	TO-247AD (3)	400

Equivalent Circuits for Simulation

** on die level* $T_{VJ} = 175°C$




		Fast Diode	
$V_{0\,max}$	*threshold voltage*	0.76	V
$R_{0\,max}$	*slope resistance **	8.1	mΩ

OBSOLETE


© 2020 IXYS all rights reserved

Outlines TO-247



Sym.	Inches		Millimeter	
	min.	max.	min.	max.
A	0.185	0.209	4.70	5.30
A1	0.087	0.102	2.21	2.59
A2	0.059	0.098	1.50	2.49
D	0.819	0.845	20.79	21.45
E	0.610	0.640	15.48	16.24
E2	0.170	0.216	4.31	5.48
e	0.215 BSC		5.46 BSC	
L	0.780	0.800	19.80	20.30
L1	-	0.177	-	4.49
Ø P	0.140	0.144	3.55	3.65
Q	0.212	0.244	5.38	6.19
S	0.242 BSC		6.14 BSC	
b	0.039	0.055	0.99	1.40
b2	0.065	0.094	1.65	2.39
b4	0.102	0.135	2.59	3.43
c	0.015	0.035	0.38	0.89
D1	0.515	-	13.07	-
D2	0.020	0.053	0.51	1.35
E1	0.530	-	13.45	-
Ø P1	-	0.29	-	7.39

OBSOLETE



© 2020 IXYS all rights reserved

Fast Diode




Fig. 1 Forward current I_F versus V_F




Fig. 2 Typ. reverse recov. charge Q_{rr} versus -di$_F$/dt




Fig. 3 Typ. reverse recovery current I_{RR} versus -di$_F$/dt




Fig. 4 Typ. dynamic parameters Q_{rr}, I_{RR} versus T_{VJ}




Fig. 5 Typ. reverse recov. time t_{rr} versus -di$_F$/dt




Fig. 6 Typ. forward recov. voltage V_{FR} & time t_{fr} versus di$_F$/dt




Fig. 7 Typ. recovery energy E_{rec} versus -di$_F$/dt




Fig. 8 Transient thermal impedance junction to case

OBSOLETE

© 2020 IXYS all rights reserved