

preliminary

HiPerFRED


V_{RRM}	=	600 V
I_{FAV}	=	6 A
t_{rr}	=	15 ns

High Performance Fast Recovery Diode
 Low Loss and Soft Recovery
 Single Diode


Part number

DSEP6-06BS

Marking on Product: P6QGUI



Backside: cathode



Features / Advantages:

- Planar passivated chips
- Very low leakage current
- Very short recovery time
- Improved thermal behaviour
- Very low I_{rm} -values
- Very soft recovery behaviour
- Avalanche voltage rated for reliable operation
- Soft reverse recovery for low EMI/RFI
- Low I_{rm} reduces:
 - Power dissipation within the diode
 - Turn-on loss in the commutating switch

Applications:

- Antiparallel diode for high frequency switching devices
- Antisaturation diode
- Snubber diode
- Free wheeling diode
- Rectifiers in switch mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)

Package: TO-252 (DPak)


- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

Fast Diode				Ratings				
Symbol	Definition	Conditions		min.	typ.	max.	Unit	
V _{RSM}	max. non-repetitive reverse blocking voltage	T _{VJ} = 25°C				600	V	
V _{RRM}	max. repetitive reverse blocking voltage	T _{VJ} = 25°C				600	V	
I _R	reverse current, drain current	V _R = 600 V	T _{VJ} = 25°C			50	μA	
		V _R = 600 V	T _{VJ} = 150°C			0.2	mA	
V _F	forward voltage drop	I _F = 6 A	T _{VJ} = 25°C			2.66	V	
		I _F = 12 A				3.30	V	
		I _F = 6 A	T _{VJ} = 150°C			1.77	V	
		I _F = 12 A				2.29	V	
I _{FAV}	average forward current	T _C = 140°C rectangular d = 0.5	T _{VJ} = 175°C			6	A	
V _{F0}	threshold voltage	} for power loss calculation only		T _{VJ} = 175°C		1.13	V	
r _F	slope resistance					76	mΩ	
R _{thJC}	thermal resistance junction to case					2.8	K/W	
R _{thCH}	thermal resistance case to heatsink				0.50		K/W	
P _{tot}	total power dissipation	T _C = 25°C				55	W	
I _{FSM}	max. forward surge current	t = 10 ms; (50 Hz), sine; V _R = 0 V		T _{VJ} = 45°C		40	A	
C _J	junction capacitance	V _R = 400 V f = 1 MHz		T _{VJ} = 25°C		5	pF	
I _{RM}	max. reverse recovery current	} I _F = 6 A; V _R = 300 V -di _F /dt = 200 A/μs		T _{VJ} = 25 °C		1.5	A	
				T _{VJ} = 100 °C		3	A	
t _{rr}	reverse recovery time			T _{VJ} = 25 °C		15	ns	
				T _{VJ} = 100 °C		60	ns	

Package TO-252 (DPak)			Ratings			
Symbol	Definition	Conditions	min.	typ.	max.	Unit
I_{RMS}	RMS current	per terminal			20	A
T_{VJ}	virtual junction temperature		-55		175	°C
T_{op}	operation temperature		-55		150	°C
T_{stg}	storage temperature		-55		150	°C
Weight	Product Marking			0.3		g
F_c	mounting force with clip		20		60	N




Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	DSEP6-06BS-TRL	P6QGUI	Tape & Reel	2500	502162
Alternative	DSEP6-06BS-TUB	P6QGUI	Tube	70	525000

Similar Part	Package	Voltage class
DSEP6-06AS	TO-252AA (DPak)	600

Equivalent Circuits for Simulation

* on die level

 $T_{VJ} = 175^{\circ}\text{C}$

Fast Diode
 $V_{0\max}$ threshold voltage

1.13

V

 $R_{0\max}$ slope resistance *

73

mΩ

