


### DUR60120W




#### Description

Littelfuse DUR series Ultrafast Recovery Rectifier is designed to meet the general requirements of commercial applications by providing low  $T_{rr}$ , high-temperature, low-leakage and low forward voltage drop products. It is suitable for output rectifier, free-wheeling or boost diode in high-frequency power switching application such as switch mode power supply and DC-DC converters.

#### Features

- Ultra-fast switching
- Low reverse leakage current
- High surge current capability
- Low forward voltage drop
- Single die in two-leaded TO-247AC package
- Pb-free E3 means 2nd level interconnect is Pb-free and the terminal finish material is tin(Sn) (IPC/JEDEC J-STD-609A.01)

#### Circuit Diagram



#### Applications

- Output rectifiers in switch mode power supplies (SMPS) and DC to DC converters
- Free-wheeling diode or boost diode in converters and motor control circuits
- Anti-parallel diode for high frequency switching devices such as IGBT
- Uninterruptible Power Supplies (UPS)
- Inductive heating and melting
- Ultrasonic cleaners and welders

#### Maximum Ratings

Characteristics	Symbol	Conditions	Max.	Unit
Peak Inverse Voltage	$V_{RWM}$	-	1200	V
Average Rectified Forward Current (Per Device)	$I_{F(AV)}$	50% duty cycle @ $T_c = 90^\circ\text{C}$ , rectangular wave form	60	A
Peak One Cycle Non-Repetitive Surge Current (Per Leg)	$I_{FSM}$	8.3 ms, half sine pulse	280	A

#### Electrical Characteristics

Characteristics	Symbol	Conditions	Typ.	Max.	Unit
Forward Voltage Drop (Per Leg) <sup>1</sup>	$V_{F1}$	@ 60A, Pulse, $T_J = 25^\circ\text{C}$	-	3.5	V
Reverse Current (Per Leg) <sup>1</sup>	$I_{R1}$	@ $V_R = \text{Rated } V_R, T_J = 25^\circ\text{C}$	2.5	650	$\mu\text{A}$
	$I_{R2}$	@ $V_R = \text{Rated } V_R, T_J = 125^\circ\text{C}$	1.4	8	mA
Reverse Recovery Time (Per Leg)	$t_{rr1}$	$I_F = 500\text{mA}, I_R = 1\text{A}, \text{and } I_{rm} = 250\text{mA}$	-	100	ns

Footnote <sup>1</sup>: Pulse Width < 300 $\mu\text{s}$ , Duty Cycle < 2%

### Thermal-Mechanical Specifications

Characteristics	Symbol	Conditions	Specification	Unit
Junction Temperature	$T_J$	-	-55 to +150	°C
Storage Temperature	$T_{stg}$	-	-55 to +150	°C
Typical Thermal Resistance Junction to Case	$R_{thJC}$	DC operation	0.65	°C/W
Approximate Weight	wt	-	6.7	g
Case Style	-	TO-247AC	-	-

Figure 1: Typical Forward Characteristics




Figure 2: Typical Reverse Characteristics






Figure 3: Typical Junction Capacitance



Part Numbering and Marking System



Where XXXXX is YYWWL


DUR	= Device Type
60	= Forward Current (60A)
120	= Reverse Voltage (1200V)
W	= Configuration
LF	= Littelfuse
YY	= Year
WW	= Week
L	= Lot Number

## Ultrafast Recovery Rectifier DUR6060W, 60A, 600V, TO-247AC

## Packing Options


Part Number	Marking	Packing Mode	M.O.Q
DUR6060W	DUR6060W	30 pcs/Tube	21000

## Dimensions-Package TO-247AC



Symbol	Millimeters		
	Min	Typ.	Max
<b>A</b>	4.80	5.00	5.20
<b>A1</b>	2.20	2.41	2.61
<b>A2</b>	1.90	2.00	2.10
<b>b</b>	1.10	1.20	1.35
<b>b1</b>	1.80	2.00	2.20
<b>c</b>	0.50	0.60	0.75
<b>D</b>	20.30	21.00	21.20
<b>D1</b>	—	16.58	—
<b>D2</b>	—	1.17	—
<b>E</b>	15.60	15.80	16.00
<b>E1</b>	—	14.02	—
<b>E2</b>	—	5.00	—
<b>E3</b>	—	2.50	—
<b>e</b>	—	5.44	—
<b>L</b>	19.42	19.92	20.42
<b>L1</b>	—	4.13	—
<b>P</b>	3.50	3.60	3.70
<b>P1</b>	7.1	7.19	7.40
<b>P2</b>	—	2.50	—
<b>Q</b>	—	5.80	—
<b>S</b>	6.05	6.15	6.25
<b>T</b>	—	10.00	—
<b>U</b>	—	6.20	—

Tube Specification TO-247AC



## Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.

Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>