


FRED

V_{RRM}	=	200 V
I_{FAV}	= 2x	30 A
t_{rr}	=	20 ns


Fast Recovery Epitaxial Diode Common Cathode

Part number

DSEK60-02A



Backside: cathode



Features / Advantages:

- Planar passivated chips
- Low leakage current
- Very short recovery time
- Improved thermal behaviour
- Very low I_{rm} -values
- Very soft recovery behaviour
- Avalanche voltage rated for reliable operation
- Soft reverse recovery for low EMI/RFI
- Low I_{rm} reduces:
 - Power dissipation within the diode
 - Turn-on loss in the commutating switch

Applications:

- Antiparallel diode for high frequency switching devices
- Antisaturation diode
- Snubber diode
- Free wheeling diode
- Rectifiers in switch mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)

Package: TO-247

- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0

Disclaimer Notice


Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.



Fast Diode				Ratings				
Symbol	Definition	Conditions		min.	typ.	max.	Unit	
V _{RSM}	max. non-repetitive reverse blocking voltage	T _{VJ} = 25°C				200	V	
V _{RRM}	max. repetitive reverse blocking voltage	T _{VJ} = 25°C				200	V	
I _R	reverse current, drain current	V _R = 200 V	T _{VJ} = 25°C			200	μA	
		V _R = 160 V	T _{VJ} = 125°C			5	mA	
V _F	forward voltage drop	I _F = 30 A	T _{VJ} = 25°C			1.16	V	
		I _F = 60 A				1.29	V	
		I _F = 30 A	T _{VJ} = 150°C			0.92	V	
		I _F = 60 A				1.09	V	
I _{FAV}	average forward current	T _C = 125°C rectangular d = 0.5	T _{VJ} = 150°C			30	A	
V _{F0}	threshold voltage	} for power loss calculation only		T _{VJ} = 150°C		0.78	V	
r _F	slope resistance					4.9	mΩ	
R _{thJC}	thermal resistance junction to case					0.8	K/W	
R _{thCH}	thermal resistance case to heatsink				0.25		K/W	
P _{tot}	total power dissipation	T _C = 25°C				155	W	
I _{FSM}	max. forward surge current	t = 10 ms; (50 Hz), sine; V _R = 0 V		T _{VJ} = 45°C		325	A	
C _J	junction capacitance	V _R = 200 V f = 1 MHz		T _{VJ} = 25°C		77	pF	
I _{RM}	max. reverse recovery current	} I _F = 35 A; V _R = 100 V -di _F /dt = 200 A/μs		T _{VJ} = 25 °C		4	A	
				T _{VJ} = 125 °C		6	A	
t _{rr}	reverse recovery time			T _{VJ} = 25 °C		20	ns	
				T _{VJ} = 125 °C		45	ns	

Package TO-247			Ratings			
Symbol	Definition	Conditions	min.	typ.	max.	Unit
I_{RMS}	RMS current	per terminal ⁿ			70	A
T_{VJ}	virtual junction temperature		-40		150	°C
T_{op}	operation temperature		-40		125	°C
T_{stg}	storage temperature		-40		150	°C
Weight				6		g
M_D	mounting torque		0.8		1.2	Nm
F_C	mounting force with clip		20		120	N

Product Marking




Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	DSEK60-02A	DSEK60-02A	Tube	30	471526

Similar Part	Package	Voltage class
DSEK60-02AR	ISOPLUS247 (3)	200

Equivalent Circuits for Simulation

* on die level

$T_{VJ} = 150^{\circ}\text{C}$



Fast Diode

$V_{0\max}$ threshold voltage


0.78

V


$R_{0\max}$ slope resistance *

2.4

mΩ

Outlines TO-247


Sym.	Inches		Millimeter	
	min.	max.	min.	max.
A	0.185	0.209	4.70	5.30
A1	0.087	0.102	2.21	2.59
A2	0.059	0.098	1.50	2.49
D	0.819	0.845	20.79	21.45
E	0.610	0.640	15.48	16.24
E2	0.170	0.216	4.31	5.48
e	0.215	BSC	5.46	BSC
L	0.780	0.800	19.80	20.30
L1	-	0.177	-	4.49
Ø P	0.140	0.144	3.55	3.65
Q	0.212	0.244	5.38	6.19
S	0.242	BSC	6.14	BSC
b	0.039	0.055	0.99	1.40
b2	0.065	0.094	1.65	2.39
b4	0.102	0.135	2.59	3.43
c	0.015	0.035	0.38	0.89
D1	0.515	-	13.07	-
D2	0.020	0.053	0.51	1.35
E1	0.530	-	13.45	-
Ø P1	-	0.29	-	7.39




Fast Diode


Fig. 1 Forward current I_F versus max. forward Voltage drop V_F




Fig. 2 Typ. reverse recov. charge Q_r versus $-di_F/dt$




Fig. 3 Typ. peak reverse current I_{RM} versus $-di_F/dt$




Fig. 4 Typ. dynamic parameters Q_r , I_{RM} versus T_{VJ}




Fig. 5 Typ. recovery time t_{rr} versus $-di_F/dt$




Fig. 6 Typ. peak forward voltage V_{FR} and t_{rr} versus $-di_F/dt$




Fig. 7 Transient thermal resistance junction to case

Constants for Z_{thJC} calculation:

i	R_{thi} (K/W)	t_i (s)
1	0.200	0.0018
2	0.220	0.0100
3	0.080	0.5000
4	0.300	0.0900