


Standard Rectifier Module

3~ Rectifier	
V_{RRM}	= 1600 V
I_{DAV}	= 60 A
I_{FSM}	= 350 A

3~ Rectifier Bridge + Softstart-Thyristor


Part number

MDMA60UC1600VC



Backside: isolated

 E72873



Features / Advantages:

- Package with DCB ceramic
- Improved temperature and power cycling
- Planar passivated chips
- Very low forward voltage drop
- Very low leakage current

Applications:

- Diode for main rectification plus Softstart-Thyristor
- For three phase bridge configurations
- Supplies for DC power equipment
- Input rectifiers for PWM inverter
- Battery DC power supplies
- Field supply for DC motors

Package: V1-B-Pack

- Isolation Voltage: 3600 V~
- Industry standard outline
- RoHS compliant
- Soldering pins for PCB mounting
- Height: 10 mm
- Base plate: DCB ceramic
- Reduced weight
- Advanced power cycling

Disclaimer Notice


Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

Rectifier				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
V_{RSM}	max. non-repetitive reverse blocking voltage	$T_{VJ} = 25^{\circ}\text{C}$				1700	V
V_{RRM}	max. repetitive reverse blocking voltage	$T_{VJ} = 25^{\circ}\text{C}$				1600	V
I_R	reverse current	$V_R = 1600\text{ V}$	$T_{VJ} = 25^{\circ}\text{C}$			40	μA
		$V_R = 1600\text{ V}$	$T_{VJ} = 150^{\circ}\text{C}$			1.5	mA
V_F	forward voltage drop	$I_F = 20\text{ A}$	$T_{VJ} = 25^{\circ}\text{C}$			1.13	V
		$I_F = 60\text{ A}$				1.44	V
		$I_F = 20\text{ A}$	$T_{VJ} = 125^{\circ}\text{C}$			1.07	V
		$I_F = 60\text{ A}$				1.50	V
I_{DAV}	bridge output current	$T_C = 110^{\circ}\text{C}$ rectangular $d = \frac{1}{3}$	$T_{VJ} = 150^{\circ}\text{C}$			60	A
V_{F0}	threshold voltage	} for power loss calculation only	$T_{VJ} = 150^{\circ}\text{C}$			0.83	V
r_F	slope resistance					11.5	m Ω
R_{thJC}	thermal resistance junction to case					1.3	K/W
R_{thCH}	thermal resistance case to heatsink				0.3		K/W
P_{tot}	total power dissipation		$T_C = 25^{\circ}\text{C}$			95	W
I_{FSM}	max. forward surge current	$t = 10\text{ ms}; (50\text{ Hz}), \text{ sine}$	$T_{VJ} = 45^{\circ}\text{C}$			350	A
		$t = 8,3\text{ ms}; (60\text{ Hz}), \text{ sine}$	$V_R = 0\text{ V}$			380	A
		$t = 10\text{ ms}; (50\text{ Hz}), \text{ sine}$	$T_{VJ} = 150^{\circ}\text{C}$			300	A
		$t = 8,3\text{ ms}; (60\text{ Hz}), \text{ sine}$	$V_R = 0\text{ V}$			320	A
I^2t	value for fusing	$t = 10\text{ ms}; (50\text{ Hz}), \text{ sine}$	$T_{VJ} = 45^{\circ}\text{C}$			615	A ² s
		$t = 8,3\text{ ms}; (60\text{ Hz}), \text{ sine}$	$V_R = 0\text{ V}$			600	A ² s
		$t = 10\text{ ms}; (50\text{ Hz}), \text{ sine}$	$T_{VJ} = 150^{\circ}\text{C}$			450	A ² s
		$t = 8,3\text{ ms}; (60\text{ Hz}), \text{ sine}$	$V_R = 0\text{ V}$			425	A ² s
C_J	junction capacitance	$V_R = 400\text{ V}; f = 1\text{ MHz}$	$T_{VJ} = 25^{\circ}\text{C}$		10		pF



Softstart-Thyristor				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
V _{RSM/DSM}	max. non-repetitive reverse/forward blocking voltage	T _{VJ} = 25°C				1700	V
V _{RRM/DRM}	max. repetitive reverse/forward blocking voltage	T _{VJ} = 25°C				1600	V
I _{RD}	reverse current, drain current	V _{R/D} = 1600 V	T _{VJ} = 25°C			100	μA
		V _{R/D} = 1600 V	T _{VJ} = 140°C			6	mA
V _T	forward voltage drop	I _T = 50 A	T _{VJ} = 25°C			1.25	V
		I _T = 100 A				1.48	V
		I _T = 50 A	T _{VJ} = 125°C			1.17	V
		I _T = 100 A				1.44	V
I _{TAV}	average forward current	T _C = 85°C	T _{VJ} = 140°C			50	A
I _{T(RMS)}	RMS forward current	180° sine				79	A
V _{T0}	threshold voltage	for power loss calculation only				0.89	V
r _T	slope resistance						
R _{thJC}	thermal resistance junction to case					0.7	K/W
R _{thCH}	thermal resistance case to heatsink				0.20		K/W
P _{tot}	total power dissipation	T _C = 25°C				160	W
I _{TSM}	max. forward surge current	t = 10 ms; (50 Hz), sine	T _{VJ} = 45°C			800	A
		t = 8,3 ms; (60 Hz), sine	V _R = 0 V			865	A
		t = 10 ms; (50 Hz), sine	T _{VJ} = 140°C			680	A
		t = 8,3 ms; (60 Hz), sine	V _R = 0 V			735	A
I ² t	value for fusing	t = 10 ms; (50 Hz), sine	T _{VJ} = 45°C			3.20	kA²s
		t = 8,3 ms; (60 Hz), sine	V _R = 0 V			3.12	kA²s
		t = 10 ms; (50 Hz), sine	T _{VJ} = 140°C			2.31	kA²s
		t = 8,3 ms; (60 Hz), sine	V _R = 0 V			2.25	kA²s
C _J	junction capacitance	V _R = 400 V f = 1 MHz	T _{VJ} = 25°C		32		pF
P _{GM}	max. gate power dissipation	t _p = 30 μs	T _C = 140°C			10	W
		t _p = 300 μs				5	W
P _{GAV}	average gate power dissipation					0.5	W
(di/dt) _{cr}	critical rate of rise of current	T _{VJ} = 140°C; f = 50 Hz	repetitive, I _T = 150 A			150	A/μs
		t _p = 200 μs; di _G /dt = 0.45 A/μs; —					
(dv/dt) _{cr}	critical rate of rise of voltage	I _G = 0.45 A; V _D = ⅔ V _{DRM}	non-repet., I _T = 50 A			500	A/μs
(dv/dt) _{cr}	critical rate of rise of voltage	V _D = ⅔ V _{DRM}	T _{VJ} = 140°C			1000	V/μs
		R _{GK} = ∞; method 1 (linear voltage rise)					
V _{GT}	gate trigger voltage	V _D = 6 V	T _{VJ} = 25°C			1.5	V
			T _{VJ} = -40°C			1.6	V
I _{GT}	gate trigger current	V _D = 6 V	T _{VJ} = 25°C			78	mA
			T _{VJ} = -40°C			200	mA
V _{GD}	gate non-trigger voltage	V _D = ⅔ V _{DRM}	T _{VJ} = 140°C			0.2	V
I _{GD}	gate non-trigger current					5	mA
I _L	latching current	t _p = 10 μs	T _{VJ} = 25°C			200	mA
		I _G = 0.45 A; di _G /dt = 0.45 A/μs					
I _H	holding current	V _D = 6 V R _{GK} = ∞	T _{VJ} = 25°C			100	mA
t _{gd}	gate controlled delay time	V _D = ½ V _{DRM}	T _{VJ} = 25°C			2	μs
		I _G = 0.45 A; di _G /dt = 0.45 A/μs					
t _q	turn-off time	V _R = 100 V; I _T = 50 A; V _D = ⅔ V _{DRM}	T _{VJ} = 140°C		150		μs
		di/dt = 10 A/μs; dv/dt = 20 V/μs; t _p = 200 μs					

Package V1-B-Pack				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
I_{RMS}	RMS current	per terminal				100	A
T_{VJ}	virtual junction temperature			-40		150	°C
T_{op}	operation temperature			-40		125	°C
T_{stg}	storage temperature			-40		125	°C
Weight					28		g
M_D	mounting torque			2		2.5	Nm
$d_{Spp/App}$	creepage distance on surface / striking distance through air		terminal to terminal	7.0			mm
$d_{Spb/Apb}$			terminal to backside	10.0			mm
V_{ISOL}	isolation voltage	t = 1 second	50/60 Hz, RMS; $I_{ISOL} \leq 1$ mA	3600			V
		t = 1 minute		3000			V



Part description


M = Module
 D = Diode
 M = Standard Rectifier
 A = (up to 1800V)
 60 = Current Rating [A]
 UC = 3~ Rectifier Bridge + Softstart-Thyristor
 1600 = Reverse Voltage [V]
 VC = V1-B-Pack

Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	MDMA60UC1600VC	MDMA60UC1600VC	Box	10	517265

Equivalent Circuits for Simulation

* on die level



$T_{VJ} = 150^{\circ}\text{C}$



Rectifier

$V_{0\max}$	threshold voltage	0.83	V
$R_{0\max}$	slope resistance *	10.2	mΩ

Outlines V1-B-Pack




Rectifier


Fig. 1 Forward current vs. voltage drop per diode




Fig. 2 Surge overload current vs. time per diode




Fig. 3 I^2t vs. time per diode




Fig. 4 Power dissipation vs. forward current and ambient temperature per diode




Fig. 5 Max. forward current vs. case temperature per diode




Fig. 6 Transient thermal impedance junction to case vs. time per diode

Constants for Z_{thJC} calculation:

i	R_{th} (K/W)	t_i (s)
1	0.06070	0.008
2	0.173	0.05
3	0.3005	0.06
4	0.463	0.3
5	0.3028	0.15


Softstart Thyristor


Fig. 1 Forward characteristics





 Fig. 2 Surge overload current
 I_{TSM} : crest value, t : duration

 Fig. 3 I^2t versus time (1-10 s)


Fig. 4 Gate voltage & gate current




 Fig. 5 Gate controlled delay time t_{gd}


Fig. 6 Max. forward current at case temperature




 Fig. 7a Power dissipation versus direct output current
 Fig. 7b and ambient temperature


Fig. 8 Transient thermal impedance junction to case