FRED Module

Fast Recovery Epitaxial Diode

V_{RRM} = 600 V
I_{FAVM} = 304 A
t_{rr} = 250 ns


Part number

MEA 300-06DA
MEK 300-06DA
MEE 300-06DA




E72873
Backside: isolated

Common Anode




MEA 300-06DA

Common Cathode



MEK 300-06DA

Phase-Leg



MEE 300-06DA

Features / Advantages:

- International standard package with DCB ceramic base plate
- Planar passivated chips
- Short recovery time
- Low switching losses
- Soft recovery behaviour
- High reliability circuit operation
- Low voltage peaks for reduced protection circuits
- Low noise switching
- Low losses

Applications:

- Antiparallel diode for high frequency switching devices
- Free wheeling diode in converters and motor control circuits
- Inductive heating and melting
- Uninterruptible power supplies (UPS)
- Ultrasonic cleaners and welders

Package: Y4-M6

- Isolation voltage: 3600 V~
- Industry standard outline
- Soldering pins for PCB mounting
- Base plate: DCB ceramic
- Reduced weight
- Advanced power cycling

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

IXYS reserves the right to change limits, test conditions and dimensions

© 2020 IXYS All rights reserved


Diode				Ratings			
Symbol	**Definitions**	**Conditions**		**min.**	**typ.**	**max.**	
V_{RSM}	*max. non-repetitive reverse*		T_{VJ} = 25°C			600	V
V_{RRM}	*max. repetitive reverse*		T_{VJ} = 25°C			600	V
I_R	*reverse current*	$V_R = V_{RRM}$	T_{VJ} = 25°C			12	mA
		$V_R = 0.8 \cdot V_{RRM}$	T_{VJ} = 25°C			3	mA
		$V_R = 0.8 \cdot V_{RRM}$	T_{VJ} = 125°C			80	mA
V_F	*forward voltage*	I_F = 300 A	T_{VJ} = 25°C			1.27	V
			T_{VJ} = 125°C			1.05	V
		I_F = 520 A	T_{VJ} = 25°C			1.36	V
			T_{VJ} = 125°C			1.19	V
I_{FRMS}	*RMS forward current*		T_C = 75°C			430	A
I_{FAV} ①	*average forward current*	T_C = 75°C rectangular, d = 0.5	T_{VJ} = 150°C			304	A
V_{T0}	*threshold voltage*	for power-loss calculations only	$T_{VJ} = T_{VJM}$			0.85	V
r_T	*slope resistance*					1.34	mΩ
R_{thJC}	*thermal resistance junction to case*					0.143	K/W
R_{thCH}	*thermal resistance junction to heatsink*				0.085		K/W
P_{tot}	*total power dissipation*		T_{VJ} = 25°C			875	W
I_{FSM}	*max. surge forward current*	t = 10 ms (50 Hz), sine	T_{VJ} = 45°C			2.40	kA
		t = 8.3 ms (60 Hz), sine				2.64	kA
		t = 10 ms (50 Hz), sine	T_{VJ} = 150°C			2.16	kA
		t = 8.3 ms (60 Hz), sine				2.38	kA
I^2t	*I^2t value for fusing*	t = 10 ms (50 Hz), sine	T_{VJ} = 45°C			28.8	kA^2s
		t = 8.3 ms (60 Hz), sine				29.3	kA^2s
		t = 10 ms (50 Hz), sine	T_{VJ} = 150°C			23.3	kA^2s
		t = 8.3 ms (60 Hz), sine				23.8	kA^2s
t_{rr}	*max. reverse recovery current*	I_F = 300 A; $-di_F/dt$ = 400 A/µs	T_{VJ} = 25°C		140	170	ns
			T_{VJ} = 100°C		250	300	ns
I_{RM}	*reverse recovery time*	V_R = 300 V; L ≤ 0.05 µH	T_{VJ} = 25°C		35	45	A
			T_{VJ} = 100°C		55	70	A

① I_{FAVM} rating includes reverse blocking losses at T_{VJM}, $V_R = 0.8\ V_{RRM}$, duty cycle d = 0.5

OBSOLETE

© 2020 IXYS All rights reserved

Package	Y4-M6				Ratings			
Symbol	Definitions	Conditions			min.	typ.	max.	
I_{RMS}	*RMS current*	per terminal					300	A
T_{VJ} T_{op} T_{stg}	*virtual junction temperature* *operation temperature* *storage temperature*				-40 -40 -40		150 125 125	°C °C °C
Weight						126		g
M_D	*mounting torque*				2.25		2.75	Nm
M_T	*terminal torque*				4.5		5.5	Nm
$d_{Spp/App}$ $d_{Spb/Apb}$	*creepage distance on surface | striking distance through air*		terminal to terminal terminal to backside	14.0 16.0	10.0 16.0			mm mm
V_{ISOL}	*isolation voltage*	t = 1 second t = 1 minute	50/60 Hz, RMS; $I_{ISOL} \leq 1$ mA		3600 3000			V V




Data Matrix: *part no.* (1-19), DC + *PI* (20-25), *lot.no.#* (26-31), *blank* (32), *serial no.#* (33-36)

Ordering	Part Name	Marking on Product	Delivering Mode	Base Qty	Ordering Code
Standard	MEA 300-06DA	MEA 300-06DA	Box	36	464686
Standard	MEK 300-06DA	MEK 300-06DA	Box	36	464619
Standard	MEE 300-06DA	MEE 300-06DA	Box	36	464708


OBSOLETE


© 2020 IXYS All rights reserved

Outlines Y4-M6



Dim.	min [mm]	max [mm]	min [inch]	max [inch]
a	30.0	30.6	1.181	1.205
b	typ. 0.25		typ. 0.010	
c	64.0	65.0	2.520	2.559
d	6.5	7.0	0.256	0.275
e	4.9	5.1	0.193	0.201
h	93.5	94.5	3.681	3.720
i	79.5	80.5	3.130	3.169
k	33.4	34.0	1.315	1.339
l	16.7	17.3	0.657	0.681
m	22.7	23.3	0.894	0.917
n	22.7	23.3	0.894	0.917
o	14.0	15.0	0.551	0.591
p	typ. 10.5		typ. 0.413	





MEA 300-06DA MEK 300-06DA MEE 300-06DA

OBSOLETE

© 2020 IXYS All rights reserved

Curves




Fig. 1 Typ. forward current I_F versus max. voltage drop V_F per leg




Fig. 2 Typ. reverse recovery charge Q_r versus $-di_F/dt$




Fig. 3 Typ. peak reverse current I_{RM} versus $-di_F/dt$




Fig. 4 Typ. dynamic parameters Q_r, I_{RM} versus junction temperature T_{VJ}




Fig. 5 Typ. recovery time t_{rr} versus $-di_F/dt$




Fig. 6 Typ. peak forward voltage V_{FR} and t_{rr} versus $-di_F/dt$




Fig. 7 Typ. transient thermal impedance junction to heatsink

Constants for Z_{thJS} calculation:

i	Rth_i [K/W]	t_i [s]
1	0.002	0.080
2	0.008	0.024
3	0.054	0.112
4	0.164	0.464

OBSOLETE

© 2020 IXYS All rights reserved