FRED Module

V_{RRM} = 1200 V
I_{FAVM} = 453 A
t_{rr} = 500 ns


Fast Recovery Epitaxial Diode

Single Diode

Part number
MEO 450-12DA



E72873
Backside: isolated



Features / Advantages:
- International standard package with DCB ceramic base plate
- Planar passivated chips
- Short recovery time
- Low switching losses
- Soft recovery behaviour
- High reliability circuit operation
- Low voltage peaks for reduced protection circuits
- Low noise switching
- Low losses

Applications:
- Antiparallel diode for high frequency switching devices
- Free wheeling diode in converters and motor control circuits
- Inductive heating and melting
- Uninterruptible power supplies (UPS)
- Ultrasonic cleaners and welders

Package: Y4-M6
- Isolation voltage: 3600 V~
- Industry standard outline
- Soldering pins for PCB mounting
- Base plate: DCB ceramic
- Reduced weight
- Advanced power cycling

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

IXYS reserves the right to change limits, test conditions and dimensions

© 2020 IXYS All rights reserved


Diode				Ratings			
Symbol	**Definitions**	**Conditions**		**min.**	**typ.**	**max.**	
V_{RSM}	*max. non-repetitive reverse*		T_{VJ} = 25°C			1200	V
V_{RRM}	*max. repetitive reverse*		T_{VJ} = 25°C			1200	V
I_R	*reverse current*	$V_R = V_{RRM}$	T_{VJ} = 25°C			24	mA
		$V_R = 0.8 \cdot V_{RRM}$	T_{VJ} = 25°C			6	mA
		$V_R = 0.8 \cdot V_{RRM}$	T_{VJ} = 125°C			120	mA
V_F	*forward voltage*	I_F = 300 A	T_{VJ} = 25°C			1.78	V
			T_{VJ} = 125°C			1.51	V
		I_F = 520 A	T_{VJ} = 25°C			1.96	V
			T_{VJ} = 125°C			1.76	V
I_{FRMS}	*RMS forward current*		T_C = 75°C			640	A
I_{FAV} ①	*average forward current*	T_C = 75°C rectangular, d = 0.5	T_{VJ} = 150°C			453	A
V_{T0}	*threshold voltage*	for power-loss calculations only	$T_{VJ} = T_{VJM}$			1.16	V
r_T	*slope resistance*					1.15	mΩ
R_{thJC}	*thermal resistance junction to case*					0.071	K/W
R_{thCH}	*thermal resistance junction to heatsink*				0.043		K/W
P_{tot}	*total power dissipation*		T_{VJ} = 25°C			1750	W
I_{FSM}	*max. surge forward current*	t = 10 ms (50 Hz), sine	T_{VJ} = 45°C			4.80	kA
		t = 8.3 ms (60 Hz), sine				5.28	kA
		t = 10 ms (50 Hz), sine	T_{VJ} = 150°C			4.32	kA
		t = 8.3 ms (60 Hz), sine				4.75	kA
I^2t	*I^2t value for fusing*	t = 10 ms (50 Hz), sine	T_{VJ} = 45°C			115.2	kA^2s
		t = 8.3 ms (60 Hz), sine				117.1	kA^2s
		t = 10 ms (50 Hz), sine	T_{VJ} = 150°C			93.3	kA^2s
		t = 8.3 ms (60 Hz), sine				94.8	kA^2s
t_{rr}	*max. reverse recovery current*	I_F = 450 A; $-di_F/dt$ = 800 A/µs	T_{VJ} = 25°C		250	300	ns
			T_{VJ} = 100°C		500	600	ns
I_{RM}	*reverse recovery time*	V_R = 600 V; L ≤ 0.05 µH	T_{VJ} = 25°C		80	100	A
			T_{VJ} = 100°C		125	150	A

① I_{FAVM} rating includes reverse blocking losses at T_{VJM}, $V_R = 0.8\ V_{RRM}$, duty cycle d = 0.5

OBSOLETE

© 2020 IXYS All rights reserved

Package	Y4-M6				Ratings			
Symbol	Definitions	Conditions			min.	typ.	max.	
I_{RMS}	*RMS current*	per terminal					300	A
T_{VJ} T_{op} T_{stg}	*virtual junction temperature* *operation temperature* *storage temperature*				-40 -40 -40		150 125 125	°C °C °C
Weight						108		g
M_D	*mounting torque*				2.25		2.75	Nm
M_T	*terminal torque*				4.5		5.5	Nm
$d_{Spp/App}$ $d_{Spb/Apb}$	*creepage distance on surface* | *striking distance through air*		terminal to terminal terminal to backside	14.0 16.0	10.0 16.0			mm mm
V_{ISOL}	*isolation voltage*	t = 1 second t = 1 minute	50/60 Hz, RMS; $I_{ISOL} \leq 1$ mA		3600 3000			V V




Data Matrix: *part no.* (1-19), DC + *PI* (20-25), *lot.no.#* (26-31), *blank* (32), *serial no.#* (33-36)


Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	MEO 450-12DA	MEO 450-12DA	Box	6	464635

OBSOLETE


© 2020 IXYS All rights reserved


Outlines Y4-M6






Dim.	MIN [mm]	MAX [mm]	MIN [inch]	MAX [inch]
a	30.0	30.6	1.181	1.205
b	typ. 0.25		typ. 0.010	
c	64.0	65.0	2.520	2.559
d	6.5	7.0	0.256	0.275
e	4.9	5.1	0.193	0.201
h	93.5	94.5	3.681	3.720
i	79.5	80.5	3.130	3.169
k	33.4	34.0	1.315	1.339
l	16.7	17.3	0.657	0.681
m	22.7	23.3	0.894	0.917
n	22.7	23.3	0.894	0.917
o	14.0	15.0	0.551	0.591
p	typ. 10.5		typ. 0.413	







OBSOLETE

© 2020 IXYS All rights reserved

Curves




Fig. 1 Typ. forward current I_F vs. V_F




Fig. 2 Typ. reverse recovery charge Q_r versus $-di_F/dt$




Fig. 3 Typ. peak reverse current I_{RM} versus $-di_F/dt$




Fig. 4 Typ. dynamic parameters Q_r, I_{RM} versus T_{VJ}




Fig. 5 Typ. recovery time t_{rr} vs. $-di_F/dt$




Fig. 6 Typ. peak forward voltage V_{FR} and t_{fr} versus T_{VJ}




Fig. 7 Typ. transient thermal impedance junction to case

Constants for Z_{thJS} calculation:

i	R_{thi} (K/W)	t_i (s)
1	0.001	0.08
2	0.004	0.024
3	0.027	0.112
4	0.082	0.464

OBSOLETE

© 2020 IXYS All rights reserved