




RESISTANCE @  $+25^{\circ}\text{C}$  =  $10,000\ \Omega \pm 10\%$   
 RESISTANCE/TEMPERATURE CURVE = "F"  
 BETA " $\beta$ " (0 TO  $+50^{\circ}\text{C}$ ) =  $3,419^{\circ}\text{K}$  NOMINAL  
 TEMPERATURE COEFFICIENT @  $+25^{\circ}\text{C}$  =  $-3.86\%/^{\circ}\text{C}$  NOMINAL  
 DISSIPATION CONSTANT =  $2\ \text{mW}/^{\circ}\text{C}$  NOMINAL  
 THERMAL TIME CONSTANT = 8 SECONDS NOMINAL  
 MAXIMUM TEMPERATURE RATING =  $+220^{\circ}\text{C}$

| REV  | REVISION RECORD       | DATE     | APP |
|------|-----------------------|----------|-----|
| NONE | RELEASE TO PRODUCTION | 09/14/05 | DD  |

|          |             |                                                                                                                                                                |
|----------|-------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| SCALE    | NONE        | <b>U.S. SENSOR corp.</b><br>© COPYRIGHT<br>714-639-1000 <a href="http://www.ussensor.com">www.ussensor.com</a><br><b>NTC THERMISTOR</b><br><b>P/N SM103F5K</b> |
| DRAWN BY | DAN DANKERT |                                                                                                                                                                |
| DATE     | 09/14/05    |                                                                                                                                                                |
| REV.     | NONE        |                                                                                                                                                                |
| LAYER    | 0 OF 2      |                                                                                                                                                                |