



RTD ELEMENT RESISTANCE @ 0°C = 1,000 Ω ± 0.12%  
 RTD ELEMENT ACCURACY @ °C = ± 0.30°C  
 RTD ELEMENT ACCURACY CLASS = DIN EN 60751 F 0.3 ("B")  
 TCR = 3,850 ppm/°C  
 MAXIMUM TEMPERATURE RATING = +105°C

MOUNTING-HOLE DIAMETER = 0.197" NOMINAL  
 MOUNTING-HOLE STUD-SIZE = #10

SEE MANUFACTURING SPECIFICATION (LAYER 1)

"A"	CLARIFIED ACCURACY CLASS	06/30/17	DD
NONE	RELEASE TO PRODUCTION	02/05/15	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE	© COPYRIGHT <b>U.S. SENSOR CORP.</b> 714-639-1000 www.ussensor.com
DRAWN BY DAN DANKERT	
DATE 02/05/15	RTD PROBE ASSY
REV. "A"	P/N USW3866
LAYER 0 OF 2	