




RESISTANCE @  $+25^{\circ}\text{C}$  = 10,000  $\Omega$  NOMINAL  
 ACCURACY (0 TO  $+50^{\circ}\text{C}$ ) =  $\pm 0.50^{\circ}\text{C}$   
 RESISTANCE/TEMPERATURE CURVE = "J"  
 BETA " $\beta$ " (0 TO  $+50^{\circ}\text{C}$ ) = 3,892°K NOMINAL  
 TEMPERATURE COEFFICIENT @  $+25^{\circ}\text{C}$  =  $-4.4\%/^{\circ}\text{C}$  NOMINAL  
 DISSIPATION CONSTANT = 2 mW/ $^{\circ}\text{C}$  NOMINAL  
 THERMAL TIME CONSTANT = 8 SECONDS NOMINAL  
 MAXIMUM TEMPERATURE RATING =  $+220^{\circ}\text{C}$

| REV  | REVISION RECORD       | DATE     | APP |
|------|-----------------------|----------|-----|
| NONE | RELEASE TO PRODUCTION | 09/05/03 | DD  |

|          |             |                                                                                                                                                                |
|----------|-------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| SCALE    | NONE        | <b>U.S. SENSOR corp.</b><br>© COPYRIGHT<br>714-639-1000 <a href="http://www.ussensor.com">www.ussensor.com</a><br><b>NTC THERMISTOR</b><br><b>P/N HM103J1A</b> |
| DRAWN BY | DAN DANKERT |                                                                                                                                                                |
| DATE     | 09/05/03    |                                                                                                                                                                |
| REV.     | NONE        |                                                                                                                                                                |
| LAYER    | 0 OF 1      |                                                                                                                                                                |