


MM074-16I06


1600V, 40 A, AC Controlling, 1~ full-controlled

▲ E72873



Backside: isolated

Pinout Diagram (SOT-227 B)



Description

1600 V, 40 A phase-leg thyristor module featuring planar passivated chip technology in an industry-standard SOT-227B package for line-frequency rectification and AC power control applications.

Features

- Thyristor for line frequency
- Planar passivated chip
- Long-term stability

Benefits

- Supports reliable operation in 50/60 Hz rectification
- Supports high-voltage power conversion
- Enhances blocking-voltage robustness and long-term reliability
- Reduces conduction losses and improves power efficiency
- Enables efficient thermal dissipation while maintaining electrical isolation

Applications

- Line rectification 50/60 Hz
- Soft start AC motor control
- DC Motor control
- Power converter
- AC power control
- Lighting and temperature control

Package SOT-227 B (minibloc)

- Isolation Voltage: 3000 V
- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0
- Base plate: Copper internally DCB isolated
- Advanced power cycling

Product Summary

Characteristic	Value	Unit
V_{RRM}	1600	V
$I_{T(AV)}$	40	A
V_T	1.29	V

Rectifier - Maximum Ratings ($T_{vj} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

Symbol	Characteristics	Conditions		Value	Units
V_{RRM} / V_{DRM}	Repetitive Peak Reverse / Peak Off-State Voltage	$T_{vj} = 25\text{ }^{\circ}\text{C}$		1600	V
V_{RSM} / V_{DSM}	Non-Repetitive Peak Reverse / Peak Off-State Voltage	$T_{vj} = 25\text{ }^{\circ}\text{C}$		1700	V
I_R / I_D	Reverse Current / Off-State Current	$V_R / V_D = 1600\text{ V}$	$T_{vj} = 25\text{ }^{\circ}\text{C}$	100	μA
			$T_{vj} = 125\text{ }^{\circ}\text{C}$	6	mA
$I_{T(AV)}$	Average On-State Current	180° sine wave, $T_{vj} = 150\text{ }^{\circ}\text{C}$	$T_c = 95\text{ }^{\circ}\text{C}$	40	A
$I_{T(RMS)}$	R.M.S On-State Current			88	A
P_{tot}	Total Power Dissipation	$T_c = 25\text{ }^{\circ}\text{C}$		180	W
I_{TSM}	Non-Repetitive Surge On-State Current	$t_p = 10\text{ ms; (50 Hz), sine}$	$T_{vj} = 45\text{ }^{\circ}\text{C},$ $V_R = 0\text{ V}$	600	A
		$t_p = 8.3\text{ ms; (60 Hz), sine}$		650	A
		$t_p = 10\text{ ms; (50 Hz), sine}$	$T_{vj} = 150\text{ }^{\circ}\text{C},$ $V_R = 0\text{ V}$	510	A
		$t_p = 8.3\text{ ms; (60 Hz), sine}$		550	A
I^2t	I^2t Value	$t_p = 10\text{ ms; (50 Hz), sine}$	$T_{vj} = 45\text{ }^{\circ}\text{C},$ $V_R = 0\text{ V}$	1.80	kA^2s
		$t_p = 8.3\text{ ms; (60 Hz), sine}$		1.76	kA^2s
		$t_p = 10\text{ ms; (50 Hz), sine}$	$T_{vj} = 150\text{ }^{\circ}\text{C},$ $V_R = 0\text{ V}$	1.30	kA^2s
		$t_p = 8.3\text{ ms; (60 Hz), sine}$		1.26	kA^2s
P_{GM}	Peak Gate Power Dissipation	$t_p = 30\text{ }\mu\text{s}, T_c = 150\text{ }^{\circ}\text{C}$		10	W
		$t_p = 300\text{ }\mu\text{s}, T_c = 150\text{ }^{\circ}\text{C}$		5	W
$P_{G(AV)}$	Average gate power dissipation	—		0.5	W
T_{vj}	Virtual Junction Temperature Range	—		-40 to +150	$^{\circ}\text{C}$
T_{stg}	Storage Temperature Range	—		-40 to +150	$^{\circ}\text{C}$

Electrical Characteristics – Static ($T_{vj} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

Symbol	Characteristics	Conditions	Value			Units
			Min.	Typ.	Max.	
V_T	On-State Voltage	$I_T = 40\text{ A}$	–	–	1.29	V
		$I_T = 80\text{ A}$			1.61	V
		$I_T = 40\text{ A}$	–	–	1.29	V
		$I_T = 80\text{ A}$			1.70	V
$V_{(TO)}$	Threshold Voltage ¹	$T_{vj} = 150\text{ }^{\circ}\text{C}$	–	–	0.87	V
r_T	Slope Resistance ¹	$T_{vj} = 150\text{ }^{\circ}\text{C}$	–	–	10.5	m Ω
V_{GT}	Gate Trigger Voltage	$V_D = 6\text{ V}$	–	–	1.5	V
					1.6	V
I_{GT}	Gate Trigger Current	$V_D = 6\text{ V}$	–	–	100	mA
					150	mA
V_{GD}	Gate Non-Trigger Voltage	$V_D = \frac{2}{3} V_{DRM}, T_{vj} = 150\text{ }^{\circ}\text{C}$	–	–	0.2	V
I_{GD}	Gate Non-Trigger Current	$V_D = \frac{2}{3} V_{DRM}, T_{vj} = 150\text{ }^{\circ}\text{C}$	–	–	5	mA
I_L	Latching Current	$t_p = 10\text{ }\mu\text{s}, I_G = 0.3\text{ A}, di_g/dt = 0.3\text{ A}/\mu\text{s}, T_{vj} = 25\text{ }^{\circ}\text{C}$	–	–	450	mA
I_H	Holding Current	$V_D = 6\text{ V}, R_{GK} = \infty, T_{vj} = 25\text{ }^{\circ}\text{C}$	–	–	200	mA

Note 1: For power loss calculations only**Electrical Characteristics – Dynamic** ($T_{vj} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

Symbol	Characteristics	Conditions	Value			Units
			Min.	Typ.	Max.	
C_j	Junction Capacitance	$V_R = 400\text{ V}, f = 1\text{ MHz}, T_{vj} = 25\text{ }^{\circ}\text{C}$	–	22	–	pF
$di/dt_{(cr)}$	Critical Rate of Rise of Off-State Current	$T_{vj} = 150\text{ }^{\circ}\text{C}, f = 50\text{ Hz}, t_p = 200\text{ }\mu\text{s}, di_g/dt = 0.3\text{ A}/\mu\text{s}, I_G = 0.3\text{ A}, V_{DM} = \frac{2}{3} V_{DRM}$	–	–	100	A/ μs
					500	A/ μs
$dv/dt_{(cr)}$	Critical Rate Of Rise Of Off-State Voltage	$V_{DM} = \frac{2}{3} V_{DRM}, R_{GK} = \infty, T_{vj} = 150\text{ }^{\circ}\text{C}$	–	–	1000	A/ μs
t_{gd}	Gate-Controlled Turn-On Delay Time	$V_D = \frac{1}{2} V_{DRM}, I_G = 0.3\text{ A}, di_g/dt = 0.3\text{ A}/\mu\text{s}, T_{vj} = 25\text{ }^{\circ}\text{C}$	–	–	2	μs
t_q	Circuit-Commutated Turn-Off Time	$V_R = 100\text{ V}, V_D = \frac{2}{3} V_{DRM}, I_T = 20\text{ A}, di/dt = 10\text{ A}/\mu\text{s}, dv/dt = 15\text{ V}/\mu\text{s}, t_p = 200\text{ }\mu\text{s}, T_{vj} = 125\text{ }^{\circ}\text{C}$	–	150	–	μs

Thermal Specifications

Symbol	Characteristics	Conditions	Value			Units
			Min.	Typ.	Max.	
$R_{th(j-c)}$	Thermal Resistance Junction To Case	–	–	–	0.7	K/W
$R_{th(c-h)}$	Thermal Resistance Case To Heatsink	–	–	0.1	–	K/W

Package SOT-227B (minibloc)

Symbol	Characteristics	Conditions	Value			Units
			Min.	Typ.	Max.	
I_{tRMS}	Terminal RMS Current	per terminal	–	–	150	A
T_{op}	Operation Temperature	–	-40	–	125	°C
M_s	Mounting Torque For Screws To Heatsink	–	1.1	–	1.5	Nm/lb.in
M_t	Mounting Torque For Terminal Screws	–	1.1	–	1.5	Nm/lb.in
d_s	Creepage Distance Along The Surface	terminal to terminal	3.2	–	–	mm
d_a	Clearance Distance In Air	terminal to backside	6.8	–	–	mm
G	Package Weight	–		30		g
V_{isol}	Isolation Withstand Voltage	$f = 50 / 60 \text{ Hz}, I_{isol} \leq 1 \text{ mA}, t = 1 \text{ second}$	3000			V
		$f = 50 / 60 \text{ Hz}, I_{isol} \leq 1 \text{ mA}, t = 1 \text{ minute}$	2500			V

Characteristic Curves - Thyristor

Fig. 1. Typical Forward Characteristics




Fig. 2. Non-Repetitive Surge Forward Current vs. Pulse Width



Fig. 3. I^2t vs. Time

Fig. 4. Typical Gate Trigger Characteristics




Fig. 5. Typical Gate Current Delay Time t_{gd} vs. Gate Current

Fig. 6. Average Forward Current vs. Case Temperature



Characteristic Curves - Thyristor

Fig. 7. Average On-State Power Dissipation vs. Average On-State Current




Fig. 8. Average On-State Power Dissipation vs. Ambient Temperature






Fig. 9. Typical Transient Thermal Impedance




Part Outline Drawing SOT-227B (miniBLOC)



Symbol	Millimeters		Inches	
	Min.	Max.	Min.	Max
A	31.50	31.88	1.240	1.255
B	7.80	8.20	0.307	0.323
C	4.09	4.29	0.161	0.169
D	4.09	4.29	0.161	0.169
E	4.09	4.29	0.161	0.169
F	14.91	15.11	0.587	0.595
G	30.12	30.30	1.186	1.193
H	37.80	38.23	1.488	1.505
J	11.68	12.22	0.460	0.481
K	8.92	9.60	0.351	0.378
L	0.74	0.84	0.029	0.033
M	12.50	13.10	0.492	0.516
N	25.15	25.42	0.990	1.001
O	1.95	2.13	0.077	0.084
P	4.95	6.20	0.195	0.244
Q	26.54	26.90	1.045	1.059
R	3.94	4.42	0.155	0.167
S	4.55	4.85	0.179	0.191
T	24.59	25.25	0.968	0.994
U	-0.05	0.10	-0.002	0.004
V	3.20	5.50	0.126	0.217
W	19.81	21.08	0.780	0.830
Z	2.50	2.70	0.098	0.106

Part Number and Marking



Ordering Information

Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity
Standard	MMO74-16io6	MMO74-16io6	Tube	10

Equivalent Circuits for Simulation (*on die level, T_{vj} = 150 °C)

Symbol	Definition	Thyristor	Units
V _{0max}	Threshold voltage	0.87	V
R _{0max}	Slope resistance*	9.7	mΩ

Disclaimer Notice
Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.
Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

