




RESISTANCE @ +25°C = 10,000 Ω ± 1%
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 MAXIMUM TEMPERATURE RATING = +125°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

"A"	LEAD WIRE LENGTH WAS 1.50" ± 0.375"	09/21/10	DD
NONE	RELEASE TO PRODUCTION	04/02/10	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR corp. 1832 W. COLL INS AVE. ORANGE, CA . 92867 714-639-1000 www.ussensor.com NTC THERMISTOR PROBE P/N USP10975	
DRAWN BY	DAN DANKERT		
DATE	04/02/10		
REV.	"A"		
LAYER	0 OF 2		