




RESISTANCE @ +25°C = 10,000 Ω $\pm$ 1%
 RESISTANCE/TEMPERATURE CURVE = "E1"
 BETA " β " (+25 TO +85°C) = 3,435°K NOMINAL
 DISSIPATION CONSTANT = 0.7 mW/°C NOMINAL (STILL AIR)
 THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (AIR)
 TEMPERATURE RATING = -30 TO +90°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	03/06/15	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	© COPYRIGHT U.S. SENSOR CORP. 714-639-1000 www.ussensor.com	
DRAWN BY	DAN DANKERT		
DATE	03/06/15	NTC THERMISTOR	
REV.	NONE	P/N USP16673	
LAYER	0 OF 2		