


S6X8ECS2



Main Features

Symbol	Value	Unit
$I_{T(RMS)}$	0.8	A
V_{DRM}/V_{RRM}	600	V
I_{GT}	30	μA

Applications

The S6X8ECS2 is specifically designed for GFCI (Ground Fault Circuit Interrupter) and gas ignition applications.


Description

This new .8 A sensitive gate SCR in an TO-92 package with a GAK pin out, offers a high static component series with a high static dv/dt and a low turn off (t_q) time by the use of small die planar construction implementation. All SCR's junctions are glass-passivated to ensure long term reliability and parametric stability.

Features

- Surge capability >10Amps
- High dv/dt noise immunity
- Improved turn-off time (t_q) $\leq 25 \mu sec$.
- TO-92 G-A-K pinout
- Sensitive gate for direct microprocessor interface
- RoHS compliant and Halogen-Free

Schematic Symbol



Absolute Maximum Ratings

Symbol	Parameter		Value	Unit
$I_{T(RMS)}$	RMS on-state current (full sine wave)	$T_c = 55^\circ C$	0.8	A
$I_{T(AV)}$	Average on-state current	$T_c = 55^\circ C$	0.51	A
I_{TSM}	Non repetitive surge peak on-state current (Single cycle, T_J initial = $25^\circ C$)	F = 50 Hz	8	A
		F = 60 Hz	10	
I^2t	I^2t Value for fusing	$t_p = 10$ ms F = 50 Hz	0.32	A^2s
		$t_p = 8.3$ ms F = 60 Hz	0.41	
di/dt	Critical rate of rise of on-state current $I_G = 10mA$	$T_J = 125^\circ C$	50	$A/\mu s$
I_{GM}	Peak gate current	$t_p = 10 \mu s$ $T_J = 125^\circ C$	1.0	A
$P_{G(AV)}$	Average gate power dissipation	$T_J = 125^\circ C$	0.1	W
T_{stg}	Storage junction temperature range		-40 to 150	$^\circ C$
T_J	Operating junction temperature range		-40 to 125	$^\circ C$



Electrical Characteristics ($T_J = 25^\circ\text{C}$, unless otherwise specified)

Symbol	Description	Test Conditions	Value		Unit
			Min	Max	
I_{GT}	DC Gate Trigger Current	$V_D = 6\text{V}$ $R_L = 100\ \Omega$	1	30	μA
V_{GT}			—	0.8	V
V_{GRM}	Peak Reverse Gate Voltage	$I_{RG} = 10\ \mu\text{A}$	5	—	V
I_H	Holding Current	$R_{GK} = 1\ \text{k}\Omega$ Initial Current = 20mA	—	3	mA
(dv/dt)s	Critical Rate-of-Rise of Off-State Voltage	$T_J = 125^\circ\text{C}$, $V_D = V_{DRM}/V_{RRM}$ Exponential Waveform, $R_{GK} = 1\ \text{k}\Omega$	75	—	V/ μs
V_{GT}	Gate Non-Trigger Voltage	$V_D = V_{DRM}$, $R_{GK} = 1\ \text{k}\Omega$ $T_J = 25^\circ\text{C}$	0.2	—	V
t_q	Turn-Off Time	$T_J = 125^\circ\text{C}$ @ 600 V $R_{GK} = 1\ \text{k}\Omega$	—	25	μs
t_{gt}	Turn-On Time	$I_G = 10\text{mA}$ PW = 15 μsec $I_T = 1.6\text{A}$ (pk)	2.0 (Typ)		μs

Static Characteristics ($T_J = 25^\circ\text{C}$, unless otherwise specified)

Symbol	Description	Test Conditions	Value	Unit
			Max	
V_{TM}	Peak On-State Voltage	$I_{TM} = 1.2\ \text{A}$ (pk)	1.4	V
I_{DRM}	Off-State Current, Peak Repetitive	$T_J = 25^\circ\text{C}$ @ $V_D = V_{DRM}$, $R_{GK} = 1\ \text{k}\Omega$	3	μA
		$T_J = 125^\circ\text{C}$ @ $V_D = V_{DRM}$, $R_{GK} = 1\ \text{k}\Omega$	500	μA

Thermal Resistances

Symbol	Parameter		Value	Unit
R _{θ(JC)}	Junction to case (AC)	I _T = 0.8 A _(RMS) , 60Hz AC resistive load condition, 100% conduction.	75	°C/W
R _{θ(J-A)}	Junction to ambient		150	°C/W

Figure 1: Normalized DC Gate Trigger Current For All Quadrants vs. Junction Temperature




Figure 2: Normalized DC Holding Current vs. Junction Temperature






Figure 3: DC Gate Trigger Voltage vs. Junction Temperature




Figure 4: On-State Current vs. On-State Voltage (Typical)




Figure 5: Power Dissipation (Typical) vs. RMS On-State Current




Figure 6: Maximum Allowable Case Temperature vs. On-State Current






Figure 7: Surge Peak On-State Current vs. Number of Cycles





Soldering Parameters

Reflow Condition		Pb – Free assembly
Pre Heat	- Temperature Min ($T_{s(min)}$)	150°C
	- Temperature Max ($T_{s(max)}$)	200°C
	- Time (min to max) (t_s)	60 – 180 secs
Average ramp up rate (Liquidus Temp (T_L) to peak		5°C/second max
$T_{s(max)}$ to T_L - Ramp-up Rate		5°C/second max
Reflow	- Temperature (T_L) (Liquidus)	217°C
	- Time (min to max) (t_s)	60 – 150 seconds
Peak Temperature (T_p)		260 ^{+0/-5} °C
Time within 5°C of actual peak Temperature (t_p)		20 – 40 seconds
Ramp-down Rate		5°C/second max
Time 25°C to peak Temperature (T_p)		8 minutes Max.
Do not exceed		280°C



Physical Specifications

Terminal Finish	100% Matte Tin-plated.
Body Material	UL Recognized compound meeting flammability rating V-0.
Lead Material	Copper Alloy

Design Considerations


Careful selection of the correct component for the application's operating parameters and environment will go a long way toward extending the operating life of the Thyristor. Good design practice should limit the maximum continuous current through the main terminals to 75% of the component rating. Other ways to ensure long life for a power discrete semiconductor are proper heat sinking and selection of voltage ratings for worst case conditions. Overheating, overvoltage (including dv/dt), and surge currents are the main killers of semiconductors. Correct mounting, soldering, and forming of the leads also help protect against component damage.

Reliability/Environmental Tests

Test	Specifications and Conditions
AC Blocking	MIL-STD-750, M-1040, Cond A Applied Peak AC voltage @ 125°C for 1008 hours
Temperature Cycling	MIL-STD-750, M-1051, 100 cycles; -40°C to +150°C; 15-min dwell-time
Temperature/Humidity	EIA / JEDEC, JESD22-A101 1008 hours; 320V - DC: 85°C; 85% rel humidity
High Temp Storage	MIL-STD-750, M-1031, 1008 hours; 150°C
Low-Temp Storage	1008 hours; -40°C
Resistance to Solder Heat	MIL-STD-750 Method 2031
Solderability	ANSI/J-STD-002, category 3, Test A
Lead Bend	MIL-STD-750, M-2036 Cond E



Dimensions




Dimensions	Inches		Millimeters	
	Min	Max	Min	Max
A	0.175	0.205	4.450	5.200
B	0.170	0.210	4.320	5.330
C	0.500	—	12.700	—
D	0.135	—	3.430	—
E	0.125	0.165	3.180	4.190
F	0.080	0.105	2.040	2.660
G	0.016	0.021	0.407	0.533
H	0.045	0.055	1.150	1.390
I	0.095	0.105	2.420	2.660
J	0.015	0.020	0.380	0.500


Packing Options

Part Number	Marking	Weight	Packing Mode	Base Quantity
S6X8ECS2	S6X8ECS2	0.217 g	Bulk	2500
S6X8ECS2AP	S6X8ECS2	0.217 g	Ammo Pack	2000
S6X8ECS2RP	S6X8ECS2	0.217 g	Tape & Reel	2000

Part Numbering System



Part Marking System






Thyristors

0.8 Amp Sensitive SCRs

Meets all EIA-468-C Standards



Meets all EIA-468-C Standards

