


REVISION		
REV	DATE	DESCRIPTION
A	3/11/24	527585GCP - RELEASE PER EM3406 MRY



Suitable Wire, CU kcmil/Al/NG			Over-Current Protection Fuse Required Class / Max Amp Rating							SCCR/RMS Sym. Amps 600V Max
CLASS	LINE	LOAD	J	T	RK1	RK5	G	CC		
B-C	600 - 2	600 - 2	500	500	400	200	60	30	100,000	
G, H, I	350 - 2	350 - 2	450	450	400	200	60	30	100,000	
	600 - 2	600 - 2	None						10,000	

- | | | | | |
|---|--|-------------------|----------------------------|-----------------------------------|
| NO | COMPONENT NO | DESCRIPTION | QTY/M | U/M |
| BILL OF MATERIAL | | | | |
| <S> | CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE | | | |
| ● | DENOTES CRITICAL CHARACTERISTICS. | | | |
| CPK | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE | | | |
| (ST) | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. | | | |
| CP | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE. | | | |
| MATL SPEC | | | FINISH | |
| DRW myork | | DATE
3/7/2023 | SCALE
NTS | FINISH GOOD WT

GRAMS/PIECE |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994 | | | | |
| 3RD ANGLE
PROJECTION
 | | | | |
| TITLE | | | | |
| SPLICER BLOCK 600V, 420A, 3 POLE OUTLINE | | | | |
|  Littelfuse®
CHICAGO, ILLINOIS 60631 | | REVISION

A | DRWG NO.

OL-LS43603 | SHEET 1 OF 1 |