


DSS6-015AS

150 V, 6 A Schottky Rectifier Diode

RoHS




Features:

- Very low V_F
- Extremely low switching losses
- Low I_{RM} values
- Improved thermal behavior
- High reliability circuit operation
- Low voltage peaks for reduced protection circuits
- Low noise switching
- Terminals finish: 100% pure tin
- Epoxy meets UL 94 V-0

Applications:

- Rectifiers in switch mode power supplies (SMPS)
- Free wheeling diode in low voltage converters

Pinout Diagram (TO-252AA)



C: Cathode; **A:** Anode; **tab:** Cathode

Product Summary

Characteristic	Value	Unit
V_{RRM}	150	V
I_{FAV}	6	A
V_F	0.65	V

Maximum Ratings ($T_A = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Characteristics	Condition	Max.	Units
V_{RRM}	Peak Repetitive Reverse Voltage	—	150	V
V_{RWM}	Working Peak Reverse Voltage			
V_R	DC Blocking Voltage			
I_{FAV}	Average Rectified Forward Current	50% duty cycle @ $T_C = 165^\circ\text{C}$, rectangular wave form	6	A
I_{FSM}	Peak One Cycle Non-Repetitive Surge Current	10 ms, Half Sine pulse, $T_{VJ} = 25^\circ\text{C}$	140	A
P_{tot}	Total power dissipation	$T_C = 25^\circ\text{C}$	50	W

Electrical Characteristics ($T_A = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Characteristics	Conditions	Typ.	Max.	Units
V_{F1}	Forward Voltage Drop ¹	@ 6 A, Pulse, $T_{VJ} = 25^\circ\text{C}$	—	0.80	V
V_{F2}		@ 6 A, Pulse, $T_{VJ} = 125^\circ\text{C}$	—	0.65	V
I_{R1}	Reverse Current*	@ $V_R = \text{rated } V_R$, $T_{VJ} = 25^\circ\text{C}$	—	250	μA
I_{R2}		@ $V_R = \text{rated } V_R$, $T_{VJ} = 125^\circ\text{C}$	—	2.5	mA
C_T	Junction Capacitance	@ $V_R = 24\text{ V}$, $T_C = 25^\circ\text{C}$, $f_{SIG} = 1\text{ MHz}$	112	—	pF

Note 1: Pulse width < 300 μs , duty cycle < 2%

Thermal-Mechanical Specifications

Symbol	Characteristics	Condition	Specification	Units
T_{VJ}	Junction Temperature	—	-55 to +175	$^\circ\text{C}$
T_O	Operation Temperature	—	-55 to +150	$^\circ\text{C}$
T_{stg}	Storage Temperature	—	-55 to +150	$^\circ\text{C}$
F_C	Mounting force with clip	—	Min 20 Max 60	N
R_{thJC}	Maximum Thermal Resistance Junction to Case	DC operation	3	K/W
R_{thCS}	Typical Thermal Resistance Case to Heat Sink	—	0.50	K/W
wt	Approximate Weight	—	0.39	g

Characteristic Curves

Fig. 1. Typical Forward Characteristics




Fig. 2. Typical Reverse Characteristics





Fig. 3. Typical Junction Capacitance




Symbol	Inches			Millimeters		
	Min.	Typical	Max.	Min.	Typical	Max
A	0.085	–	0.094	2.18	–	2.39
A1	–	–	0.005	–	–	0.13
b	0.025	–	0.035	0.64	–	0.89
c	0.018	–	0.035	0.46	–	0.89
D	0.250	–	0.264	6.35	–	6.73
D1	0.195	–	0.215	4.95	–	5.46
D2	0.170	–	–	4.32	–	–
E	0.235	0.240	0.245	5.97	6.10	6.22
e	0.090 BSC			2.29 BSC		
L	0.370	–	0.410	9.40	–	10.41
L1	0.114			2.90 REF		
L2	0.055	0.060	0.070	1.40	1.52	1.78
L3	0.063 REF			1.60 REF		
L4	–	–	0.040	–	–	1.02
Ø	0.043	–	0.051	1.10	–	1.30

IXYS
DSS6-015AS
XXXXXX
YYWWS

DS = Schottky Diode
S = Product Generation
6 = Current Rate
015 = Voltage Rating
AS = Package Code
YY = Year
WW = Work Week
S = Plant Location Code
XXXXXX = Lot Number

Part Number	Marking	Packing Mode	M.O.Q
DSS6-015AS	DSS6-015AS	Reel (2500 pcs)	—

Carrier Tape Specification (TO-252AA)



Symbol	Inches			Millimeters		
	Min.	Typical	Max.	Min.	Typical	Max.
A	0.267	–	0.276	6.80	–	7.00
B	0.409	–	0.417	10.40	–	10.60
C	0.102	–	0.110	2.60	–	2.80
d	Ø0.057	–	Ø0.065	Ø1.45	–	Ø1.65
E	0.065	–	0.073	1.65	–	1.85
F	0.291	–	0.299	7.40	–	7.60
P0	0.154	–	0.161	3.90	–	4.10
P	0.311	–	0.319	7.90	–	8.10
P1	0.075	–	0.083	1.90	–	2.10
W	0.626	–	0.642	15.90	–	16.30

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

